

April 27, 2010

## Main Specifications for Renesas Electronics' NV4A61MF

Optical Output Power (Continuous)	175 mW	
Optical Output Power (Pulse)	350 mW	
Threshold Current	35 mA	
Operating Current (Continuous, at 175 mW)	160 mA	
Lasing Wavelength	405 nm	
Beam Angle	Horizontal	9 deg
	Vertical	19 deg