


# Package Outline Drawing


## L10.3x2

10 LEAD THIN DUAL FLAT NO-LEAD PLASTIC PACKAGE WITH E-PAD (TDFN)


Rev 1, 4/15




TOP VIEW




BOTTOM VIEW



TYPICAL RECOMMENDED LAND PATTERN



SIDE VIEW



DETAIL "X"

**NOTES:**

1. Dimensions are in mm. Dimensions in ( ) for reference only.
  2. Dimensioning and tolerancing conform to AMSEY14.5m-1994.
  3. Unless otherwise specified, tolerance : Decimal  $\pm 0.05$
  4. Dimension b applies to the metalized terminal and is measured between 0.18mm and 0.30mm from the terminal tip.
- △ Tiebar shown (if present) is a non-functional feature and may be located on any of the 4 sides (or ends).
- △ The configuration of the pin #1 identifier is optional, but must be located within the zone indicated. The pin #1 identifier may be either a mold or mark feature.