



| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|------|------|
| | Min | Nom | Max |
| D | — | 21.0 | — |
| E | — | 21.0 | — |
| v | — | — | 0.15 |
| w | — | — | 0.30 |
| A | — | — | 2.10 |
| A ₁ | 0.40 | 0.50 | 0.60 |
| e | — | 1.00 | — |
| b | 0.50 | 0.60 | 0.70 |
| x | — | — | 0.10 |
| y | — | — | 0.15 |
| y ₁ | — | — | 0.35 |
| S _D | — | — | — |
| S _E | — | — | — |
| Z _D | — | 1.00 | — |
| Z _E | — | 1.00 | — |