




外形図 Outline drawing
 Renesasコード PRBG0640FC-A

RDK-G-001613

ルネサス エレクトロニクス株式会社
 Renesas Electronics Corporation

JEITA Package Code	RENESAS Code	MASS (Typ.) [g]
P-BGA640-27×27-1.00	PRBG0640FC-A	3.10



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	27.000	—
E	—	27.000	—
D1	—	25.000	—
E1	—	25.000	—
A	—	—	2.352
A1	0.400	—	0.600
b	0.500	—	0.700
e	—	1.000	—
aaa	—	—	0.200
bbb	—	—	0.250
ccc	—	—	0.350
ddd	—	—	0.150
eee	—	—	0.250
fff	—	—	0.100
n	—	640	—