



| | | | |
|---------------------|--------------|------------------|-----------------|
| JEITA Package Code | RENESAS Code | Previous Code | MASS (TYP.) [g] |
| P-BGA729-35x35-1.00 | PRBG0729FB-B | P729F1-100-RN9-2 | 4.8 |



| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|-------|-------|
| | Min | Nom | Max |
| D | 34.80 | 35.00 | 35.20 |
| D1 | — | 32.00 | — |
| E | 34.80 | 35.00 | 35.20 |
| E1 | — | 32.00 | — |
| w | — | — | 0.30 |
| e | — | 1.00 | — |
| A | 2.03 | 2.23 | 2.43 |
| A1 | 0.40 | 0.50 | 0.60 |
| A2 | — | 1.73 | — |
| b | 0.50 | 0.60 | 0.70 |
| x | — | — | 0.10 |
| y | — | — | 0.15 |
| y1 | — | — | 0.35 |
| ZD | — | 1.50 | — |
| ZE | — | 1.50 | — |