



Terminal cross section



Detail F

## NOTE)

1. DIMENSIONS\*1\*AND\*2\* DO NOT INCLUDE MOLD FLASH
2. DIMENSION\*3\* DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	28	—
E	—	28	—
A <sub>2</sub>	—	3.20	—
H <sub>D</sub>	30.4	30.6	30.8
H <sub>E</sub>	30.4	30.6	30.8
A	—	—	3.95
A <sub>1</sub>	0.25	0.40	0.50
b <sub>p</sub>	0.13	0.18	0.23
b <sub>1</sub>	—	0.16	—
c	0.12	0.17	0.22
c <sub>1</sub>	—	0.15	—
θ	0°	—	8°
e	—	0.4	—
x	—	—	0.11
y	—	—	0.08
Z <sub>D</sub>	—	1.40	—
Z <sub>E</sub>	—	1.40	—
L	0.3	0.5	0.7
L <sub>1</sub>	—	1.3	—