




416-PIN PLASTIC BGA (CAVITY DOWN TYPE) (40x40)



NOTE
Each lead centerline is located within $\phi 0.3$ mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	40.0±0.2
B	20.0
C	20.0
D	40.0±0.2
E	1.585
F	1.27 (T.P.)
G	0.6±0.1
H	1.88
J	2.48±0.30
K	0.15
L	$\phi 0.75 \pm 0.15$
M	0.3
N	0.25 MIN.