





JEITA Package Code  
P-HLQFP64-14x14-0.80

RENESAS Code  
PLQP0064GB-A

Previous Code  
64P6J-A

MASS[Typ.]  
0.9g



Detail F

NOTE)

1. DIMENSIONS \*1" AND \*2" DO NOT INCLUDE MOLD FLASH.
2. DIMENSION \*3" DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	13.9	14.0	14.1
E	13.9	14.0	14.1
A <sub>2</sub>	—	1.4	—
H <sub>D</sub>	15.8	16.0	16.2
H <sub>E</sub>	15.8	16.0	16.2
A	—	—	1.7
A <sub>1</sub>	0	0.1	0.2
b <sub>p</sub>	0.32	0.37	0.42
c	0.105	0.125	0.175
θ	0°	—	8°
Ⓧ	—	0.8	—
x	—	—	0.20
y	—	—	0.10
L	0.3	0.5	0.7
D <sub>2</sub>	—	8.0	—
E <sub>1</sub>	—	8.0	—