



### 304-PIN PLASTIC FBGA (19x19)



(UNIT:mm)

ITEM	DIMENSIONS
D	19.00±0.10
E	19.00±0.10
w	0.20
e	0.80
A	1.48±0.10
A1	0.35±0.06
A2	1.13
b	0.50 <sup>+0.05</sup> <sub>-0.10</sub>
x	0.08
y	0.10
y1	0.20
ZD	1.10
ZE	1.10

P304F1-80-HN2