



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	17.0	—
E	—	17.0	—
v	—	—	0.15
w	—	—	0.20
A	—	—	1.40
A <sub>1</sub>	0.35	0.40	0.45
e	—	0.80	—
b	0.45	0.50	0.55
x	—	—	0.08
y	—	—	0.10
y <sub>1</sub>	—	—	0.2
S <sub>D</sub>	—	—	—
S <sub>E</sub>	—	—	—
Z <sub>D</sub>	—	0.9	—
Z <sub>E</sub>	—	0.9	—