




JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-LFQFP216-24x24-0.40	PLQP0216LA-A	216P6R-B	1.7g



Terminal cross section



Detail F

- NOTE)
1. DIMENSIONS **1* AND **2* DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION **3* DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	23.9	24.0	24.1
E	23.9	24.0	24.1
A ₂	—	1.4	—
H _D	25.8	26.0	26.2
H _E	25.8	26.0	26.2
A	—	—	1.7
A ₁	0	0.1	0.2
b _p	0.125	0.145	0.165
b ₁	—	0.135	—
c	0.09	0.145	0.20
c ₁	—	0.125	—
θ	0°	—	8°
Ⓢ	—	0.4	—
x	—	—	0.07
y	—	—	0.10
Z _D	—	1.4	—
Z _E	—	1.4	—
L	0.35	0.5	0.65
L ₁	—	1.0	—