

JEITA Package Code

RENESAS Code

Previous Code




MASS[Typ.]

P-QFP100-14x20-0.65

PRQP0100JD-B

100P6F-A

1.8g



Detail F

NOTE)

1. DIMENSIONS *1* AND *2* DO NOT INCLUDE MOLD FLASH.
2. DIMENSION *3* DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	19.8	20.0	20.2
E	13.8	14.0	14.2
A ₂	—	2.8	—
H _D	22.5	22.8	23.1
H _E	16.5	16.8	17.1
A	—	—	3.05
A ₁	0	0.1	0.2
b _p	0.25	0.3	0.4
c	0.13	0.15	0.2
θ	0°	—	10°
[e]	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z _D	—	0.575	—
Z _E	—	0.825	—
L	0.4	0.6	0.8