





JEITA Package Code
P-QFP56-10x10-0.65

RENASAS Code
PRQP0056JA-A

Previous Code
56P6S-A

MASS[Typ.]
0.6g



Detail F

NOTE)

1. DIMENSIONS $*1^*$ AND $*2^*$ DO NOT INCLUDE MOLD FLASH.
2. DIMENSION $*3^*$ DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	9.8	10.0	10.2
E	9.8	10.0	10.2
A_2	—	2.8	—
H_D	12.5	12.8	13.1
H_E	12.5	12.8	13.1
A	—	—	3.05
A_1	0	0.1	0.2
b_p	0.25	0.3	0.4
c	0.13	0.15	0.2
θ	0°	—	10°
e	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z_D	—	0.775	—
Z_E	—	0.775	—
L	0.4	0.6	0.8