


| | | | |
|-----------------------|--------------|---------------|------------|
| JEITA Package Code | RENESAS Code | Previous Code | MASS[Typ.] |
| S-XFBGA6-0.9x1.4-0.50 | SXBG0006KB-A | TBS-6AV | 0.001g |



* Reference value.

| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|------|----------|
| | Min | Nom | Max |
| A | — | — | 0.50 |
| A ₁ | 0.155 | — | 0.185 |
| A ₂ | — | — | (0.315)* |
| b | 0.20 | — | 0.25 |
| D | — | 0.90 | — |
| E | — | 1.40 | — |
| e | — | 0.50 | — |
| x | — | — | 0.05 |
| y | — | — | 0.05 |
| y ₁ | — | — | 0.20 |
| Z _D | — | 0.20 | — |
| Z _E | — | 0.20 | — |