


## 24-PIN PLASTIC SSOP(19.1x9.6)



(UNIT:mm)

ITEM	DIMENSIONS
D	9.60±0.10
E	19.10±0.10
HE	21.10±0.20
A	2.47±0.20
A1	0.12±0.05
A2	2.35
A3	0.25
e	0.50
bp	0.20 <sup>+0.10</sup> <sub>-0.05</sub>
c	0.15 <sup>+0.05</sup> <sub>-0.01</sub>
L	0.50
Lp	0.60±0.15
L1	1.00±0.15
x	0.16
y	0.10
θ	3° <sup>+5°</sup> <sub>-3°</sub>

P24MM-50-MAB-1