




# 680-PIN TAPE BGA (40x40)



Section B-B



ITEM	MILLIMETERS
D	40.0±0.20
E	40.0±0.20
w	0.15
A	1.30 <sup>+0.30</sup> <sub>-0.20</sub>
A1	0.50±0.10
A2	0.80
A4	0.25 MIN.
Ⓢ	1.00
b	0.60±0.10
x	0.10
y	0.15
y1	0.35
ZD	1.00
ZE	1.00

P680FF-100-UA1