





432-PIN TAPE FBGA (HEAT SPREADER TYPE) (27x27)



ITEM	MILLIMETERS
A	27.00±0.20
A1	15.11 MAX.
A2	15.11 MAX.
D	27.00±0.20
E	1.50
F	0.8 (T.P.)
G	0.40±0.05
H	1.00
J	1.40 ^{+0.10} _{-0.50}
K	0.10
L	φ0.50 ^{+0.05} _{-0.10}
M	0.08
N	0.15 MIN.
Q	3.0
R	2.0
S	2.0
T	3.0
U	15.11
W	0.15
X	15.11
Y	C 0.4
Z	0.20

S432N7-80-BC-1