



144-PIN TAPE FBGA (7x7)



(UNIT:mm)

| ITEM | DIMENSIONS |
|------|------------|
| D | 7.00±0.10 |
| E | 7.00±0.10 |
| w | 0.20 |
| A | 0.88±0.10 |
| A1 | 0.18±0.05 |
| A2 | 0.70 |
| e | 0.50 |
| b | 0.32±0.05 |
| x | 0.05 |
| y | 0.08 |
| y1 | 0.20 |
| ZD | 0.75 |
| ZE | 0.75 |

P144F9-50-BN5