





## 28-PIN PLASTIC TSOP (II) (10.16mm(400))



detail of lead end



### NOTE

Each lead centerline is located within 0.21 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	18.63 MAX.
B	1.075 MAX.
C	1.27 (T.P.)
D	$0.42^{+0.08}_{-0.07}$
E	$0.1 \pm 0.05$
F	1.2 MAX.
G	0.97
H	$11.76 \pm 0.2$
I	$10.16 \pm 0.1$
J	$0.8 \pm 0.2$
K	$0.145^{+0.025}_{-0.015}$
L	$0.5 \pm 0.1$
M	0.21
N	0.10
P	$3^{\circ+7^{\circ}}_{-3^{\circ}}$

S28G5-50-7JD4-1