





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-TSOP(2)32-10.16x20.95-1.27	PTSB0032DC-A	32PTY-A	0.5g



Detail F

NOTE)

1. DIMENSIONS $*1$ AND $*2$ DO NOT INCLUDE MOLD FLASH.
2. DIMENSION $*3$ DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	20.85	20.95	21.05
E	10.06	10.16	10.26
A2	—	1.0	—
A1	0.05	0.125	0.2
A	—	—	1.2
b_p	0.35	0.4	0.5
c	0.105	0.125	0.175
θ	0°	—	10°
H_E	11.56	11.76	11.96
e	—	1.27	—
x	—	—	0.25
y	—	—	0.10
Z_b	—	0.95	—
L	0.4	0.5	0.6