





34-PIN PLASTIC TSOP(II) (12.70 mm (500))



detail of lead end



NOTE

Each lead centerline is located within 0.21 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	22.66 MAX.
B	1.2 MAX.
C	1.27 (T.P.)
D	0.40±0.10
E	0.05±0.05
F	1.1 MAX.
G	0.97
H	14.3±0.2
I	12.7±0.1
J	0.8±0.2
K	0.125 ^{+0.10} _{-0.05}
L	0.5±0.1
M	0.21
N	0.10
P	3 ^{+7°} _{-3°}

S34G7-50-7JD-1