

This is information about the next version of PG-FP6.

Product	Version
Programming GUI for PG-FP6 (FP6 Terminal)	V1.15.00

✓: supported; X: not supported; -: Support not planned

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RA	RA0E1	R7FA0E105	✓ (SWD)	R7FA0E1x5.pr6	
RA	RA0E1	R7FA0E107	✓ (SWD)	R7FA0E1x7.pr6	
RA	RA0E2	R7FA0E207	✓ (SWD)	R7FA0E2x7.pr6	
RA	RA0E2	R7FA0E209	✓ (SWD)	R7FA0E2x9.pr6	
RA	RA2A1	R7FA2A1AB	✓ (2 wire UART, SWD)	R7FA2A1AB.pr6	
RA	RA2A2	R7FA2A2AD	✓ (2 wire UART, SWD)	R7FA2A2xD.pr6	
RA	RA2A2	R7FA2A2BD	✓ (2 wire UART, SWD)	R7FA2A2xD.pr6	
RA	RA2E1	R7FA2E1A5	✓ (2 wire UART, SWD)	R7FA2E1A5.pr6	
RA	RA2E1	R7FA2E1A7	✓ (2 wire UART, SWD)	R7FA2E1A7.pr6	
RA	RA2E1	R7FA2E1A9	✓ (2 wire UART, SWD)	R7FA2E1A9.pr6	
RA	RA2E2	R7FA2E2A3	✓ (2 wire UART, SWD)	R7FA2E2A3.pr6	
RA	RA2E2	R7FA2E2A5	✓ (2 wire UART, SWD)	R7FA2E2A5.pr6	
RA	RA2E2	R7FA2E2A7	✓ (2 wire UART, SWD)	R7FA2E2A7.pr6	
RA	RA2E3	R7FA2E305	✓ (2 wire UART, SWD)	R7FA2E3x5.pr6	
RA	RA2E3	R7FA2E307	✓ (2 wire UART, SWD)	R7FA2E3x7.pr6	
RA	RA2L1	R7FA2L1A9	✓ (2 wire UART, SWD)	R7FA2L1A9.pr6	
RA	RA2L1	R7FA2L1AB	✓ (2 wire UART, SWD)	R7FA2L1AB.pr6	
RA	RA2T1	R7FA2T107	✓ (2 wire UART, SWD)	R7FA2T1x7.pr6	
RA	RA4E1	R7FA4E10B	✓ (2 wire UART, SWD)	R7FA4E10B.pr6	
RA	RA4E1	R7FA4E10D	✓ (2 wire UART, SWD)	R7FA4E10D.pr6	
RA	RA4E2	R7FA4E2B9	✓ (2 wire UART, SWD)	R7FA4E2x9.pr6	
RA	RA4L1	R7FA4L1BB	✓ (2 wire UART, SWD)	R7FA4L1xB L.pr6	Linear mode
RA	RA4L1	R7FA4L1BB	✓ (2 wire UART, SWD)	R7FA4L1xB D.pr6	Dual mode
RA	RA4L1	R7FA4L1BD	✓ (2 wire UART, SWD)	R7FA4L1xD L.pr6	Linear mode
RA	RA4L1	R7FA4L1BD	✓ (2 wire UART, SWD)	R7FA4L1xD D.pr6	Dual mode
RA	RA4M1	R7FA4M1AB	✓ (2 wire UART, SWD)	R7FA4M1AB.pr6	
RA	RA4M2	R7FA4M2AB	✓ (2 wire UART, SWD)	R7FA4M2AB.pr6	
RA	RA4M2	R7FA4M2AC	✓ (2 wire UART, SWD)	R7FA4M2AC.pr6	
RA	RA4M2	R7FA4M2AD	✓ (2 wire UART, SWD)	R7FA4M2AD.pr6	
RA	RA4M3	R7FA4M3AD	✓ (2 wire UART, SWD)	R7FA4M3AD L.pr6	
RA	RA4M3	R7FA4M3AE	✓ (2 wire UART, SWD)	R7FA4M3AE L.pr6	
RA	RA4M3	R7FA4M3AF	✓ (2 wire UART, SWD)	R7FA4M3AF L.pr6	
RA	RA4T1	R7FA4T1B9	✓ (2 wire UART, SWD)	R7FA4T1x9.pr6	
RA	RA4T1	R7FA4T1BB	✓ (2 wire UART, SWD)	R7FA4T1xB.pr6	
RA	RA4W1	R7FA4W1AD	✓ (2 wire UART, SWD)	R7FA4W1AD.pr6	
RA	RA6E1	R7FA6E10D	✓ (2 wire UART, SWD)	R7FA6E10D L.pr6	Linear mode
RA	RA6E1	R7FA6E10D	✓ (2 wire UART, SWD)	R7FA6E10D D.pr6	Dual mode
RA	RA6E1	R7FA6E10F	✓ (2 wire UART, SWD)	R7FA6E10F L.pr6	Linear mode
RA	RA6E1	R7FA6E10F	✓ (2 wire UART, SWD)	R7FA6E10D D.pr6	Dual mode
RA	RA6E2	R7FA6E2B9	✓ (2 wire UART, SWD)	R7FA6E2x9.pr6	
RA	RA6E2	R7FA6E2BB	✓ (2 wire UART, SWD)	R7FA6E2xB.pr6	
RA	RA6M1	R7FA6M1AD	✓ (2 wire UART, SWD)	R7FA6M1AD.pr6	
RA	RA6M2	R7FA6M2AD	✓ (2 wire UART, SWD)	R7FA6M2AD.pr6	
RA	RA6M2	R7FA6M2AF	✓ (2 wire UART, SWD)	R7FA6M2AF.pr6	
RA	RA6M3	R7FA6M3AF	✓ (2 wire UART, SWD)	R7FA6M3AF.pr6	
RA	RA6M3	R7FA6M3AH	✓ (2 wire UART, SWD)	R7FA6M3AH.pr6	
RA	RA6M4	R7FA6M4AD	✓ (2 wire UART, SWD)	R7FA6M4AD L.pr6	Linear mode
RA	RA6M4	R7FA6M4AD	✓ (2 wire UART, SWD)	R7FA6M4AD D.pr6	Dual mode
RA	RA6M4	R7FA6M4AE	✓ (2 wire UART, SWD)	R7FA6M4AE L.pr6	Linear mode
RA	RA6M4	R7FA6M4AE	✓ (2 wire UART, SWD)	R7FA6M4AE D.pr6	Dual mode
RA	RA6M4	R7FA6M4AF	✓ (2 wire UART, SWD)	R7FA6M4AF L.pr6	Linear mode
RA	RA6M4	R7FA6M4AF	✓ (2 wire UART, SWD)	R7FA6M4AF D.pr6	Dual mode
RA	RA6M5	R7FA6M5AG	✓ (2 wire UART, SWD)	R7FA6M5AG L.pr6	Linear mode
RA	RA6M5	R7FA6M5AG	✓ (2 wire UART, SWD)	R7FA6M5AG D.pr6	Dual mode
RA	RA6M5	R7FA6M5AH	✓ (2 wire UART, SWD)	R7FA6M5AH L.pr6	Linear mode
RA	RA6M5	R7FA6M5AH	✓ (2 wire UART, SWD)	R7FA6M5AH D.pr6	Dual mode
RA	RA6M5	R7FA6M5BF	✓ (2 wire UART, SWD)	R7FA6M5BF L.pr6	Linear mode
RA	RA6M5	R7FA6M5BF	✓ (2 wire UART, SWD)	R7FA6M5BF D.pr6	Dual mode
RA	RA6M5	R7FA6M5BG	✓ (2 wire UART, SWD)	R7FA6M5BG L.pr6	Linear mode
RA	RA6M5	R7FA6M5BG	✓ (2 wire UART, SWD)	R7FA6M5BG D.pr6	Dual mode
RA	RA6M5	R7FA6M5BH	✓ (2 wire UART, SWD)	R7FA6M5BH L.pr6	Linear mode

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RA	RA6M5	R7FA6M5BH	✓ (2 wire UART, SWD)	R7FA6M5BH_D.pr6	Dual mode
RA	RA6T1	R7FA6T1AB	✓ (2 wire UART, SWD)	R7FA6T1AB.pr6	
RA	RA6T1	R7FA6T1AD	✓ (2 wire UART, SWD)	R7FA6T1AD.pr6	
RA	RA6T2	R7FA6T2AB	✓ (2 wire UART, SWD)	R7FA6T2xB.pr6	
RA	RA6T2	R7FA6T2AD	✓ (2 wire UART, SWD)	R7FA6T2xD.pr6	
RA	RA6T2	R7FA6T2BB	✓ (2 wire UART, SWD)	R7FA6T2xB.pr6	
RA	RA6T2	R7FA6T2BD	✓ (2 wire UART, SWD)	R7FA6T2xD.pr6	
RA	RA6T3	R7FA6T3BB	✓ (2 wire UART, SWD)	R7FA6T3xB.pr6	
RA	RA8D1	R7FA8D1AF	✓ (2 wire UART, SWD)	R7FA8D1xF_L.pr6	Linear mode
RA	RA8D1	R7FA8D1AF	✓ (2 wire UART, SWD)	R7FA8D1xF_D.pr6	Dual mode
RA	RA8D1	R7FA8D1AH	✓ (2 wire UART, SWD)	R7FA8D1xH_L.pr6	Linear mode
RA	RA8D1	R7FA8D1AH	✓ (2 wire UART, SWD)	R7FA8D1xH_D.pr6	Dual mode
RA	RA8D1	R7FA8D1BF	✓ (2 wire UART, SWD)	R7FA8D1xF_L.pr6	Linear mode
RA	RA8D1	R7FA8D1BF	✓ (2 wire UART, SWD)	R7FA8D1xF_D.pr6	Dual mode
RA	RA8D1	R7FA8D1BH	✓ (2 wire UART, SWD)	R7FA8D1xH_L.pr6	Linear mode
RA	RA8D1	R7FA8D1BH	✓ (2 wire UART, SWD)	R7FA8D1xH_D.pr6	Dual mode
RA	RA8E1	R7FA8E1AF	✓ (2 wire UART, SWD)	R7FA8E1xF_L.pr6	Linear mode
RA	RA8E1	R7FA8E1AF	✓ (2 wire UART, SWD)	R7FA8E1xF_D.pr6	Dual mode
RA	RA8E2	R7FA8E2AF	✓ (2 wire UART, SWD)	R7FA8E2xF_L.pr6	Linear mode
RA	RA8E2	R7FA8E2AF	✓ (2 wire UART, SWD)	R7FA8E2xF_D.pr6	Dual mode
RA	RA8M1	R7FA8M1AF	✓ (2 wire UART, SWD)	R7FA8M1xF_L.pr6	Linear mode
RA	RA8M1	R7FA8M1AF	✓ (2 wire UART, SWD)	R7FA8M1xF_D.pr6	Dual mode
RA	RA8M1	R7FA8M1AH	✓ (2 wire UART, SWD)	R7FA8M1xH_L.pr6	Linear mode
RA	RA8M1	R7FA8M1AH	✓ (2 wire UART, SWD)	R7FA8M1xH_D.pr6	Dual mode
RA	RA8T1	R7FA8T1AF	✓ (2 wire UART, SWD)	R7FA8T1xF_L.pr6	Linear mode
RA	RA8T1	R7FA8T1AF	✓ (2 wire UART, SWD)	R7FA8T1xF_D.pr6	Dual mode
RA	RA8T1	R7FA8T1AH	✓ (2 wire UART, SWD)	R7FA8T1xH_L.pr6	Linear mode
RA	RA8T1	R7FA8T1AH	✓ (2 wire UART, SWD)	R7FA8T1xH_D.pr6	Dual mode
RL78	RL78/D1A	R5F10CGB	✓ (1 wire UART)	R5F10CGB.pr5	
RL78	RL78/D1A	R5F10CGC	✓ (1 wire UART)	R5F10CGC.pr5	
RL78	RL78/D1A	R5F10CGD	✓ (1 wire UART)	R5F10CGD.pr5	
RL78	RL78/D1A	R5F10CLD	✓ (1 wire UART)	R5F10CLD.pr5	
RL78	RL78/D1A	R5F10CMD	✓ (1 wire UART)	R5F10CMD.pr5	
RL78	RL78/D1A	R5F10CME	✓ (1 wire UART)	R5F10CME.pr5	
RL78	RL78/D1A	R5F10DGC	✓ (1 wire UART)	R5F10DGC.pr5	
RL78	RL78/D1A	R5F10DGD	✓ (1 wire UART)	R5F10DGD.pr5	
RL78	RL78/D1A	R5F10DGE	✓ (1 wire UART)	R5F10DGE.pr5	
RL78	RL78/D1A	R5F10DLD	✓ (1 wire UART)	R5F10DLD.pr5	
RL78	RL78/D1A	R5F10DLE	✓ (1 wire UART)	R5F10DLE.pr5	
RL78	RL78/D1A	R5F10DMD	✓ (1 wire UART)	R5F10DMD.pr5	
RL78	RL78/D1A	R5F10DME	✓ (1 wire UART)	R5F10DME.pr5	
RL78	RL78/D1A	R5F10DMF	✓ (1 wire UART)	R5F10DMF.pr5	
RL78	RL78/D1A	R5F10DMG	✓ (1 wire UART)	R5F10DMG.pr5	
RL78	RL78/D1A	R5F10DMJ	✓ (1 wire UART)	R5F10DMJ.pr5	
RL78	RL78/D1A	R5F10DPE	✓ (1 wire UART)	R5F10DPE.pr5	
RL78	RL78/D1A	R5F10DPF	✓ (1 wire UART)	R5F10DPF.pr5	
RL78	RL78/D1A	R5F10DPG	✓ (1 wire UART)	R5F10DPG.pr5	
RL78	RL78/D1A	R5F10DPJ	✓ (1 wire UART)	R5F10DPJ.pr5	
RL78	RL78/D1A	R5F10DPK	✓ (1 wire UART)	R5F10DPK.pr5	
RL78	RL78/D1A	R5F10DPL	✓ (1 wire UART)	R5F10DPL.pr5	
RL78	RL78/D1A	R5F10DSJ	✓ (1 wire UART)	R5F10DSJ.pr5	
RL78	RL78/D1A	R5F10DSK	✓ (1 wire UART)	R5F10DSK.pr5	
RL78	RL78/D1A	R5F10DSL	✓ (1 wire UART)	R5F10DSL.pr5	
RL78	RL78/D1A	R5F10TPJ	✓ (1 wire UART)	R5F10TPJ.pr5	
RL78	RL78/F12	R5F10968	✓ (1 wire UART)	R5F10968.pr5	
RL78	RL78/F12	R5F1096A	✓ (1 wire UART)	R5F1096A.pr5	
RL78	RL78/F12	R5F1096B	✓ (1 wire UART)	R5F1096B.pr5	
RL78	RL78/F12	R5F1096C	✓ (1 wire UART)	R5F1096C.pr5	
RL78	RL78/F12	R5F1096D	✓ (1 wire UART)	R5F1096D.pr5	
RL78	RL78/F12	R5F1096E	✓ (1 wire UART)	R5F1096E.pr5	
RL78	RL78/F12	R5F109AA	✓ (1 wire UART)	R5F109AA.pr5	
RL78	RL78/F12	R5F109AB	✓ (1 wire UART)	R5F109AB.pr5	
RL78	RL78/F12	R5F109AC	✓ (1 wire UART)	R5F109AC.pr5	
RL78	RL78/F12	R5F109AD	✓ (1 wire UART)	R5F109AD.pr5	
RL78	RL78/F12	R5F109AE	✓ (1 wire UART)	R5F109AE.pr5	
RL78	RL78/F12	R5F109BA	✓ (1 wire UART)	R5F109BA.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/F12	R5F109BB	✓ (1 wire UART)	R5F109BB.pr5	
RL78	RL78/F12	R5F109BC	✓ (1 wire UART)	R5F109BC.pr5	
RL78	RL78/F12	R5F109BD	✓ (1 wire UART)	R5F109BD.pr5	
RL78	RL78/F12	R5F109BE	✓ (1 wire UART)	R5F109BE.pr5	
RL78	RL78/F12	R5F109GA	✓ (1 wire UART)	R5F109GA.pr5	
RL78	RL78/F12	R5F109GB	✓ (1 wire UART)	R5F109GB.pr5	
RL78	RL78/F12	R5F109GC	✓ (1 wire UART)	R5F109GC.pr5	
RL78	RL78/F12	R5F109GD	✓ (1 wire UART)	R5F109GD.pr5	
RL78	RL78/F12	R5F109GE	✓ (1 wire UART)	R5F109GE.pr5	
RL78	RL78/F12	R5F109LA	✓ (1 wire UART)	R5F109LA.pr5	
RL78	RL78/F12	R5F109LB	✓ (1 wire UART)	R5F109LB.pr5	
RL78	RL78/F12	R5F109LC	✓ (1 wire UART)	R5F109LC.pr5	
RL78	RL78/F12	R5F109LD	✓ (1 wire UART)	R5F109LD.pr5	
RL78	RL78/F12	R5F109LE	✓ (1 wire UART)	R5F109LE.pr5	
RL78	RL78/F13	R5F10A6A	✓ (1 wire UART)	R5F10A6A.pr5	
RL78	RL78/F13	R5F10A6C	✓ (1 wire UART)	R5F10A6C.pr5	
RL78	RL78/F13	R5F10A6D	✓ (1 wire UART)	R5F10A6D.pr5	
RL78	RL78/F13	R5F10A6E	✓ (1 wire UART)	R5F10A6E.pr5	
RL78	RL78/F13	R5F10AAA	✓ (1 wire UART)	R5F10AAA.pr5	
RL78	RL78/F13	R5F10AAC	✓ (1 wire UART)	R5F10AAC.pr5	
RL78	RL78/F13	R5F10AAD	✓ (1 wire UART)	R5F10AAD.pr5	
RL78	RL78/F13	R5F10AAE	✓ (1 wire UART)	R5F10AAE.pr5	
RL78	RL78/F13	R5F10ABA	✓ (1 wire UART)	R5F10ABA.pr5	
RL78	RL78/F13	R5F10ABC	✓ (1 wire UART)	R5F10ABC.pr5	
RL78	RL78/F13	R5F10ABD	✓ (1 wire UART)	R5F10ABD.pr5	
RL78	RL78/F13	R5F10ABE	✓ (1 wire UART)	R5F10ABE.pr5	
RL78	RL78/F13	R5F10AGA	✓ (1 wire UART)	R5F10AGA.pr5	
RL78	RL78/F13	R5F10AGC	✓ (1 wire UART)	R5F10AGC.pr5	
RL78	RL78/F13	R5F10AGD	✓ (1 wire UART)	R5F10AGD.pr5	
RL78	RL78/F13	R5F10AGE	✓ (1 wire UART)	R5F10AGE.pr5	
RL78	RL78/F13	R5F10AGF	✓ (1 wire UART)	R5F10AGF.pr5	
RL78	RL78/F13	R5F10AGG	✓ (1 wire UART)	R5F10AGG.pr5	
RL78	RL78/F13	R5F10ALC	✓ (1 wire UART)	R5F10ALC.pr5	
RL78	RL78/F13	R5F10ALD	✓ (1 wire UART)	R5F10ALD.pr5	
RL78	RL78/F13	R5F10ALE	✓ (1 wire UART)	R5F10ALE.pr5	
RL78	RL78/F13	R5F10ALF	✓ (1 wire UART)	R5F10ALF.pr5	
RL78	RL78/F13	R5F10ALG	✓ (1 wire UART)	R5F10ALG.pr5	
RL78	RL78/F13	R5F10AME	✓ (1 wire UART)	R5F10AME.pr5	
RL78	RL78/F13	R5F10AMF	✓ (1 wire UART)	R5F10AMF.pr5	
RL78	RL78/F13	R5F10AMG	✓ (1 wire UART)	R5F10AMG.pr5	
RL78	RL78/F13	R5F10BAC	✓ (1 wire UART)	R5F10BAC.pr5	
RL78	RL78/F13	R5F10BAD	✓ (1 wire UART)	R5F10BAD.pr5	
RL78	RL78/F13	R5F10BAE	✓ (1 wire UART)	R5F10BAE.pr5	
RL78	RL78/F13	R5F10BAF	✓ (1 wire UART)	R5F10BAF.pr5	
RL78	RL78/F13	R5F10BAG	✓ (1 wire UART)	R5F10BAG.pr5	
RL78	RL78/F13	R5F10BBC	✓ (1 wire UART)	R5F10BBC.pr5	
RL78	RL78/F13	R5F10BBD	✓ (1 wire UART)	R5F10BBD.pr5	
RL78	RL78/F13	R5F10BBE	✓ (1 wire UART)	R5F10BBE.pr5	
RL78	RL78/F13	R5F10BBF	✓ (1 wire UART)	R5F10BBF.pr5	
RL78	RL78/F13	R5F10BBG	✓ (1 wire UART)	R5F10BBG.pr5	
RL78	RL78/F13	R5F10BGC	✓ (1 wire UART)	R5F10BGC.pr5	
RL78	RL78/F13	R5F10BGD	✓ (1 wire UART)	R5F10BGD.pr5	
RL78	RL78/F13	R5F10BGE	✓ (1 wire UART)	R5F10BGE.pr5	
RL78	RL78/F13	R5F10BGF	✓ (1 wire UART)	R5F10BGF.pr5	
RL78	RL78/F13	R5F10BGG	✓ (1 wire UART)	R5F10BGG.pr5	
RL78	RL78/F13	R5F10BLC	✓ (1 wire UART)	R5F10BLC.pr5	
RL78	RL78/F13	R5F10BLD	✓ (1 wire UART)	R5F10BLD.pr5	
RL78	RL78/F13	R5F10BLE	✓ (1 wire UART)	R5F10BLE.pr5	
RL78	RL78/F13	R5F10BLF	✓ (1 wire UART)	R5F10BLF.pr5	
RL78	RL78/F13	R5F10BLG	✓ (1 wire UART)	R5F10BLG.pr5	
RL78	RL78/F13	R5F10BME	✓ (1 wire UART)	R5F10BME.pr5	
RL78	RL78/F13	R5F10BMF	✓ (1 wire UART)	R5F10BMF.pr5	
RL78	RL78/F13	R5F10BMG	✓ (1 wire UART)	R5F10BMG.pr5	
RL78	RL78/F14	R5F10PAD	✓ (1 wire UART)	R5F10PAD.pr5	
RL78	RL78/F14	R5F10PAE	✓ (1 wire UART)	R5F10PAE.pr5	
RL78	RL78/F14	R5F10PBD	✓ (1 wire UART)	R5F10PBD.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/F14	R5F10PBE	✓ (1 wire UART)	R5F10PBE.pr5	
RL78	RL78/F14	R5F10PGD	✓ (1 wire UART)	R5F10PGD.pr5	
RL78	RL78/F14	R5F10PGE	✓ (1 wire UART)	R5F10PGE.pr5	
RL78	RL78/F14	R5F10PGF	✓ (1 wire UART)	R5F10PGF.pr5	
RL78	RL78/F14	R5F10PGG	✓ (1 wire UART)	R5F10PGG.pr5	
RL78	RL78/F14	R5F10PGH	✓ (1 wire UART)	R5F10PGH.pr5	
RL78	RL78/F14	R5F10PGJ	✓ (1 wire UART)	R5F10PGJ.pr5	
RL78	RL78/F14	R5F10PLE	✓ (1 wire UART)	R5F10PLE.pr5	
RL78	RL78/F14	R5F10PLF	✓ (1 wire UART)	R5F10PLF.pr5	
RL78	RL78/F14	R5F10PLG	✓ (1 wire UART)	R5F10PLG.pr5	
RL78	RL78/F14	R5F10PLH	✓ (1 wire UART)	R5F10PLH.pr5	
RL78	RL78/F14	R5F10PLJ	✓ (1 wire UART)	R5F10PLJ.pr5	
RL78	RL78/F14	R5F10PME	✓ (1 wire UART)	R5F10PME.pr5	
RL78	RL78/F14	R5F10PMF	✓ (1 wire UART)	R5F10PMF.pr5	
RL78	RL78/F14	R5F10PMG	✓ (1 wire UART)	R5F10PMG.pr5	
RL78	RL78/F14	R5F10PMH	✓ (1 wire UART)	R5F10PMH.pr5	
RL78	RL78/F14	R5F10PMJ	✓ (1 wire UART)	R5F10PMJ.pr5	
RL78	RL78/F14	R5F10PPE	✓ (1 wire UART)	R5F10PPE.pr5	
RL78	RL78/F14	R5F10PPF	✓ (1 wire UART)	R5F10PPF.pr5	
RL78	RL78/F14	R5F10PPG	✓ (1 wire UART)	R5F10PPG.pr5	
RL78	RL78/F14	R5F10PPH	✓ (1 wire UART)	R5F10PPH.pr5	
RL78	RL78/F14	R5F10PPJ	✓ (1 wire UART)	R5F10PPJ.pr5	
RL78	RL78/F15	R5F113GK	✓ (1 wire UART)	R5F113GK.pr5	
RL78	RL78/F15	R5F113GL	✓ (1 wire UART)	R5F113GL.pr5	
RL78	RL78/F15	R5F113LK	✓ (1 wire UART)	R5F113LK.pr5	
RL78	RL78/F15	R5F113LL	✓ (1 wire UART)	R5F113LL.pr5	
RL78	RL78/F15	R5F113MK	✓ (1 wire UART)	R5F113MK.pr5	
RL78	RL78/F15	R5F113ML	✓ (1 wire UART)	R5F113ML.pr5	
RL78	RL78/F15	R5F113PG	✓ (1 wire UART)	R5F113PG.pr5	
RL78	RL78/F15	R5F113PH	✓ (1 wire UART)	R5F113PH.pr5	
RL78	RL78/F15	R5F113PJ	✓ (1 wire UART)	R5F113PJ.pr5	
RL78	RL78/F15	R5F113PK	✓ (1 wire UART)	R5F113PK.pr5	
RL78	RL78/F15	R5F113PL	✓ (1 wire UART)	R5F113PL.pr5	
RL78	RL78/F15	R5F113TG	✓ (1 wire UART)	R5F113TG.pr5	
RL78	RL78/F15	R5F113TH	✓ (1 wire UART)	R5F113TH.pr5	
RL78	RL78/F15	R5F113TJ	✓ (1 wire UART)	R5F113TJ.pr5	
RL78	RL78/F15	R5F113TK	✓ (1 wire UART)	R5F113TK.pr5	
RL78	RL78/F15	R5F113TL	✓ (1 wire UART)	R5F113TL.pr5	
RL78	RL78/F1A	R5F114GC	✓ (1 wire UART)	R5F114GC.pr5	
RL78	RL78/F1A	R5F114GD	✓ (1 wire UART)	R5F114GD.pr5	
RL78	RL78/F1A	R5F114GE	✓ (1 wire UART)	R5F114GE.pr5	
RL78	RL78/F1A	R5F114GF	✓ (1 wire UART)	R5F114GF.pr5	
RL78	RL78/F1A	R5F114GG	✓ (1 wire UART)	R5F114GG.pr5	
RL78	RL78/F1E	R5F11KLE	✓ (1 wire UART)	R5F11KLE.pr5	
RL78	RL78/F1E	R5F11KLF	✓ (1 wire UART)	R5F11KLF.pr5	
RL78	RL78/F1E	R5F11KLG	✓ (1 wire UART)	R5F11KLG.pr5	
RL78	RL78/F1E	R5F11LLE	✓ (1 wire UART)	R5F11LLE.pr5	
RL78	RL78/F1E	R5F11LLF	✓ (1 wire UART)	R5F11LLF.pr5	
RL78	RL78/F1E	R5F11LLG	✓ (1 wire UART)	R5F11LLG.pr5	
RL78	RL78/F22	R7F122F7G	✓ (1 wire UART)	R7F122F7G.pr6	
RL78	RL78/F22	R7F122FBG	✓ (1 wire UART)	R7F122FBG.pr6	
RL78	RL78/F22	R7F122FGG	✓ (1 wire UART)	R7F122FGG.pr6	
RL78	RL78/F23	R7F123FBG	✓ (1 wire UART)	R5F123FBG.pr6	
RL78	RL78/F23	R7F123FGG	✓ (1 wire UART)	R5F123FGG.pr6	
RL78	RL78/F23	R7F123FLG	✓ (1 wire UART)	R5F123FLG.pr6	
RL78	RL78/F23	R7F123FMG	✓ (1 wire UART)	R5F123FMG.pr6	
RL78	RL78/F24	R7F124FBJ	✓ (1 wire UART)	R7F124FBJ.pr6	
RL78	RL78/F24	R7F124FGJ	✓ (1 wire UART)	R7F124FGJ.pr6	
RL78	RL78/F24	R7F124FLJ	✓ (1 wire UART)	R7F124FLJ.pr6	
RL78	RL78/F24	R7F124FMJ	✓ (1 wire UART)	R7F124FMJ.pr6	
RL78	RL78/F24	R7F124FPJ	✓ (1 wire UART)	R7F124FPJ.pr6	
RL78	RL78/F25	R7F125FGL	✓ (1 wire UART)	R7F125FGL.pr6	
RL78	RL78/F25	R7F125FLL	✓ (1 wire UART)	R7F125FLL.pr6	
RL78	RL78/F25	R7F125FML	✓ (1 wire UART)	R7F125FML.pr6	
RL78	RL78/F25	R7F125FPL	✓ (1 wire UART)	R7F125FPL.pr6	
RL78	RL78/G10	R5F10Y14	✓ (1 wire UART)	R5F10Y14.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/G10	R5F10Y16	✓ (1 wire UART)	R5F10Y16.pr5	
RL78	RL78/G10	R5F10Y17	✓ (1 wire UART)	R5F10Y17.pr5	
RL78	RL78/G10	R5F10Y44	✓ (1 wire UART)	R5F10Y44.pr5	
RL78	RL78/G10	R5F10Y46	✓ (1 wire UART)	R5F10Y46.pr5	
RL78	RL78/G10	R5F10Y47	✓ (1 wire UART)	R5F10Y47.pr5	
RL78	RL78/G11	R5F1051A	✓ (1 wire UART)	R5F1051A.pr5	
RL78	RL78/G11	R5F1054A	✓ (1 wire UART)	R5F1054A.pr5	
RL78	RL78/G11	R5F1056A	✓ (1 wire UART)	R5F1056A.pr5	
RL78	RL78/G11	R5F1057A	✓ (1 wire UART)	R5F1057A.pr5	
RL78	RL78/G11	R5F1058A	✓ (1 wire UART)	R5F1058A.pr5	
RL78	RL78/G12	R5F10266	✓ (1 wire UART)	R5F10266.pr5	
RL78	RL78/G12	R5F10267	✓ (1 wire UART)	R5F10267.pr5	
RL78	RL78/G12	R5F10268	✓ (1 wire UART)	R5F10268.pr5	
RL78	RL78/G12	R5F10269	✓ (1 wire UART)	R5F10269.pr5	
RL78	RL78/G12	R5F1026A	✓ (1 wire UART)	R5F1026A.pr5	
RL78	RL78/G12	R5F10277	✓ (1 wire UART)	R5F10277.pr5	
RL78	RL78/G12	R5F10278	✓ (1 wire UART)	R5F10278.pr5	
RL78	RL78/G12	R5F10279	✓ (1 wire UART)	R5F10279.pr5	
RL78	RL78/G12	R5F1027A	✓ (1 wire UART)	R5F1027A.pr5	
RL78	RL78/G12	R5F102A7	✓ (1 wire UART)	R5F102A7.pr5	
RL78	RL78/G12	R5F102A8	✓ (1 wire UART)	R5F102A8.pr5	
RL78	RL78/G12	R5F102A9	✓ (1 wire UART)	R5F102A9.pr5	
RL78	RL78/G12	R5F102AA	✓ (1 wire UART)	R5F102AA.pr5	
RL78	RL78/G12	R5F10366	✓ (1 wire UART)	R5F10366.pr5	
RL78	RL78/G12	R5F10367	✓ (1 wire UART)	R5F10367.pr5	
RL78	RL78/G12	R5F10368	✓ (1 wire UART)	R5F10368.pr5	
RL78	RL78/G12	R5F10369	✓ (1 wire UART)	R5F10369.pr5	
RL78	RL78/G12	R5F1036A	✓ (1 wire UART)	R5F1036A.pr5	
RL78	RL78/G12	R5F10377	✓ (1 wire UART)	R5F10377.pr5	
RL78	RL78/G12	R5F10378	✓ (1 wire UART)	R5F10378.pr5	
RL78	RL78/G12	R5F10379	✓ (1 wire UART)	R5F10379.pr5	
RL78	RL78/G12	R5F1037A	✓ (1 wire UART)	R5F1037A.pr5	
RL78	RL78/G12	R5F103A7	✓ (1 wire UART)	R5F103A7.pr5	
RL78	RL78/G12	R5F103A8	✓ (1 wire UART)	R5F103A8.pr5	
RL78	RL78/G12	R5F103A9	✓ (1 wire UART)	R5F103A9.pr5	
RL78	RL78/G12	R5F103AA	✓ (1 wire UART)	R5F103AA.pr5	
RL78	RL78/G13	R5F1006A	✓ (1 wire UART)	R5F1006A.pr5	
RL78	RL78/G13	R5F1006C	✓ (1 wire UART)	R5F1006C.pr5	
RL78	RL78/G13	R5F1006D	✓ (1 wire UART)	R5F1006D.pr5	
RL78	RL78/G13	R5F1006E	✓ (1 wire UART)	R5F1006E.pr5	
RL78	RL78/G13	R5F1007A	✓ (1 wire UART)	R5F1007A.pr5	
RL78	RL78/G13	R5F1007C	✓ (1 wire UART)	R5F1007C.pr5	
RL78	RL78/G13	R5F1007D	✓ (1 wire UART)	R5F1007D.pr5	
RL78	RL78/G13	R5F1007E	✓ (1 wire UART)	R5F1007E.pr5	
RL78	RL78/G13	R5F1008A	✓ (1 wire UART)	R5F1008A.pr5	
RL78	RL78/G13	R5F1008C	✓ (1 wire UART)	R5F1008C.pr5	
RL78	RL78/G13	R5F1008D	✓ (1 wire UART)	R5F1008D.pr5	
RL78	RL78/G13	R5F1008E	✓ (1 wire UART)	R5F1008E.pr5	
RL78	RL78/G13	R5F100AA	✓ (1 wire UART)	R5F100AA.pr5	
RL78	RL78/G13	R5F100AC	✓ (1 wire UART)	R5F100AC.pr5	
RL78	RL78/G13	R5F100AD	✓ (1 wire UART)	R5F100AD.pr5	
RL78	RL78/G13	R5F100AE	✓ (1 wire UART)	R5F100AE.pr5	
RL78	RL78/G13	R5F100AF	✓ (1 wire UART)	R5F100AF.pr5	
RL78	RL78/G13	R5F100AG	✓ (1 wire UART)	R5F100AG.pr5	
RL78	RL78/G13	R5F100BA	✓ (1 wire UART)	R5F100BA.pr5	
RL78	RL78/G13	R5F100BC	✓ (1 wire UART)	R5F100BC.pr5	
RL78	RL78/G13	R5F100BD	✓ (1 wire UART)	R5F100BD.pr5	
RL78	RL78/G13	R5F100BE	✓ (1 wire UART)	R5F100BE.pr5	
RL78	RL78/G13	R5F100BF	✓ (1 wire UART)	R5F100BF.pr5	
RL78	RL78/G13	R5F100BG	✓ (1 wire UART)	R5F100BG.pr5	
RL78	RL78/G13	R5F100CA	✓ (1 wire UART)	R5F100CA.pr5	
RL78	RL78/G13	R5F100CC	✓ (1 wire UART)	R5F100CC.pr5	
RL78	RL78/G13	R5F100CD	✓ (1 wire UART)	R5F100CD.pr5	
RL78	RL78/G13	R5F100CE	✓ (1 wire UART)	R5F100CE.pr5	
RL78	RL78/G13	R5F100CF	✓ (1 wire UART)	R5F100CF.pr5	
RL78	RL78/G13	R5F100CG	✓ (1 wire UART)	R5F100CG.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/G13	R5F100EA	✓ (1 wire UART)	R5F100EA.pr5	
RL78	RL78/G13	R5F100EC	✓ (1 wire UART)	R5F100EC.pr5	
RL78	RL78/G13	R5F100ED	✓ (1 wire UART)	R5F100ED.pr5	
RL78	RL78/G13	R5F100EE	✓ (1 wire UART)	R5F100EE.pr5	
RL78	RL78/G13	R5F100EF	✓ (1 wire UART)	R5F100EF.pr5	
RL78	RL78/G13	R5F100EG	✓ (1 wire UART)	R5F100EG.pr5	
RL78	RL78/G13	R5F100EH	✓ (1 wire UART)	R5F100EH.pr5	
RL78	RL78/G13	R5F100FA	✓ (1 wire UART)	R5F100FA.pr5	
RL78	RL78/G13	R5F100FC	✓ (1 wire UART)	R5F100FC.pr5	
RL78	RL78/G13	R5F100FD	✓ (1 wire UART)	R5F100FD.pr5	
RL78	RL78/G13	R5F100FE	✓ (1 wire UART)	R5F100FE.pr5	
RL78	RL78/G13	R5F100FF	✓ (1 wire UART)	R5F100FF.pr5	
RL78	RL78/G13	R5F100FG	✓ (1 wire UART)	R5F100FG.pr5	
RL78	RL78/G13	R5F100FH	✓ (1 wire UART)	R5F100FH.pr5	
RL78	RL78/G13	R5F100FJ	✓ (1 wire UART)	R5F100FJ.pr5	
RL78	RL78/G13	R5F100FK	✓ (1 wire UART)	R5F100FK.pr5	
RL78	RL78/G13	R5F100FL	✓ (1 wire UART)	R5F100FL.pr5	
RL78	RL78/G13	R5F100GA	✓ (1 wire UART)	R5F100GA.pr5	
RL78	RL78/G13	R5F100GC	✓ (1 wire UART)	R5F100GC.pr5	
RL78	RL78/G13	R5F100GD	✓ (1 wire UART)	R5F100GD.pr5	
RL78	RL78/G13	R5F100GE	✓ (1 wire UART)	R5F100GE.pr5	
RL78	RL78/G13	R5F100GF	✓ (1 wire UART)	R5F100GF.pr5	
RL78	RL78/G13	R5F100GG	✓ (1 wire UART)	R5F100GG.pr5	
RL78	RL78/G13	R5F100GH	✓ (1 wire UART)	R5F100GH.pr5	
RL78	RL78/G13	R5F100GJ	✓ (1 wire UART)	R5F100GJ.pr5	
RL78	RL78/G13	R5F100GK	✓ (1 wire UART)	R5F100GK.pr5	
RL78	RL78/G13	R5F100GL	✓ (1 wire UART)	R5F100GL.pr5	
RL78	RL78/G13	R5F100JC	✓ (1 wire UART)	R5F100JC.pr5	
RL78	RL78/G13	R5F100JD	✓ (1 wire UART)	R5F100JD.pr5	
RL78	RL78/G13	R5F100JE	✓ (1 wire UART)	R5F100JE.pr5	
RL78	RL78/G13	R5F100JF	✓ (1 wire UART)	R5F100JF.pr5	
RL78	RL78/G13	R5F100JG	✓ (1 wire UART)	R5F100JG.pr5	
RL78	RL78/G13	R5F100JH	✓ (1 wire UART)	R5F100JH.pr5	
RL78	RL78/G13	R5F100JJ	✓ (1 wire UART)	R5F100JJ.pr5	
RL78	RL78/G13	R5F100JK	✓ (1 wire UART)	R5F100JK.pr5	
RL78	RL78/G13	R5F100JL	✓ (1 wire UART)	R5F100JL.pr5	
RL78	RL78/G13	R5F100LC	✓ (1 wire UART)	R5F100LC.pr5	
RL78	RL78/G13	R5F100LD	✓ (1 wire UART)	R5F100LD.pr5	
RL78	RL78/G13	R5F100LE	✓ (1 wire UART)	R5F100LE.pr5	
RL78	RL78/G13	R5F100LF	✓ (1 wire UART)	R5F100LF.pr5	
RL78	RL78/G13	R5F100LG	✓ (1 wire UART)	R5F100LG.pr5	
RL78	RL78/G13	R5F100LH	✓ (1 wire UART)	R5F100LH.pr5	
RL78	RL78/G13	R5F100LJ	✓ (1 wire UART)	R5F100LJ.pr5	
RL78	RL78/G13	R5F100LK	✓ (1 wire UART)	R5F100LK.pr5	
RL78	RL78/G13	R5F100LL	✓ (1 wire UART)	R5F100LL.pr5	
RL78	RL78/G13	R5F100MF	✓ (1 wire UART)	R5F100MF.pr5	
RL78	RL78/G13	R5F100MG	✓ (1 wire UART)	R5F100MG.pr5	
RL78	RL78/G13	R5F100MH	✓ (1 wire UART)	R5F100MH.pr5	
RL78	RL78/G13	R5F100MJ	✓ (1 wire UART)	R5F100MJ.pr5	
RL78	RL78/G13	R5F100MK	✓ (1 wire UART)	R5F100MK.pr5	
RL78	RL78/G13	R5F100ML	✓ (1 wire UART)	R5F100ML.pr5	
RL78	RL78/G13	R5F100PF	✓ (1 wire UART)	R5F100PF.pr5	
RL78	RL78/G13	R5F100PG	✓ (1 wire UART)	R5F100PG.pr5	
RL78	RL78/G13	R5F100PH	✓ (1 wire UART)	R5F100PH.pr5	
RL78	RL78/G13	R5F100PJ	✓ (1 wire UART)	R5F100PJ.pr5	
RL78	RL78/G13	R5F100PK	✓ (1 wire UART)	R5F100PK.pr5	
RL78	RL78/G13	R5F100PL	✓ (1 wire UART)	R5F100PL.pr5	
RL78	RL78/G13	R5F100SH	✓ (1 wire UART)	R5F100SH.pr5	
RL78	RL78/G13	R5F100SJ	✓ (1 wire UART)	R5F100SJ.pr5	
RL78	RL78/G13	R5F100SK	✓ (1 wire UART)	R5F100SK.pr5	
RL78	RL78/G13	R5F100SL	✓ (1 wire UART)	R5F100SL.pr5	
RL78	RL78/G13	R5F1016A	✓ (1 wire UART)	R5F1016A.pr5	
RL78	RL78/G13	R5F1016C	✓ (1 wire UART)	R5F1016C.pr5	
RL78	RL78/G13	R5F1016D	✓ (1 wire UART)	R5F1016D.pr5	
RL78	RL78/G13	R5F1016E	✓ (1 wire UART)	R5F1016E.pr5	
RL78	RL78/G13	R5F1017A	✓ (1 wire UART)	R5F1017A.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/G13	R5F1017C	✓ (1 wire UART)	R5F1017C.pr5	
RL78	RL78/G13	R5F1017D	✓ (1 wire UART)	R5F1017D.pr5	
RL78	RL78/G13	R5F1017E	✓ (1 wire UART)	R5F1017E.pr5	
RL78	RL78/G13	R5F1018A	✓ (1 wire UART)	R5F1018A.pr5	
RL78	RL78/G13	R5F1018C	✓ (1 wire UART)	R5F1018C.pr5	
RL78	RL78/G13	R5F1018D	✓ (1 wire UART)	R5F1018D.pr5	
RL78	RL78/G13	R5F1018E	✓ (1 wire UART)	R5F1018E.pr5	
RL78	RL78/G13	R5F101AA	✓ (1 wire UART)	R5F101AA.pr5	
RL78	RL78/G13	R5F101AC	✓ (1 wire UART)	R5F101AC.pr5	
RL78	RL78/G13	R5F101AD	✓ (1 wire UART)	R5F101AD.pr5	
RL78	RL78/G13	R5F101AE	✓ (1 wire UART)	R5F101AE.pr5	
RL78	RL78/G13	R5F101AF	✓ (1 wire UART)	R5F101AF.pr5	
RL78	RL78/G13	R5F101AG	✓ (1 wire UART)	R5F101AG.pr5	
RL78	RL78/G13	R5F101BA	✓ (1 wire UART)	R5F101BA.pr5	
RL78	RL78/G13	R5F101BC	✓ (1 wire UART)	R5F101BC.pr5	
RL78	RL78/G13	R5F101BD	✓ (1 wire UART)	R5F101BD.pr5	
RL78	RL78/G13	R5F101BE	✓ (1 wire UART)	R5F101BE.pr5	
RL78	RL78/G13	R5F101BF	✓ (1 wire UART)	R5F101BF.pr5	
RL78	RL78/G13	R5F101BG	✓ (1 wire UART)	R5F101BG.pr5	
RL78	RL78/G13	R5F101CA	✓ (1 wire UART)	R5F101CA.pr5	
RL78	RL78/G13	R5F101CC	✓ (1 wire UART)	R5F101CC.pr5	
RL78	RL78/G13	R5F101CD	✓ (1 wire UART)	R5F101CD.pr5	
RL78	RL78/G13	R5F101CE	✓ (1 wire UART)	R5F101CE.pr5	
RL78	RL78/G13	R5F101CF	✓ (1 wire UART)	R5F101CF.pr5	
RL78	RL78/G13	R5F101CG	✓ (1 wire UART)	R5F101CG.pr5	
RL78	RL78/G13	R5F101EA	✓ (1 wire UART)	R5F101EA.pr5	
RL78	RL78/G13	R5F101EC	✓ (1 wire UART)	R5F101EC.pr5	
RL78	RL78/G13	R5F101ED	✓ (1 wire UART)	R5F101ED.pr5	
RL78	RL78/G13	R5F101EE	✓ (1 wire UART)	R5F101EE.pr5	
RL78	RL78/G13	R5F101EF	✓ (1 wire UART)	R5F101EF.pr5	
RL78	RL78/G13	R5F101EG	✓ (1 wire UART)	R5F101EG.pr5	
RL78	RL78/G13	R5F101EH	✓ (1 wire UART)	R5F101EH.pr5	
RL78	RL78/G13	R5F101FA	✓ (1 wire UART)	R5F101FA.pr5	
RL78	RL78/G13	R5F101FC	✓ (1 wire UART)	R5F101FC.pr5	
RL78	RL78/G13	R5F101FD	✓ (1 wire UART)	R5F101FD.pr5	
RL78	RL78/G13	R5F101FE	✓ (1 wire UART)	R5F101FE.pr5	
RL78	RL78/G13	R5F101FF	✓ (1 wire UART)	R5F101FF.pr5	
RL78	RL78/G13	R5F101FG	✓ (1 wire UART)	R5F101FG.pr5	
RL78	RL78/G13	R5F101FH	✓ (1 wire UART)	R5F101FH.pr5	
RL78	RL78/G13	R5F101FJ	✓ (1 wire UART)	R5F101FJ.pr5	
RL78	RL78/G13	R5F101FK	✓ (1 wire UART)	R5F101FK.pr5	
RL78	RL78/G13	R5F101FL	✓ (1 wire UART)	R5F101FL.pr5	
RL78	RL78/G13	R5F101GA	✓ (1 wire UART)	R5F101GA.pr5	
RL78	RL78/G13	R5F101GC	✓ (1 wire UART)	R5F101GC.pr5	
RL78	RL78/G13	R5F101GD	✓ (1 wire UART)	R5F101GD.pr5	
RL78	RL78/G13	R5F101GE	✓ (1 wire UART)	R5F101GE.pr5	
RL78	RL78/G13	R5F101GF	✓ (1 wire UART)	R5F101GF.pr5	
RL78	RL78/G13	R5F101GG	✓ (1 wire UART)	R5F101GG.pr5	
RL78	RL78/G13	R5F101GH	✓ (1 wire UART)	R5F101GH.pr5	
RL78	RL78/G13	R5F101GJ	✓ (1 wire UART)	R5F101GJ.pr5	
RL78	RL78/G13	R5F101GK	✓ (1 wire UART)	R5F101GK.pr5	
RL78	RL78/G13	R5F101GL	✓ (1 wire UART)	R5F101GL.pr5	
RL78	RL78/G13	R5F101JC	✓ (1 wire UART)	R5F101JC.pr5	
RL78	RL78/G13	R5F101JD	✓ (1 wire UART)	R5F101JD.pr5	
RL78	RL78/G13	R5F101JE	✓ (1 wire UART)	R5F101JE.pr5	
RL78	RL78/G13	R5F101JF	✓ (1 wire UART)	R5F101JF.pr5	
RL78	RL78/G13	R5F101JG	✓ (1 wire UART)	R5F101JG.pr5	
RL78	RL78/G13	R5F101JH	✓ (1 wire UART)	R5F101JH.pr5	
RL78	RL78/G13	R5F101JJ	✓ (1 wire UART)	R5F101JJ.pr5	
RL78	RL78/G13	R5F101JK	✓ (1 wire UART)	R5F101JK.pr5	
RL78	RL78/G13	R5F101JL	✓ (1 wire UART)	R5F101JL.pr5	
RL78	RL78/G13	R5F101LC	✓ (1 wire UART)	R5F101LC.pr5	
RL78	RL78/G13	R5F101LD	✓ (1 wire UART)	R5F101LD.pr5	
RL78	RL78/G13	R5F101LE	✓ (1 wire UART)	R5F101LE.pr5	
RL78	RL78/G13	R5F101LF	✓ (1 wire UART)	R5F101LF.pr5	
RL78	RL78/G13	R5F101LG	✓ (1 wire UART)	R5F101LG.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/G13	R5F101LH	✓ (1 wire UART)	R5F101LH.pr5	
RL78	RL78/G13	R5F101LJ	✓ (1 wire UART)	R5F101LJ.pr5	
RL78	RL78/G13	R5F101LK	✓ (1 wire UART)	R5F101LK.pr5	
RL78	RL78/G13	R5F101LL	✓ (1 wire UART)	R5F101LL.pr5	
RL78	RL78/G13	R5F101MF	✓ (1 wire UART)	R5F101MF.pr5	
RL78	RL78/G13	R5F101MG	✓ (1 wire UART)	R5F101MG.pr5	
RL78	RL78/G13	R5F101MH	✓ (1 wire UART)	R5F101MH.pr5	
RL78	RL78/G13	R5F101MJ	✓ (1 wire UART)	R5F101MJ.pr5	
RL78	RL78/G13	R5F101MK	✓ (1 wire UART)	R5F101MK.pr5	
RL78	RL78/G13	R5F101ML	✓ (1 wire UART)	R5F101ML.pr5	
RL78	RL78/G13	R5F101PF	✓ (1 wire UART)	R5F101PF.pr5	
RL78	RL78/G13	R5F101PG	✓ (1 wire UART)	R5F101PG.pr5	
RL78	RL78/G13	R5F101PH	✓ (1 wire UART)	R5F101PH.pr5	
RL78	RL78/G13	R5F101PJ	✓ (1 wire UART)	R5F101PJ.pr5	
RL78	RL78/G13	R5F101PK	✓ (1 wire UART)	R5F101PK.pr5	
RL78	RL78/G13	R5F101PL	✓ (1 wire UART)	R5F101PL.pr5	
RL78	RL78/G13	R5F101SH	✓ (1 wire UART)	R5F101SH.pr5	
RL78	RL78/G13	R5F101SJ	✓ (1 wire UART)	R5F101SJ.pr5	
RL78	RL78/G13	R5F101SK	✓ (1 wire UART)	R5F101SK.pr5	
RL78	RL78/G13	R5F101SL	✓ (1 wire UART)	R5F101SL.pr5	
RL78	RL78/G13A	R5F140FK	✓ (1 wire UART)	R5F140FK.pr5	
RL78	RL78/G13A	R5F140FL	✓ (1 wire UART)	R5F140FL.pr5	
RL78	RL78/G13A	R5F140GK	✓ (1 wire UART)	R5F140GK.pr5	
RL78	RL78/G13A	R5F140GL	✓ (1 wire UART)	R5F140GL.pr5	
RL78	RL78/G13A	R5F140LK	✓ (1 wire UART)	R5F140LK.pr5	
RL78	RL78/G13A	R5F140LL	✓ (1 wire UART)	R5F140LL.pr5	
RL78	RL78/G13A	R5F140PK	✓ (1 wire UART)	R5F140PK.pr5	
RL78	RL78/G13A	R5F140PL	✓ (1 wire UART)	R5F140PL.pr5	
RL78	RL78/G14	R5F104AA	✓ (1 wire UART)	R5F104AA.pr5	
RL78	RL78/G14	R5F104AC	✓ (1 wire UART)	R5F104AC.pr5	
RL78	RL78/G14	R5F104AD	✓ (1 wire UART)	R5F104AD.pr5	
RL78	RL78/G14	R5F104AE	✓ (1 wire UART)	R5F104AE.pr5	
RL78	RL78/G14	R5F104AF	✓ (1 wire UART)	R5F104AF.pr5	
RL78	RL78/G14	R5F104AG	✓ (1 wire UART)	R5F104AG.pr5	
RL78	RL78/G14	R5F104BA	✓ (1 wire UART)	R5F104BA.pr5	
RL78	RL78/G14	R5F104BC	✓ (1 wire UART)	R5F104BC.pr5	
RL78	RL78/G14	R5F104BD	✓ (1 wire UART)	R5F104BD.pr5	
RL78	RL78/G14	R5F104BE	✓ (1 wire UART)	R5F104BE.pr5	
RL78	RL78/G14	R5F104BF	✓ (1 wire UART)	R5F104BF.pr5	
RL78	RL78/G14	R5F104BG	✓ (1 wire UART)	R5F104BG.pr5	
RL78	RL78/G14	R5F104CA	✓ (1 wire UART)	R5F104CA.pr5	
RL78	RL78/G14	R5F104CC	✓ (1 wire UART)	R5F104CC.pr5	
RL78	RL78/G14	R5F104CD	✓ (1 wire UART)	R5F104CD.pr5	
RL78	RL78/G14	R5F104CE	✓ (1 wire UART)	R5F104CE.pr5	
RL78	RL78/G14	R5F104CF	✓ (1 wire UART)	R5F104CF.pr5	
RL78	RL78/G14	R5F104CG	✓ (1 wire UART)	R5F104CG.pr5	
RL78	RL78/G14	R5F104EA	✓ (1 wire UART)	R5F104EA.pr5	
RL78	RL78/G14	R5F104EC	✓ (1 wire UART)	R5F104EC.pr5	
RL78	RL78/G14	R5F104ED	✓ (1 wire UART)	R5F104ED.pr5	
RL78	RL78/G14	R5F104EE	✓ (1 wire UART)	R5F104EE.pr5	
RL78	RL78/G14	R5F104EF	✓ (1 wire UART)	R5F104EF.pr5	
RL78	RL78/G14	R5F104EG	✓ (1 wire UART)	R5F104EG.pr5	
RL78	RL78/G14	R5F104EH	✓ (1 wire UART)	R5F104EH.pr5	
RL78	RL78/G14	R5F104FA	✓ (1 wire UART)	R5F104FA.pr5	
RL78	RL78/G14	R5F104FC	✓ (1 wire UART)	R5F104FC.pr5	
RL78	RL78/G14	R5F104FD	✓ (1 wire UART)	R5F104FD.pr5	
RL78	RL78/G14	R5F104FE	✓ (1 wire UART)	R5F104FE.pr5	
RL78	RL78/G14	R5F104FF	✓ (1 wire UART)	R5F104FF.pr5	
RL78	RL78/G14	R5F104FG	✓ (1 wire UART)	R5F104FG.pr5	
RL78	RL78/G14	R5F104FH	✓ (1 wire UART)	R5F104FH.pr5	
RL78	RL78/G14	R5F104FJ	✓ (1 wire UART)	R5F104FJ.pr5	
RL78	RL78/G14	R5F104GA	✓ (1 wire UART)	R5F104GA.pr5	
RL78	RL78/G14	R5F104GC	✓ (1 wire UART)	R5F104GC.pr5	
RL78	RL78/G14	R5F104GD	✓ (1 wire UART)	R5F104GD.pr5	
RL78	RL78/G14	R5F104GE	✓ (1 wire UART)	R5F104GE.pr5	
RL78	RL78/G14	R5F104GF	✓ (1 wire UART)	R5F104GF.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/G14	R5F104GG	✓ (1 wire UART)	R5F104GG.pr5	
RL78	RL78/G14	R5F104GH	✓ (1 wire UART)	R5F104GH.pr5	
RL78	RL78/G14	R5F104GJ	✓ (1 wire UART)	R5F104GJ.pr5	
RL78	RL78/G14	R5F104GK	✓ (1 wire UART)	R5F104GK.pr5	
RL78	RL78/G14	R5F104GL	✓ (1 wire UART)	R5F104GL.pr5	
RL78	RL78/G14	R5F104JC	✓ (1 wire UART)	R5F104JC.pr5	
RL78	RL78/G14	R5F104JD	✓ (1 wire UART)	R5F104JD.pr5	
RL78	RL78/G14	R5F104JE	✓ (1 wire UART)	R5F104JE.pr5	
RL78	RL78/G14	R5F104JF	✓ (1 wire UART)	R5F104JF.pr5	
RL78	RL78/G14	R5F104JG	✓ (1 wire UART)	R5F104JG.pr5	
RL78	RL78/G14	R5F104JH	✓ (1 wire UART)	R5F104JH.pr5	
RL78	RL78/G14	R5F104JJ	✓ (1 wire UART)	R5F104JJ.pr5	
RL78	RL78/G14	R5F104LC	✓ (1 wire UART)	R5F104LC.pr5	
RL78	RL78/G14	R5F104LD	✓ (1 wire UART)	R5F104LD.pr5	
RL78	RL78/G14	R5F104LE	✓ (1 wire UART)	R5F104LE.pr5	
RL78	RL78/G14	R5F104LF	✓ (1 wire UART)	R5F104LF.pr5	
RL78	RL78/G14	R5F104LG	✓ (1 wire UART)	R5F104LG.pr5	
RL78	RL78/G14	R5F104LH	✓ (1 wire UART)	R5F104LH.pr5	
RL78	RL78/G14	R5F104LJ	✓ (1 wire UART)	R5F104LJ.pr5	
RL78	RL78/G14	R5F104LK	✓ (1 wire UART)	R5F104LK.pr5	
RL78	RL78/G14	R5F104LL	✓ (1 wire UART)	R5F104LL.pr5	
RL78	RL78/G14	R5F104MF	✓ (1 wire UART)	R5F104MF.pr5	
RL78	RL78/G14	R5F104MG	✓ (1 wire UART)	R5F104MG.pr5	
RL78	RL78/G14	R5F104MH	✓ (1 wire UART)	R5F104MH.pr5	
RL78	RL78/G14	R5F104MJ	✓ (1 wire UART)	R5F104MJ.pr5	
RL78	RL78/G14	R5F104MK	✓ (1 wire UART)	R5F104MK.pr5	
RL78	RL78/G14	R5F104ML	✓ (1 wire UART)	R5F104ML.pr5	
RL78	RL78/G14	R5F104PF	✓ (1 wire UART)	R5F104PF.pr5	
RL78	RL78/G14	R5F104PG	✓ (1 wire UART)	R5F104PG.pr5	
RL78	RL78/G14	R5F104PH	✓ (1 wire UART)	R5F104PH.pr5	
RL78	RL78/G14	R5F104PJ	✓ (1 wire UART)	R5F104PJ.pr5	
RL78	RL78/G14	R5F104PK	✓ (1 wire UART)	R5F104PK.pr5	
RL78	RL78/G14	R5F104PL	✓ (1 wire UART)	R5F104PL.pr5	
RL78	RL78/G15	R5F12007	✓ (1 wire UART)	R5F120x7.pr6	
RL78	RL78/G15	R5F12008	✓ (1 wire UART)	R5F120x8.pr6	
RL78	RL78/G15	R5F12017	✓ (1 wire UART)	R5F120x7.pr6	
RL78	RL78/G15	R5F12018	✓ (1 wire UART)	R5F120x8.pr6	
RL78	RL78/G15	R5F12047	✓ (1 wire UART)	R5F120x7.pr6	
RL78	RL78/G15	R5F12048	✓ (1 wire UART)	R5F120x8.pr6	
RL78	RL78/G15	R5F12067	✓ (1 wire UART)	R5F120x7.pr6	
RL78	RL78/G15	R5F12068	✓ (1 wire UART)	R5F120x8.pr6	
RL78	RL78/G16	R5F1211A	✓ (1 wire UART)	R5F121xA.pr6	
RL78	RL78/G16	R5F1211C	✓ (1 wire UART)	R5F121xC.pr6	
RL78	RL78/G16	R5F1214A	✓ (1 wire UART)	R5F121xA.pr6	
RL78	RL78/G16	R5F1214C	✓ (1 wire UART)	R5F121xC.pr6	
RL78	RL78/G16	R5F1216A	✓ (1 wire UART)	R5F121xA.pr6	
RL78	RL78/G16	R5F1216C	✓ (1 wire UART)	R5F121xC.pr6	
RL78	RL78/G16	R5F1217A	✓ (1 wire UART)	R5F121xA.pr6	
RL78	RL78/G16	R5F1217C	✓ (1 wire UART)	R5F121xC.pr6	
RL78	RL78/G16	R5F121BA	✓ (1 wire UART)	R5F121xA.pr6	
RL78	RL78/G16	R5F121BC	✓ (1 wire UART)	R5F121xC.pr6	
RL78	RL78/G1A	R5F10E8A	✓ (1 wire UART)	R5F10E8A.pr5	
RL78	RL78/G1A	R5F10E8C	✓ (1 wire UART)	R5F10E8C.pr5	
RL78	RL78/G1A	R5F10E8D	✓ (1 wire UART)	R5F10E8D.pr5	
RL78	RL78/G1A	R5F10E8E	✓ (1 wire UART)	R5F10E8E.pr5	
RL78	RL78/G1A	R5F10E8A	✓ (1 wire UART)	R5F10E8A.pr5	
RL78	RL78/G1A	R5F10EBC	✓ (1 wire UART)	R5F10EBC.pr5	
RL78	RL78/G1A	R5F10EBD	✓ (1 wire UART)	R5F10EBD.pr5	
RL78	RL78/G1A	R5F10EBE	✓ (1 wire UART)	R5F10EBE.pr5	
RL78	RL78/G1A	R5F10EGA	✓ (1 wire UART)	R5F10EGA.pr5	
RL78	RL78/G1A	R5F10EGC	✓ (1 wire UART)	R5F10EGC.pr5	
RL78	RL78/G1A	R5F10EGD	✓ (1 wire UART)	R5F10EGD.pr5	
RL78	RL78/G1A	R5F10EGE	✓ (1 wire UART)	R5F10EGE.pr5	
RL78	RL78/G1A	R5F10ELC	✓ (1 wire UART)	R5F10ELC.pr5	
RL78	RL78/G1A	R5F10ELD	✓ (1 wire UART)	R5F10ELD.pr5	
RL78	RL78/G1A	R5F10ELE	✓ (1 wire UART)	R5F10ELE.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/G1C	R5F10JBC	✓ (1 wire UART)	R5F10JBC.pr5	
RL78	RL78/G1C	R5F10JGC	✓ (1 wire UART)	R5F10JGC.pr5	
RL78	RL78/G1C	R5F10KBC	✓ (1 wire UART)	R5F10KBC.pr5	
RL78	RL78/G1C	R5F10KGC	✓ (1 wire UART)	R5F10KGC.pr5	
RL78	RL78/G1D	R5F11AGG	✓ (1 wire UART)	R5F11AGG.pr5	
RL78	RL78/G1D	R5F11AGH	✓ (1 wire UART)	R5F11AGH.pr5	
RL78	RL78/G1D	R5F11AGJ	✓ (1 wire UART)	R5F11AGJ.pr5	
RL78	RL78/G1E	R5F10FLC	✓ (1 wire UART)	R5F10FLC.pr5	
RL78	RL78/G1E	R5F10FLD	✓ (1 wire UART)	R5F10FLD.pr5	
RL78	RL78/G1E	R5F10FLE	✓ (1 wire UART)	R5F10FLE.pr5	
RL78	RL78/G1E	R5F10FMC	✓ (1 wire UART)	R5F10FMC.pr5	
RL78	RL78/G1E	R5F10FMD	✓ (1 wire UART)	R5F10FMD.pr5	
RL78	RL78/G1E	R5F10FME	✓ (1 wire UART)	R5F10FME.pr5	
RL78	RL78/G1F	R5F11B7C	✓ (1 wire UART)	R5F11B7C.pr5	
RL78	RL78/G1F	R5F11B7E	✓ (1 wire UART)	R5F11B7E.pr5	
RL78	RL78/G1F	R5F11BBC	✓ (1 wire UART)	R5F11BBC.pr5	
RL78	RL78/G1F	R5F11BBE	✓ (1 wire UART)	R5F11BBE.pr5	
RL78	RL78/G1F	R5F11BCC	✓ (1 wire UART)	R5F11BCC.pr5	
RL78	RL78/G1F	R5F11BCE	✓ (1 wire UART)	R5F11BCE.pr5	
RL78	RL78/G1F	R5F11BGC	✓ (1 wire UART)	R5F11BGC.pr5	
RL78	RL78/G1F	R5F11BGE	✓ (1 wire UART)	R5F11BGE.pr5	
RL78	RL78/G1F	R5F11BLC	✓ (1 wire UART)	R5F11BLC.pr5	
RL78	RL78/G1F	R5F11BLE	✓ (1 wire UART)	R5F11BLE.pr5	
RL78	RL78/G1G	R5F11EA8	✓ (1 wire UART)	R5F11EA8.pr5	
RL78	RL78/G1G	R5F11EAA	✓ (1 wire UART)	R5F11EAA.pr5	
RL78	RL78/G1G	R5F11EB8	✓ (1 wire UART)	R5F11EB8.pr5	
RL78	RL78/G1G	R5F11EBA	✓ (1 wire UART)	R5F11EBA.pr5	
RL78	RL78/G1G	R5F11EF8	✓ (1 wire UART)	R5F11EF8.pr5	
RL78	RL78/G1G	R5F11EFA	✓ (1 wire UART)	R5F11EFA.pr5	
RL78	RL78/G1H	R5F11FLJ	✓ (1 wire UART)	R5F11FLJ.pr5	
RL78	RL78/G1H	R5F11FLK	✓ (1 wire UART)	R5F11FLK.pr5	
RL78	RL78/G1H	R5F11FLL	✓ (1 wire UART)	R5F11FLL.pr5	
RL78	-	R5F11VBG	✓ (1 wire UART)	R5F11VBG.pr5	
RL78	-	R5F11VLG	✓ (1 wire UART)	R5F11VLG.pr5	
RL78	RL78/G1M	R5F11W67	✓ (1 wire UART)	R5F11W67.pr5	
RL78	RL78/G1M	R5F11W68	✓ (1 wire UART)	R5F11W68.pr5	
RL78	RL78/G1N	R5F11Y67	✓ (1 wire UART)	R5F11Y67.pr5	
RL78	RL78/G1N	R5F11Y68	✓ (1 wire UART)	R5F11Y68.pr5	
RL78	RL78/G1P	R5F11Z7A	✓ (1 wire UART)	R5F11Z7A.pr5	
RL78	RL78/G1P	R5F11ZBA	✓ (1 wire UART)	R5F11ZBA.pr5	
RL78	RL78/G22	R7F102G4C	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102G4E	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102G6C	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102G6E	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102G7C	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102G7E	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102G8C	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102G8E	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102GAC	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102GAE	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102GBC	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102GBE	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102GCC	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102GCE	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102GEC	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102GEE	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102GFC	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102GFE	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G22	R7F102GGC	✓ (1 wire UART)	R7F102GxC.pr6	
RL78	RL78/G22	R7F102GGE	✓ (1 wire UART)	R7F102GxE.pr6	
RL78	RL78/G23	R7F100GAF	✓ (1 wire UART)	R7F100GxF.pr6	
RL78	RL78/G23	R7F100GAG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GAH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GAJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GBF	✓ (1 wire UART)	R7F100GxF.pr6	
RL78	RL78/G23	R7F100GBG	✓ (1 wire UART)	R7F100GxG.pr6	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/G23	R7F100GBH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GBJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GCF	✓ (1 wire UART)	R7F100GxF.pr6	
RL78	RL78/G23	R7F100GCG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GCH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GCJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GEF	✓ (1 wire UART)	R7F100GxF.pr6	
RL78	RL78/G23	R7F100GEG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GEH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GEJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GFF	✓ (1 wire UART)	R7F100GxF.pr6	
RL78	RL78/G23	R7F100GFG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GFH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GFJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GFK	✓ (1 wire UART)	R7F100GxK.pr6	
RL78	RL78/G23	R7F100GFL	✓ (1 wire UART)	R7F100GxL.pr6	
RL78	RL78/G23	R7F100GFN	✓ (1 wire UART)	R7F100GxN.pr6	
RL78	RL78/G23	R7F100GGF	✓ (1 wire UART)	R7F100GxF.pr6	
RL78	RL78/G23	R7F100GGG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GGH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GGJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GGK	✓ (1 wire UART)	R7F100GxK.pr6	
RL78	RL78/G23	R7F100GGL	✓ (1 wire UART)	R7F100GxL.pr6	
RL78	RL78/G23	R7F100GGN	✓ (1 wire UART)	R7F100GxN.pr6	
RL78	RL78/G23	R7F100GJF	✓ (1 wire UART)	R7F100GxF.pr6	
RL78	RL78/G23	R7F100GJG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GJH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GJJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GJK	✓ (1 wire UART)	R7F100GxK.pr6	
RL78	RL78/G23	R7F100GJL	✓ (1 wire UART)	R7F100GxL.pr6	
RL78	RL78/G23	R7F100GJN	✓ (1 wire UART)	R7F100GxN.pr6	
RL78	RL78/G23	R7F100GLF	✓ (1 wire UART)	R7F100GxF.pr6	
RL78	RL78/G23	R7F100GLG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GLH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GLJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GLK	✓ (1 wire UART)	R7F100GxK.pr6	
RL78	RL78/G23	R7F100GLL	✓ (1 wire UART)	R7F100GxL.pr6	
RL78	RL78/G23	R7F100GLN	✓ (1 wire UART)	R7F100GxN.pr6	
RL78	RL78/G23	R7F100GMG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GMH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GMJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GMK	✓ (1 wire UART)	R7F100GxK.pr6	
RL78	RL78/G23	R7F100GML	✓ (1 wire UART)	R7F100GxL.pr6	
RL78	RL78/G23	R7F100GMN	✓ (1 wire UART)	R7F100GxN.pr6	
RL78	RL78/G23	R7F100GPG	✓ (1 wire UART)	R7F100GxG.pr6	
RL78	RL78/G23	R7F100GPH	✓ (1 wire UART)	R7F100GxH.pr6	
RL78	RL78/G23	R7F100GPJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GPK	✓ (1 wire UART)	R7F100GxK.pr6	
RL78	RL78/G23	R7F100GPL	✓ (1 wire UART)	R7F100GxL.pr6	
RL78	RL78/G23	R7F100GPN	✓ (1 wire UART)	R7F100GxN.pr6	
RL78	RL78/G23	R7F100GSJ	✓ (1 wire UART)	R7F100GxJ.pr6	
RL78	RL78/G23	R7F100GSK	✓ (1 wire UART)	R7F100GxK.pr6	
RL78	RL78/G23	R7F100GSL	✓ (1 wire UART)	R7F100GxL.pr6	
RL78	RL78/G23	R7F100GSN	✓ (1 wire UART)	R7F100GxN.pr6	
RL78	RL78/G24	R7F101G6E	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101G6G	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/G24	R7F101G7E	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101G7G	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/G24	R7F101G8E	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101G8G	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/G24	R7F101GAE	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101GAG	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/G24	R7F101GBE	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101GBG	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/G24	R7F101GEE	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101GEG	✓ (1 wire UART)	R7F101GxG.pr6	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/G24	R7F101GFE	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101GFG	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/G24	R7F101GGE	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101GGG	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/G24	R7F101GJE	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101GJG	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/G24	R7F101GLE	✓ (1 wire UART)	R7F101GxE.pr6	
RL78	RL78/G24	R7F101GLG	✓ (1 wire UART)	R7F101GxG.pr6	
RL78	RL78/H1D	R5F11NGF	✓ (1 wire UART)	R5F11NGF.pr5	
RL78	RL78/H1D	R5F11NGG	✓ (1 wire UART)	R5F11NGG.pr5	
RL78	RL78/H1D	R5F11NLF	✓ (1 wire UART)	R5F11NLF.pr5	
RL78	RL78/H1D	R5F11NLG	✓ (1 wire UART)	R5F11NLG.pr5	
RL78	RL78/H1D	R5F11NME	✓ (1 wire UART)	R5F11NME.pr5	
RL78	RL78/H1D	R5F11NMF	✓ (1 wire UART)	R5F11NMF.pr5	
RL78	RL78/H1D	R5F11NMG	✓ (1 wire UART)	R5F11NMG.pr5	
RL78	RL78/H1D	R5F11PLF	✓ (1 wire UART)	R5F11PLF.pr5	
RL78	RL78/H1D	R5F11PLG	✓ (1 wire UART)	R5F11PLG.pr5	
RL78	RL78/H1D	R5F11RMG	✓ (1 wire UART)	R5F11RMG.pr5	
RL78	RL78/I1A	R5F1076C	✓ (1 wire UART)	R5F1076C.pr5	
RL78	RL78/I1A	R5F107AC	✓ (1 wire UART)	R5F107AC.pr5	
RL78	RL78/I1A	R5F107AE	✓ (1 wire UART)	R5F107AE.pr5	
RL78	RL78/I1A	R5F107DE	✓ (1 wire UART)	R5F107DE.pr5	
RL78	RL78/I1B	R5F10MME	✓ (1 wire UART)	R5F10MME.pr5	
RL78	RL78/I1B	R5F10MMG	✓ (1 wire UART)	R5F10MMG.pr5	
RL78	RL78/I1B	R5F10MPE	✓ (1 wire UART)	R5F10MPE.pr5	
RL78	RL78/I1B	R5F10MPG	✓ (1 wire UART)	R5F10MPG.pr5	
RL78	RL78/I1C	R5F10NLE	✓ (1 wire UART)	R5F10NLE.pr5	
RL78	RL78/I1C	R5F10NLG	✓ (1 wire UART)	R5F10NLG.pr5	
RL78	RL78/I1C	R5F10NME	✓ (1 wire UART)	R5F10NME.pr5	
RL78	RL78/I1C	R5F10NMG	✓ (1 wire UART)	R5F10NMG.pr5	
RL78	RL78/I1C	R5F10NMJ	✓ (1 wire UART)	R5F10NMJ.pr5	
RL78	RL78/I1C	R5F10NML	✓ (1 wire UART)	R5F10NML.pr5	
RL78	RL78/I1C	R5F10NPG	✓ (1 wire UART)	R5F10NPG.pr5	
RL78	RL78/I1C	R5F10NPJ	✓ (1 wire UART)	R5F10NPJ.pr5	
RL78	RL78/I1C	R5F10NPL	✓ (1 wire UART)	R5F10NPL.pr5	
RL78	RL78/I1C	R5F11TLE	✓ (1 wire UART)	R5F11TLE.pr5	
RL78	RL78/I1C	R5F11TLG	✓ (1 wire UART)	R5F11TLG.pr5	
RL78	RL78/I1D	R5F11768	✓ (1 wire UART)	R5F11768.pr5	
RL78	RL78/I1D	R5F1176A	✓ (1 wire UART)	R5F1176A.pr5	
RL78	RL78/I1D	R5F11778	✓ (1 wire UART)	R5F11778.pr5	
RL78	RL78/I1D	R5F1177A	✓ (1 wire UART)	R5F1177A.pr5	
RL78	RL78/I1D	R5F117A8	✓ (1 wire UART)	R5F117A8.pr5	
RL78	RL78/I1D	R5F117AA	✓ (1 wire UART)	R5F117AA.pr5	
RL78	RL78/I1D	R5F117AC	✓ (1 wire UART)	R5F117AC.pr5	
RL78	RL78/I1D	R5F117BA	✓ (1 wire UART)	R5F117BA.pr5	
RL78	RL78/I1D	R5F117BC	✓ (1 wire UART)	R5F117BC.pr5	
RL78	RL78/I1D	R5F117GA	✓ (1 wire UART)	R5F117GA.pr5	
RL78	RL78/I1D	R5F117GC	✓ (1 wire UART)	R5F117GC.pr5	
RL78	RL78/I1E	R5F11CBC	✓ (1 wire UART)	R5F11CBC.pr5	
RL78	RL78/I1E	R5F11CCC	✓ (1 wire UART)	R5F11CCC.pr5	
RL78	RL78/L12	R5F10RB8	✓ (1 wire UART)	R5F10RB8.pr5	
RL78	RL78/L12	R5F10RBA	✓ (1 wire UART)	R5F10RBA.pr5	
RL78	RL78/L12	R5F10RBC	✓ (1 wire UART)	R5F10RBC.pr5	
RL78	RL78/L12	R5F10RF8	✓ (1 wire UART)	R5F10RF8.pr5	
RL78	RL78/L12	R5F10RFA	✓ (1 wire UART)	R5F10RFA.pr5	
RL78	RL78/L12	R5F10RFC	✓ (1 wire UART)	R5F10RFC.pr5	
RL78	RL78/L12	R5F10RG8	✓ (1 wire UART)	R5F10RG8.pr5	
RL78	RL78/L12	R5F10RGA	✓ (1 wire UART)	R5F10RGA.pr5	
RL78	RL78/L12	R5F10RGC	✓ (1 wire UART)	R5F10RGC.pr5	
RL78	RL78/L12	R5F10RJ8	✓ (1 wire UART)	R5F10RJ8.pr5	
RL78	RL78/L12	R5F10RJA	✓ (1 wire UART)	R5F10RJA.pr5	
RL78	RL78/L12	R5F10RJC	✓ (1 wire UART)	R5F10RJC.pr5	
RL78	RL78/L12	R5F10RLA	✓ (1 wire UART)	R5F10RLA.pr5	
RL78	RL78/L12	R5F10RLC	✓ (1 wire UART)	R5F10RLC.pr5	
RL78	RL78/L13	R5F10WLA	✓ (1 wire UART)	R5F10WLA.pr5	
RL78	RL78/L13	R5F10WLC	✓ (1 wire UART)	R5F10WLC.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RL78	RL78/L13	R5F10WLD	✓ (1 wire UART)	R5F10WLD.pr5	
RL78	RL78/L13	R5F10WLE	✓ (1 wire UART)	R5F10WLE.pr5	
RL78	RL78/L13	R5F10WLF	✓ (1 wire UART)	R5F10WLF.pr5	
RL78	RL78/L13	R5F10WLG	✓ (1 wire UART)	R5F10WLG.pr5	
RL78	RL78/L13	R5F10WMA	✓ (1 wire UART)	R5F10WMA.pr5	
RL78	RL78/L13	R5F10WMC	✓ (1 wire UART)	R5F10WMC.pr5	
RL78	RL78/L13	R5F10WMD	✓ (1 wire UART)	R5F10WMD.pr5	
RL78	RL78/L13	R5F10WME	✓ (1 wire UART)	R5F10WME.pr5	
RL78	RL78/L13	R5F10WMF	✓ (1 wire UART)	R5F10WMF.pr5	
RL78	RL78/L13	R5F10WMG	✓ (1 wire UART)	R5F10WMG.pr5	
RL78	RL78/L1A	R5F11MMD	✓ (1 wire UART)	R5F11MMD.pr5	
RL78	RL78/L1A	R5F11MME	✓ (1 wire UART)	R5F11MME.pr5	
RL78	RL78/L1A	R5F11MMF	✓ (1 wire UART)	R5F11MMF.pr5	
RL78	RL78/L1A	R5F11MPE	✓ (1 wire UART)	R5F11MPE.pr5	
RL78	RL78/L1A	R5F11MPF	✓ (1 wire UART)	R5F11MPF.pr5	
RL78	RL78/L1A	R5F11MPG	✓ (1 wire UART)	R5F11MPG.pr5	
RL78	RL78/L1C	R5F110ME	✓ (1 wire UART)	R5F110ME.pr5	
RL78	RL78/L1C	R5F110MF	✓ (1 wire UART)	R5F110MF.pr5	
RL78	RL78/L1C	R5F110MG	✓ (1 wire UART)	R5F110MG.pr5	
RL78	RL78/L1C	R5F110MH	✓ (1 wire UART)	R5F110MH.pr5	
RL78	RL78/L1C	R5F110MJ	✓ (1 wire UART)	R5F110MJ.pr5	
RL78	RL78/L1C	R5F110NE	✓ (1 wire UART)	R5F110NE.pr5	
RL78	RL78/L1C	R5F110NF	✓ (1 wire UART)	R5F110NF.pr5	
RL78	RL78/L1C	R5F110NG	✓ (1 wire UART)	R5F110NG.pr5	
RL78	RL78/L1C	R5F110NH	✓ (1 wire UART)	R5F110NH.pr5	
RL78	RL78/L1C	R5F110NJ	✓ (1 wire UART)	R5F110NJ.pr5	
RL78	RL78/L1C	R5F110PE	✓ (1 wire UART)	R5F110PE.pr5	
RL78	RL78/L1C	R5F110PF	✓ (1 wire UART)	R5F110PF.pr5	
RL78	RL78/L1C	R5F110PG	✓ (1 wire UART)	R5F110PG.pr5	
RL78	RL78/L1C	R5F110PH	✓ (1 wire UART)	R5F110PH.pr5	
RL78	RL78/L1C	R5F110PJ	✓ (1 wire UART)	R5F110PJ.pr5	
RL78	RL78/L1C	R5F111ME	✓ (1 wire UART)	R5F111ME.pr5	
RL78	RL78/L1C	R5F111MF	✓ (1 wire UART)	R5F111MF.pr5	
RL78	RL78/L1C	R5F111MG	✓ (1 wire UART)	R5F111MG.pr5	
RL78	RL78/L1C	R5F111MH	✓ (1 wire UART)	R5F111MH.pr5	
RL78	RL78/L1C	R5F111MJ	✓ (1 wire UART)	R5F111MJ.pr5	
RL78	RL78/L1C	R5F111NE	✓ (1 wire UART)	R5F111NE.pr5	
RL78	RL78/L1C	R5F111NF	✓ (1 wire UART)	R5F111NF.pr5	
RL78	RL78/L1C	R5F111NG	✓ (1 wire UART)	R5F111NG.pr5	
RL78	RL78/L1C	R5F111NH	✓ (1 wire UART)	R5F111NH.pr5	
RL78	RL78/L1C	R5F111NJ	✓ (1 wire UART)	R5F111NJ.pr5	
RL78	RL78/L1C	R5F111PE	✓ (1 wire UART)	R5F111PE.pr5	
RL78	RL78/L1C	R5F111PF	✓ (1 wire UART)	R5F111PF.pr5	
RL78	RL78/L1C	R5F111PG	✓ (1 wire UART)	R5F111PG.pr5	
RL78	RL78/L1C	R5F111PH	✓ (1 wire UART)	R5F111PH.pr5	
RL78	RL78/L1C	R5F111PJ	✓ (1 wire UART)	R5F111PJ.pr5	
RX	RX110	R5F5110H	✓ (2 wire UART, FINE)	R5F5110H L.pr5	Little endian
RX	RX110	R5F5110H	✓ (2 wire UART, FINE)	R5F5110H B.pr5	Big endian
RX	RX110	R5F5110J	✓ (2 wire UART, FINE)	R5F5110J L.pr5	Little endian
RX	RX110	R5F5110J	✓ (2 wire UART, FINE)	R5F5110J B.pr5	Big endian
RX	RX110	R5F51101	✓ (2 wire UART, FINE)	R5F51101 L.pr5	Little endian
RX	RX110	R5F51101	✓ (2 wire UART, FINE)	R5F51101 B.pr5	Big endian
RX	RX110	R5F51103	✓ (2 wire UART, FINE)	R5F51103 L.pr5	Little endian
RX	RX110	R5F51103	✓ (2 wire UART, FINE)	R5F51103 B.pr5	Big endian
RX	RX110	R5F51104	✓ (2 wire UART, FINE)	R5F51104 L.pr5	Little endian
RX	RX110	R5F51104	✓ (2 wire UART, FINE)	R5F51104 B.pr5	Big endian
RX	RX110	R5F51105	✓ (2 wire UART, FINE)	R5F51105 L.pr5	Little endian
RX	RX110	R5F51105	✓ (2 wire UART, FINE)	R5F51105 B.pr5	Big endian
RX	RX111	R5F5111J	✓ (2 wire UART, FINE)	R5F5111J L.pr5	Little endian
RX	RX111	R5F5111J	✓ (2 wire UART, FINE)	R5F5111J B.pr5	Big endian
RX	RX111	R5F51111	✓ (2 wire UART, FINE)	R5F51111 L.pr5	Little endian
RX	RX111	R5F51111	✓ (2 wire UART, FINE)	R5F51111 B.pr5	Big endian
RX	RX111	R5F51113	✓ (2 wire UART, FINE)	R5F51113 L.pr5	Little endian
RX	RX111	R5F51113	✓ (2 wire UART, FINE)	R5F51113 B.pr5	Big endian
RX	RX111	R5F51114	✓ (2 wire UART, FINE)	R5F51114 L.pr5	Little endian
RX	RX111	R5F51114	✓ (2 wire UART, FINE)	R5F51114 B.pr5	Big endian

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RX	RX111	R5F51115	✓ (2 wire UART, FINE)	R5F51115 L.pr5	Little endian
RX	RX111	R5F51115	✓ (2 wire UART, FINE)	R5F51115 B.pr5	Big endian
RX	RX111	R5F51116	✓ (2 wire UART, FINE)	R5F51116 L.pr5	Little endian
RX	RX111	R5F51116	✓ (2 wire UART, FINE)	R5F51116 B.pr5	Big endian
RX	RX111	R5F51117	✓ (2 wire UART, FINE)	R5F51117 L.pr5	Little endian
RX	RX111	R5F51117	✓ (2 wire UART, FINE)	R5F51117 B.pr5	Big endian
RX	RX111	R5F51118	✓ (2 wire UART, FINE)	R5F51118 L.pr5	Little endian
RX	RX111	R5F51118	✓ (2 wire UART, FINE)	R5F51118 B.pr5	Big endian
RX	RX113	R5F51135	✓ (2 wire UART, FINE)	R5F51135 L.pr5	Little endian
RX	RX113	R5F51135	✓ (2 wire UART, FINE)	R5F51135 B.pr5	Big endian
RX	RX113	R5F51136	✓ (2 wire UART, FINE)	R5F51136 L.pr5	Little endian
RX	RX113	R5F51136	✓ (2 wire UART, FINE)	R5F51136 B.pr5	Big endian
RX	RX113	R5F51137	✓ (2 wire UART, FINE)	R5F51137 L.pr5	Little endian
RX	RX113	R5F51137	✓ (2 wire UART, FINE)	R5F51137 B.pr5	Big endian
RX	RX113	R5F51138	✓ (2 wire UART, FINE)	R5F51138 L.pr5	Little endian
RX	RX113	R5F51138	✓ (2 wire UART, FINE)	R5F51138 B.pr5	Big endian
RX	RX130	R5F51303A	✓ (2 wire UART, FINE)	R5F51303 L.pr5	Little endian
RX	RX130	R5F51303A	✓ (2 wire UART, FINE)	R5F51303 B.pr5	Big endian
RX	RX130	R5F51305A	✓ (2 wire UART, FINE)	R5F51305 L.pr5	Little endian, 80pins or less
RX	RX130	R5F51305A	✓ (2 wire UART, FINE)	R5F51305 B.pr5	Big endian, 80pins or less
RX	RX130	R5F51305A	✓ (2 wire UART, FINE)	R5F51305 L 2.pr5	Little endian, 100pin
RX	RX130	R5F51305A	✓ (2 wire UART, FINE)	R5F51305 B 2.pr5	Big endian, 100pin
RX	RX130	R5F51305B	✓ (2 wire UART, FINE)	R5F51305B L.pr5	Little endian
RX	RX130	R5F51305B	✓ (2 wire UART, FINE)	R5F51305B B.pr5	Big endian
RX	RX130	R5F51306A	✓ (2 wire UART, FINE)	R5F51306 L.pr5	Little endian
RX	RX130	R5F51306A	✓ (2 wire UART, FINE)	R5F51306 B.pr5	Big endian
RX	RX130	R5F51306B	✓ (2 wire UART, FINE)	R5F51306B L.pr5	Little endian
RX	RX130	R5F51306B	✓ (2 wire UART, FINE)	R5F51306B B.pr5	Big endian
RX	RX130	R5F51307A	✓ (2 wire UART, FINE)	R5F51307 L.pr5	Little endian
RX	RX130	R5F51307A	✓ (2 wire UART, FINE)	R5F51307 B.pr5	Big endian
RX	RX130	R5F51308A	✓ (2 wire UART, FINE)	R5F51308 L.pr5	Little endian
RX	RX130	R5F51308A	✓ (2 wire UART, FINE)	R5F51308 B.pr5	Big endian
RX	RX13T	R5F513T3	✓ (2 wire UART, FINE)	R5F513T5 L.pr5	Little endian
RX	RX13T	R5F513T3	✓ (2 wire UART, FINE)	R5F513T5 B.pr5	Big endian
RX	RX13T	R5F513T5	✓ (2 wire UART, FINE)	R5F513T5 L.pr5	Little endian
RX	RX13T	R5F513T5	✓ (2 wire UART, FINE)	R5F513T5 B.pr5	Big endian
RX	RX140	R5F51403	✓ (2 wire UART, FINE)	R5F51403 L.pr6	Little endian
RX	RX140	R5F51403	✓ (2 wire UART, FINE)	R5F51403 B.pr6	Big endian
RX	RX140	R5F51405	✓ (2 wire UART, FINE)	R5F51406 L.pr6	Little endian
RX	RX140	R5F51405	✓ (2 wire UART, FINE)	R5F51406 B.pr6	Big endian
RX	RX140	R5F51406	✓ (2 wire UART, FINE)	R5F51406 L.pr6	Little endian
RX	RX140	R5F51406	✓ (2 wire UART, FINE)	R5F51406 B.pr6	Big endian
RX	RX210	R5F52103B	✓ (2 wire UART, FINE)	R5F52103B L.pr5	Little endian
RX	RX210	R5F52103B	✓ (2 wire UART, FINE)	R5F52103B B.pr5	Big endian
RX	RX210	R5F52104B	✓ (2 wire UART, FINE)	R5F52104B L.pr5	Little endian
RX	RX210	R5F52104B	✓ (2 wire UART, FINE)	R5F52104B B.pr5	Big endian
RX	RX210	R5F52105A	✓ (2 wire UART)	R5F52105A L.pr5	Little endian
RX	RX210	R5F52105A	✓ (2 wire UART)	R5F52105A B.pr5	Big endian
RX	RX210	R5F52105B	✓ (2 wire UART, FINE)	R5F52105B L.pr5	Little endian, 100pins or less
RX	RX210	R5F52105B	✓ (2 wire UART, FINE)	R5F52105B L 2.pr5	Little endian, 144pins or more
RX	RX210	R5F52105B	✓ (2 wire UART, FINE)	R5F52105B B.pr5	Big endian, 100pins or less
RX	RX210	R5F52105B	✓ (2 wire UART, FINE)	R5F52105B B 2.pr5	Big endian, 144pins or more
RX	RX210	R5F52106A	✓ (2 wire UART)	R5F52106A L.pr5	Little endian
RX	RX210	R5F52106A	✓ (2 wire UART)	R5F52106A B.pr5	Big endian
RX	RX210	R5F52106B	✓ (2 wire UART, FINE)	R5F52106B L.pr5	Little endian, 100pins or less
RX	RX210	R5F52106B	✓ (2 wire UART, FINE)	R5F52106B L 2.pr5	Little endian, 144pins or more
RX	RX210	R5F52106B	✓ (2 wire UART, FINE)	R5F52106B B.pr5	Big endian, 100pins or less
RX	RX210	R5F52106B	✓ (2 wire UART, FINE)	R5F52106B B 2.pr5	Big endian, 144pins or more
RX	RX210	R5F52107A	✓ (2 wire UART)	R5F52107A L.pr5	Little endian
RX	RX210	R5F52107A	✓ (2 wire UART)	R5F52107A B.pr5	Big endian
RX	RX210	R5F52107B	✓ (2 wire UART, FINE)	R5F52107B L.pr5	Little endian
RX	RX210	R5F52107B	✓ (2 wire UART, FINE)	R5F52107B B.pr5	Big endian
RX	RX210	R5F52107C	✓ (2 wire UART, FINE)	R5F52107C L.pr5	Little endian
RX	RX210	R5F52107C	✓ (2 wire UART, FINE)	R5F52107C B.pr5	Big endian
RX	RX210	R5F52108A	✓ (2 wire UART)	R5F52108A L.pr5	Little endian
RX	RX210	R5F52108A	✓ (2 wire UART)	R5F52108A B.pr5	Big endian

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RX	RX210	R5F52108B	✓ (2 wire UART, FINE)	R5F52108B L.pr5	Little endian
RX	RX210	R5F52108B	✓ (2 wire UART, FINE)	R5F52108B B.pr5	Big endian
RX	RX210	R5F52108C	✓ (2 wire UART, FINE)	R5F52108C L.pr5	Little endian
RX	RX210	R5F52108C	✓ (2 wire UART, FINE)	R5F52108C B.pr5	Big endian
RX	RX210	R5F5210AB	✓ (2 wire UART, FINE)	R5F5210AB L.pr5	Little endian
RX	RX210	R5F5210AB	✓ (2 wire UART, FINE)	R5F5210AB B.pr5	Big endian
RX	RX210	R5F5210BB	✓ (2 wire UART, FINE)	R5F5210BB L.pr5	Little endian
RX	RX210	R5F5210BB	✓ (2 wire UART, FINE)	R5F5210BB B.pr5	Big endian
RX	RX21A	R5F521A6B	✓ (2 wire UART, FINE)	R5F521A6B L.pr5	Little endian
RX	RX21A	R5F521A6B	✓ (2 wire UART, FINE)	R5F521A6B B.pr5	Big endian
RX	RX21A	R5F521A7B	✓ (2 wire UART, FINE)	R5F521A7B L.pr5	Little endian
RX	RX21A	R5F521A7B	✓ (2 wire UART, FINE)	R5F521A7B B.pr5	Big endian
RX	RX21A	R5F521A8B	✓ (2 wire UART, FINE)	R5F521A8B L.pr5	Little endian
RX	RX21A	R5F521A8B	✓ (2 wire UART, FINE)	R5F521A8B B.pr5	Big endian
RX	RX220	R5F52201B	✓ (2 wire UART, FINE)	R5F52201B L.pr5	Little endian
RX	RX220	R5F52201B	✓ (2 wire UART, FINE)	R5F52201B B.pr5	Big endian
RX	RX220	R5F52203B	✓ (2 wire UART, FINE)	R5F52203B L.pr5	Little endian
RX	RX220	R5F52203B	✓ (2 wire UART, FINE)	R5F52203B B.pr5	Big endian
RX	RX220	R5F52205B	✓ (2 wire UART, FINE)	R5F52205B L.pr5	Little endian
RX	RX220	R5F52205B	✓ (2 wire UART, FINE)	R5F52205B B.pr5	Big endian
RX	RX220	R5F52206B	✓ (2 wire UART, FINE)	R5F52206B L.pr5	Little endian
RX	RX220	R5F52206B	✓ (2 wire UART, FINE)	R5F52206B B.pr5	Big endian
RX	RX230	R5F52305	✓ (2 wire UART, FINE)	R5F52305 L.pr6	Little endian
RX	RX230	R5F52305	✓ (2 wire UART, FINE)	R5F52305 B.pr6	Big endian
RX	RX230	R5F52306	✓ (2 wire UART, FINE)	R5F52306 L.pr6	Little endian
RX	RX230	R5F52306	✓ (2 wire UART, FINE)	R5F52306 B.pr6	Big endian
RX	RX231	R5F52315A	✓ (2 wire UART, FINE)	R5F52315A L.pr6	Little endian
RX	RX231	R5F52315A	✓ (2 wire UART, FINE)	R5F52315A B.pr6	Big endian
RX	RX231	R5F52315C	✓ (2 wire UART, FINE)	R5F52315C L.pr6	Little endian
RX	RX231	R5F52315C	✓ (2 wire UART, FINE)	R5F52315C B.pr6	Big endian
RX	RX231	R5F52316A	✓ (2 wire UART, FINE)	R5F52316A L.pr6	Little endian
RX	RX231	R5F52316A	✓ (2 wire UART, FINE)	R5F52316A B.pr6	Big endian
RX	RX231	R5F52316C	✓ (2 wire UART, FINE)	R5F52316C L.pr6	Little endian
RX	RX231	R5F52316C	✓ (2 wire UART, FINE)	R5F52316C B.pr6	Big endian
RX	RX231	R5F52317A	✓ (2 wire UART, FINE)	R5F52317A L.pr6	Little endian
RX	RX231	R5F52317A	✓ (2 wire UART, FINE)	R5F52317A B.pr6	Big endian
RX	RX231	R5F52317B	✓ (2 wire UART, FINE)	R5F52317B L.pr6	Little endian
RX	RX231	R5F52317B	✓ (2 wire UART, FINE)	R5F52317B B.pr6	Big endian
RX	RX231	R5F52318A	✓ (2 wire UART, FINE)	R5F52318A L.pr6	Little endian
RX	RX231	R5F52318A	✓ (2 wire UART, FINE)	R5F52318A B.pr6	Big endian
RX	RX231	R5F52318B	✓ (2 wire UART, FINE)	R5F52318B L.pr6	Little endian
RX	RX231	R5F52318B	✓ (2 wire UART, FINE)	R5F52318B B.pr6	Big endian
RX	RX23E-A	R5F523E5A	✓ (2 wire UART, FINE)	R5F523E6A L.pr6	Little endian
RX	RX23E-A	R5F523E5A	✓ (2 wire UART, FINE)	R5F523E6A B.pr6	Big endian
RX	RX23E-A	R5F523E5S	✓ (2 wire UART, FINE)	R5F523E6A L.pr6	Little endian
RX	RX23E-A	R5F523E5S	✓ (2 wire UART, FINE)	R5F523E6A B.pr6	Big endian
RX	RX23E-A	R5F523E6A	✓ (2 wire UART, FINE)	R5F523E6A L.pr6	Little endian
RX	RX23E-A	R5F523E6A	✓ (2 wire UART, FINE)	R5F523E6A B.pr6	Big endian
RX	RX23E-A	R5F523E6S	✓ (2 wire UART, FINE)	R5F523E6A L.pr6	Little endian
RX	RX23E-A	R5F523E6S	✓ (2 wire UART, FINE)	R5F523E6A B.pr6	Big endian
RX	RX23E-B	R5F523E5B	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E5B	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E5J	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E5J	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E5K	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E5K	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E5L	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E5L	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E5M	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E5M	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E5N	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E5N	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E6B	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E6B	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E6J	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E6J	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RX	RX23E-B	R5F523E6K	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E6K	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E6L	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E6L	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E6M	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E6M	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23E-B	R5F523E6N	✓ (2 wire UART, FINE)	R5F523E6 L.pr6	Little endian
RX	RX23E-B	R5F523E6N	✓ (2 wire UART, FINE)	R5F523E6 B.pr6	Big endian
RX	RX23T	R5F523T3	✓ (2 wire UART, FINE)	R5F523T3 L.pr6	Little endian
RX	RX23T	R5F523T3	✓ (2 wire UART, FINE)	R5F523T3 B.pr6	Big endian
RX	RX23T	R5F523T5	✓ (2 wire UART, FINE)	R5F523T5 L.pr6	Little endian
RX	RX23T	R5F523T5	✓ (2 wire UART, FINE)	R5F523T5 B.pr6	Big endian
RX	RX23W	R5F523W7	✓ (2 wire UART, FINE)	R5F523W8 L.pr6	Little endian
RX	RX23W	R5F523W7	✓ (2 wire UART, FINE)	R5F523W8 B.pr6	Big endian
RX	RX23W	R5F523W8	✓ (2 wire UART, FINE)	R5F523W8 L.pr6	Little endian
RX	RX23W	R5F523W8	✓ (2 wire UART, FINE)	R5F523W8 B.pr6	Big endian
RX	RX24T	R5F524T8	✓ (2 wire UART, FINE)	R5F524T8 L.pr6	Little endian
RX	RX24T	R5F524T8	✓ (2 wire UART, FINE)	R5F524T8 B.pr6	Big endian
RX	RX24T	R5F524TA	✓ (2 wire UART, FINE)	R5F524TA L.pr6	Little endian
RX	RX24T	R5F524TA	✓ (2 wire UART, FINE)	R5F524TA B.pr6	Big endian
RX	RX24T	R5F524TB	✓ (2 wire UART, FINE)	R5F524TB L.pr6	Little endian
RX	RX24T	R5F524TB	✓ (2 wire UART, FINE)	R5F524TB B.pr6	Big endian
RX	RX24T	R5F524TC	✓ (2 wire UART, FINE)	R5F524TC L.pr6	Little endian
RX	RX24T	R5F524TC	✓ (2 wire UART, FINE)	R5F524TC B.pr6	Big endian
RX	RX24T	R5F524TE	✓ (2 wire UART, FINE)	R5F524TE L.pr6	Little endian
RX	RX24T	R5F524TE	✓ (2 wire UART, FINE)	R5F524TE B.pr6	Big endian
RX	RX24U	R5F524UB	✓ (2 wire UART, FINE)	R5F524UB L.pr6	Little endian
RX	RX24U	R5F524UB	✓ (2 wire UART, FINE)	R5F524UB B.pr6	Big endian
RX	RX24U	R5F524UC	✓ (2 wire UART, FINE)	R5F524UC L.pr6	Little endian
RX	RX24U	R5F524UC	✓ (2 wire UART, FINE)	R5F524UC B.pr6	Big endian
RX	RX24U	R5F524UE	✓ (2 wire UART, FINE)	R5F524UE L.pr6	Little endian
RX	RX24U	R5F524UE	✓ (2 wire UART, FINE)	R5F524UE B.pr6	Big endian
RX	RX260	R5F52606	✓ (2 wire UART, FINE)	R5F52608 L.pr6	Little endian
RX	RX260	R5F52606	✓ (2 wire UART, FINE)	R5F52608 B.pr6	Big endian
RX	RX260	R5F52607	✓ (2 wire UART, FINE)	R5F52608 L.pr6	Little endian
RX	RX260	R5F52607	✓ (2 wire UART, FINE)	R5F52608 B.pr6	Big endian
RX	RX260	R5F52608	✓ (2 wire UART, FINE)	R5F52608 L.pr6	Little endian
RX	RX260	R5F52608	✓ (2 wire UART, FINE)	R5F52608 B.pr6	Big endian
RX	RX261	R5F52616	✓ (2 wire UART, FINE)	R5F52618 L.pr6	Little endian
RX	RX261	R5F52616	✓ (2 wire UART, FINE)	R5F52618 B.pr6	Big endian
RX	RX261	R5F52617	✓ (2 wire UART, FINE)	R5F52618 L.pr6	Little endian
RX	RX261	R5F52617	✓ (2 wire UART, FINE)	R5F52618 B.pr6	Big endian
RX	RX261	R5F52618	✓ (2 wire UART, FINE)	R5F52618 L.pr6	Little endian
RX	RX261	R5F52618	✓ (2 wire UART, FINE)	R5F52618 B.pr6	Big endian
RX	RX26T	R5F526T8	✓ (2 wire UART, FINE)	R5F526TA.pr6	
RX	RX26T	R5F526T9	✓ (2 wire UART, FINE)	R5F526TF L.pr6	
RX	RX26T	R5F526TA	✓ (2 wire UART, FINE)	R5F526TA.pr6	
RX	RX26T	R5F526TB	✓ (2 wire UART, FINE)	R5F526TF L.pr6	
RX	RX26T	R5F526TF	✓ (2 wire UART, FINE)	R5F526TF L.pr6	Linear Mode
RX	RX26T	R5F526TF	✓ (2 wire UART, FINE)	R5F526TF D.pr6	Dual Mode
RX	RX610	R5F56104	✓ (2 wire UART)	R5F56104.pr5	
RX	RX610	R5F56106	✓ (2 wire UART)	R5F56106.pr5	
RX	RX610	R5F56107	✓ (2 wire UART)	R5F56107.pr5	
RX	RX610	R5F56108	✓ (2 wire UART)	R5F56108.pr5	
RX	RX621	R5F56216	✓ (2 wire UART)	R5F56216.pr5	
RX	RX621	R5F56217	✓ (2 wire UART)	R5F56217.pr5	
RX	RX621	R5F56218	✓ (2 wire UART)	R5F56218.pr5	
RX	RX62G	R5F562G7A	✓ (2 wire UART)	R5F562G7A.pr5	
RX	RX62G	R5F562G7D	✓ (2 wire UART)	R5F562G7D.pr5	
RX	RX62G	R5F562GAA	✓ (2 wire UART)	R5F562GAA.pr5	
RX	RX62G	R5F562GAD	✓ (2 wire UART)	R5F562GAD.pr5	
RX	RX62N	R5F562N7	✓ (2 wire UART)	R5F562N7.pr5	
RX	RX62N	R5F562N8	✓ (2 wire UART)	R5F562N8.pr5	
RX	RX62T	R5F562T6A	✓ (2 wire UART)	R5F562T6A.pr5	
RX	RX62T	R5F562T6B	✓ (2 wire UART)	R5F562T6B.pr5	
RX	RX62T	R5F562T6D	✓ (2 wire UART)	R5F562T6D.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RX	RX62T	R5F562T6E	✓ (2 wire UART)	R5F562T6E.pr5	
RX	RX62T	R5F562T7A	✓ (2 wire UART)	R5F562T7A.pr5	
RX	RX62T	R5F562T7B	✓ (2 wire UART)	R5F562T7B.pr5	
RX	RX62T	R5F562T7D	✓ (2 wire UART)	R5F562T7D.pr5	
RX	RX62T	R5F562T7E	✓ (2 wire UART)	R5F562T7E.pr5	
RX	RX62T	R5F562TAA	✓ (2 wire UART)	R5F562TAA.pr5	
RX	RX62T	R5F562TAB	✓ (2 wire UART)	R5F562TAB.pr5	
RX	RX62T	R5F562TAD	✓ (2 wire UART)	R5F562TAD.pr5	
RX	RX62T	R5F562TAE	✓ (2 wire UART)	R5F562TAE.pr5	
RX	RX630	R5F56307	✓ (2 wire UART)	R5F56307 L.pr5	Little endian
RX	RX630	R5F56307	✓ (2 wire UART)	R5F56307 B.pr5	Big endian
RX	RX630	R5F56308	✓ (2 wire UART)	R5F56308 L.pr5	Little endian
RX	RX630	R5F56308	✓ (2 wire UART)	R5F56308 B.pr5	Big endian
RX	RX630	R5F5630A	✓ (2 wire UART)	R5F5630A L.pr5	Little endian, 145pins or less
RX	RX630	R5F5630A	✓ (2 wire UART)	R5F5630A B.pr5	Big endian, 145pins or less
RX	RX630	R5F5630A	✓ (2 wire UART)	R5F5630A L 2.pr5	Little endian, 176pins or more
RX	RX630	R5F5630A	✓ (2 wire UART)	R5F5630A B 2.pr5	Big endian, 176pins or more
RX	RX630	R5F5630B	✓ (2 wire UART)	R5F5630B L.pr5	Little endian, 145pins or less
RX	RX630	R5F5630B	✓ (2 wire UART)	R5F5630B B.pr5	Big endian, 145pins or less
RX	RX630	R5F5630B	✓ (2 wire UART)	R5F5630B L 2.pr5	Little endian, 176pins or more
RX	RX630	R5F5630B	✓ (2 wire UART)	R5F5630B B 2.pr5	Big endian, 176pins or more
RX	RX630	R5F5630D	✓ (2 wire UART)	R5F5630D L.pr5	Little endian
RX	RX630	R5F5630D	✓ (2 wire UART)	R5F5630D B.pr5	Big endian
RX	RX630	R5F5630E	✓ (2 wire UART)	R5F5630E L.pr5	Little endian
RX	RX630	R5F5630E	✓ (2 wire UART)	R5F5630E B.pr5	Big endian
RX	RX631	R5F56316	✓ (2 wire UART)	R5F56316 L.pr5	Little endian
RX	RX631	R5F56316	✓ (2 wire UART)	R5F56316 B.pr5	Big endian
RX	RX631	R5F56317	✓ (2 wire UART)	R5F56317 L.pr5	Little endian
RX	RX631	R5F56317	✓ (2 wire UART)	R5F56317 B.pr5	Big endian
RX	RX631	R5F56318	✓ (2 wire UART)	R5F56318 L.pr5	Little endian
RX	RX631	R5F56318	✓ (2 wire UART)	R5F56318 B.pr5	Big endian
RX	RX631	R5F5631A	✓ (2 wire UART)	R5F5631A L.pr5	Little endian
RX	RX631	R5F5631A	✓ (2 wire UART)	R5F5631A B.pr5	Big endian
RX	RX631	R5F5631B	✓ (2 wire UART)	R5F5631B L.pr5	Little endian
RX	RX631	R5F5631B	✓ (2 wire UART)	R5F5631B B.pr5	Big endian
RX	RX631	R5F5631D	✓ (2 wire UART)	R5F5631D L.pr5	Little endian
RX	RX631	R5F5631D	✓ (2 wire UART)	R5F5631D B.pr5	Big endian
RX	RX631	R5F5631E	✓ (2 wire UART)	R5F5631E L.pr5	Little endian
RX	RX631	R5F5631E	✓ (2 wire UART)	R5F5631E B.pr5	Big endian
RX	RX631	R5F5631F	✓ (2 wire UART)	R5F5631F L.pr5	Little endian
RX	RX631	R5F5631F	✓ (2 wire UART)	R5F5631F B.pr5	Big endian
RX	RX631	R5F5631G	✓ (2 wire UART)	R5F5631G L.pr5	Little endian
RX	RX631	R5F5631G	✓ (2 wire UART)	R5F5631G B.pr5	Big endian
RX	RX631	R5F5631J	✓ (2 wire UART)	R5F5631J L.pr5	Little endian
RX	RX631	R5F5631J	✓ (2 wire UART)	R5F5631J B.pr5	Big endian
RX	RX631	R5F5631K	✓ (2 wire UART)	R5F5631K L.pr5	Little endian
RX	RX631	R5F5631K	✓ (2 wire UART)	R5F5631K B.pr5	Big endian
RX	RX631	R5F5631M	✓ (2 wire UART)	R5F5631M L.pr5	Little endian
RX	RX631	R5F5631M	✓ (2 wire UART)	R5F5631M B.pr5	Big endian
RX	RX631	R5F5631N	✓ (2 wire UART)	R5F5631N L.pr5	Little endian
RX	RX631	R5F5631N	✓ (2 wire UART)	R5F5631N B.pr5	Big endian
RX	RX631	R5F5631P	✓ (2 wire UART)	R5F5631P L.pr5	Little endian
RX	RX631	R5F5631P	✓ (2 wire UART)	R5F5631P B.pr5	Big endian
RX	RX631	R5F5631W	✓ (2 wire UART)	R5F5631W L.pr5	Little endian
RX	RX631	R5F5631W	✓ (2 wire UART)	R5F5631W B.pr5	Big endian
RX	RX631	R5F5631Y	✓ (2 wire UART)	R5F5631Y L.pr5	Little endian
RX	RX631	R5F5631Y	✓ (2 wire UART)	R5F5631Y B.pr5	Big endian
RX	RX634	R5F5634BC	✓ (2 wire UART)	R5F5634BC L.pr5	Little endian
RX	RX634	R5F5634BC	✓ (2 wire UART)	R5F5634BC B.pr5	Big endian
RX	RX634	R5F5634BY	✓ (2 wire UART)	R5F5634BY L.pr5	Little endian
RX	RX634	R5F5634BY	✓ (2 wire UART)	R5F5634BY B.pr5	Big endian
RX	RX634	R5F5634DC	✓ (2 wire UART)	R5F5634DC L.pr5	Little endian
RX	RX634	R5F5634DC	✓ (2 wire UART)	R5F5634DC B.pr5	Big endian
RX	RX634	R5F5634DY	✓ (2 wire UART)	R5F5634DY L.pr5	Little endian
RX	RX634	R5F5634DY	✓ (2 wire UART)	R5F5634DY B.pr5	Big endian
RX	RX634	R5F5634EC	✓ (2 wire UART)	R5F5634EC L.pr5	Little endian

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RX	RX634	R5F5634EC	✓ (2 wire UART)	R5F5634EC B.pr5	Big endian
RX	RX634	R5F5634EY	✓ (2 wire UART)	R5F5634EY L.pr5	Little endian
RX	RX634	R5F5634EY	✓ (2 wire UART)	R5F5634EY B.pr5	Big endian
RX	RX63N	R5F563NA	✓ (2 wire UART)	R5F563NA L.pr5	Little endian
RX	RX63N	R5F563NA	✓ (2 wire UART)	R5F563NA B.pr5	Big endian
RX	RX63N	R5F563NB	✓ (2 wire UART)	R5F563NB L.pr5	Little endian
RX	RX63N	R5F563NB	✓ (2 wire UART)	R5F563NB B.pr5	Big endian
RX	RX63N	R5F563ND	✓ (2 wire UART)	R5F563ND L.pr5	Little endian
RX	RX63N	R5F563ND	✓ (2 wire UART)	R5F563ND B.pr5	Big endian
RX	RX63N	R5F563NE	✓ (2 wire UART)	R5F563NE L.pr5	Little endian
RX	RX63N	R5F563NE	✓ (2 wire UART)	R5F563NE B.pr5	Big endian
RX	RX63N	R5F563NF	✓ (2 wire UART)	R5F563NF L.pr5	Little endian
RX	RX63N	R5F563NF	✓ (2 wire UART)	R5F563NF B.pr5	Big endian
RX	RX63N	R5F563NG	✓ (2 wire UART)	R5F563NG L.pr5	Little endian
RX	RX63N	R5F563NG	✓ (2 wire UART)	R5F563NG B.pr5	Big endian
RX	RX63N	R5F563NJ	✓ (2 wire UART)	R5F563NJ L.pr5	Little endian
RX	RX63N	R5F563NJ	✓ (2 wire UART)	R5F563NJ B.pr5	Big endian
RX	RX63N	R5F563NK	✓ (2 wire UART)	R5F563NK L.pr5	Little endian
RX	RX63N	R5F563NK	✓ (2 wire UART)	R5F563NK B.pr5	Big endian
RX	RX63N	R5F563NW	✓ (2 wire UART)	R5F563NW L.pr5	Little endian
RX	RX63N	R5F563NW	✓ (2 wire UART)	R5F563NW B.pr5	Big endian
RX	RX63N	R5F563NY	✓ (2 wire UART)	R5F563NY L.pr5	Little endian
RX	RX63N	R5F563NY	✓ (2 wire UART)	R5F563NY B.pr5	Big endian
RX	RX63T	R5F563T4	✓ (2 wire UART)	R5F563T4 L.pr5	Little endian
RX	RX63T	R5F563T4	✓ (2 wire UART)	R5F563T4 B.pr5	Big endian
RX	RX63T	R5F563T5	✓ (2 wire UART)	R5F563T5 L.pr5	Little endian
RX	RX63T	R5F563T5	✓ (2 wire UART)	R5F563T5 B.pr5	Big endian
RX	RX63T	R5F563T6	✓ (2 wire UART)	R5F563T6 L.pr5	Little endian
RX	RX63T	R5F563T6	✓ (2 wire UART)	R5F563T6 B.pr5	Big endian
RX	RX63T	R5F563TBA	✓ (2 wire UART)	R5F563TBA L.pr5	Little endian
RX	RX63T	R5F563TBA	✓ (2 wire UART)	R5F563TBA B.pr5	Big endian
RX	RX63T	R5F563TBB	✓ (2 wire UART)	R5F563TBB L.pr5	Little endian
RX	RX63T	R5F563TBB	✓ (2 wire UART)	R5F563TBB B.pr5	Big endian
RX	RX63T	R5F563TBD	✓ (2 wire UART)	R5F563TBD L.pr5	Little endian
RX	RX63T	R5F563TBD	✓ (2 wire UART)	R5F563TBD B.pr5	Big endian
RX	RX63T	R5F563TBE	✓ (2 wire UART)	R5F563TBE L.pr5	Little endian
RX	RX63T	R5F563TBE	✓ (2 wire UART)	R5F563TBE B.pr5	Big endian
RX	RX63T	R5F563TCA	✓ (2 wire UART)	R5F563TCA L.pr5	Little endian
RX	RX63T	R5F563TCA	✓ (2 wire UART)	R5F563TCA B.pr5	Big endian
RX	RX63T	R5F563TCB	✓ (2 wire UART)	R5F563TCB L.pr5	Little endian
RX	RX63T	R5F563TCB	✓ (2 wire UART)	R5F563TCB B.pr5	Big endian
RX	RX63T	R5F563TCD	✓ (2 wire UART)	R5F563TCD L.pr5	Little endian
RX	RX63T	R5F563TCD	✓ (2 wire UART)	R5F563TCD B.pr5	Big endian
RX	RX63T	R5F563TCE	✓ (2 wire UART)	R5F563TCE L.pr5	Little endian
RX	RX63T	R5F563TCE	✓ (2 wire UART)	R5F563TCE B.pr5	Big endian
RX	RX63T	R5F563TEA	✓ (2 wire UART)	R5F563TEA L.pr5	Little endian
RX	RX63T	R5F563TEA	✓ (2 wire UART)	R5F563TEA B.pr5	Big endian
RX	RX63T	R5F563TEB	✓ (2 wire UART)	R5F563TEB L.pr5	Little endian
RX	RX63T	R5F563TEB	✓ (2 wire UART)	R5F563TEB B.pr5	Big endian
RX	RX63T	R5F563TED	✓ (2 wire UART)	R5F563TED L.pr5	Little endian
RX	RX63T	R5F563TED	✓ (2 wire UART)	R5F563TED B.pr5	Big endian
RX	RX63T	R5F563TEE	✓ (2 wire UART)	R5F563TEE L.pr5	Little endian
RX	RX63T	R5F563TEE	✓ (2 wire UART)	R5F563TEE B.pr5	Big endian
RX	RX64M	R5F564MF	✓ (2 wire UART)	R5F564M.pr6	
RX	RX64M	R5F564MG	✓ (2 wire UART)	R5F564M.pr6	
RX	RX64M	R5F564MJ	✓ (2 wire UART)	R5F564M.pr6	
RX	RX64M	R5F564ML	✓ (2 wire UART)	R5F564M.pr6	
RX	RX651	R5F56514	✓ (2 wire UART, FINE)	R5F5651.pr6	
RX	RX651	R5F56517	✓ (2 wire UART, FINE)	R5F5651.pr6	
RX	RX651	R5F56519	✓ (2 wire UART, FINE)	R5F5651.pr6	
RX	RX651	R5F5651C	✓ (2 wire UART, FINE)	R5F5651 D 2.pr6	Dual Mode
RX	RX651	R5F5651C	✓ (2 wire UART, FINE)	R5F5651 L 2.pr6	Linear Mode
RX	RX651	R5F5651E	✓ (2 wire UART, FINE)	R5F5651 D 2.pr6	Dual Mode
RX	RX651	R5F5651E	✓ (2 wire UART, FINE)	R5F5651 L 2.pr6	Linear Mode
RX	RX65N	R5F565N4	✓ (2 wire UART, FINE)	R5F565N.pr6	
RX	RX65N	R5F565N7	✓ (2 wire UART, FINE)	R5F565N.pr6	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RX	RX65N	R5F565N9	✓ (2 wire UART, FINE)	R5F565N.pr6	
RX	RX65N	R5F565NC	✓ (2 wire UART, FINE)	R5F565N D 2.pr6	Dual Mode
RX	RX65N	R5F565NC	✓ (2 wire UART, FINE)	R5F565N L 2.pr6	Linear Mode
RX	RX65N	R5F565NE	✓ (2 wire UART, FINE)	R5F565N D 2.pr6	Dual Mode
RX	RX65N	R5F565NE	✓ (2 wire UART, FINE)	R5F565N L 2.pr6	Linear Mode
RX	RX65W-A	R5F565WE	✓ (2 wire UART, FINE)	R5F565W D.pr6	Dual Mode
RX	RX65W-A	R5F565WE	✓ (2 wire UART, FINE)	R5F565W L.pr6	Linear Mode
RX	RX660	R5F56604	✓ (2 wire UART, FINE)	R5F56609.pr6	
RX	RX660	R5F56609	✓ (2 wire UART, FINE)	R5F56609.pr6	
RX	RX66N	R5F566ND	✓ (2 wire UART, FINE)	R5F566N D.pr6	Dual Mode
RX	RX66N	R5F566ND	✓ (2 wire UART, FINE)	R5F566N L.pr6	Linear Mode
RX	RX66N	R5F566NN	✓ (2 wire UART, FINE)	R5F566N D.pr6	Dual Mode
RX	RX66N	R5F566NN	✓ (2 wire UART, FINE)	R5F566N L.pr6	Linear Mode
RX	RX66T	R5F566TA	✓ (2 wire UART, FINE)	R5F566TE.pr6	
RX	RX66T	R5F566TE	✓ (2 wire UART, FINE)	R5F566TE.pr6	
RX	RX66T	R5F566TFA	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TFB	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TFC	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TFE	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TFF	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TFG	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TKA	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TKB	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TKC	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TKE	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TKF	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX66T	R5F566TKG	✓ (2 wire UART, FINE)	R5F566TK.pr6	
RX	RX671	R5F56719	✓ (2 wire UART, FINE)	R5F5671 D.pr6	Dual Mode
RX	RX671	R5F56719	✓ (2 wire UART, FINE)	R5F5671 L.pr6	Linear Mode
RX	RX671	R5F5671C	✓ (2 wire UART, FINE)	R5F5671 D.pr6	Dual Mode
RX	RX671	R5F5671C	✓ (2 wire UART, FINE)	R5F5671 L.pr6	Linear Mode
RX	RX671	R5F5671E	✓ (2 wire UART, FINE)	R5F5671 D.pr6	Dual Mode
RX	RX671	R5F5671E	✓ (2 wire UART, FINE)	R5F5671 L.pr6	Linear Mode
RX	RX71M	R5F571MF	✓ (2 wire UART)	R5F571M.pr6	
RX	RX71M	R5F571MG	✓ (2 wire UART)	R5F571M.pr6	
RX	RX71M	R5F571MJ	✓ (2 wire UART)	R5F571M.pr6	
RX	RX71M	R5F571ML	✓ (2 wire UART)	R5F571M.pr6	
RX	RX72M	R5F572MD	✓ (2 wire UART, FINE)	R5F572M D.pr6	Dual Mode
RX	RX72M	R5F572MD	✓ (2 wire UART, FINE)	R5F572M L.pr6	Linear Mode
RX	RX72M	R5F572MN	✓ (2 wire UART, FINE)	R5F572M D.pr6	Dual Mode
RX	RX72M	R5F572MN	✓ (2 wire UART, FINE)	R5F572M L.pr6	Linear Mode
RX	RX72N	R5F572ND	✓ (2 wire UART, FINE)	R5F572N D.pr6	Dual Mode
RX	RX72N	R5F572ND	✓ (2 wire UART, FINE)	R5F572N L.pr6	Linear Mode
RX	RX72N	R5F572NN	✓ (2 wire UART, FINE)	R5F572N D.pr6	Dual Mode
RX	RX72N	R5F572NN	✓ (2 wire UART, FINE)	R5F572N L.pr6	Linear Mode
RX	RX72T	R5F572TFA	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TFB	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TFC	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TFE	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TFF	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TFG	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TKA	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TKB	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TKC	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TKE	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TKF	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RX	RX72T	R5F572TKG	✓ (2 wire UART, FINE)	R5F572TK.pr6	
RH850	RH850/C1H	R7F701270	✓ (2 wire UART, CSI)	R7F701270.pr6	
RH850	RH850/C1M	R7F701271	✓ (2 wire UART, CSI)	R7F701271.pr6	
RH850	RH850/C1M-A	R7F701275	✓ (2 wire UART, CSI)	R7F701275.pr6	
RH850	RH850/C1M-A	R7F701278	✓ (2 wire UART, CSI)	R7F701278.pr6	
RH850	RH850/D1L	R7F701401	✓ (1 wire UART, 2 wire UART, CSI)	R7F701401.pr6	
RH850	RH850/D1L	R7F701402	✓ (1 wire UART, 2 wire UART, CSI)	R7F701402.pr6	
RH850	RH850/D1L	R7F701403	✓ (1 wire UART, 2 wire UART, CSI)	R7F701403.pr6	
RH850	RH850/D1L	R7F701421	✓ (1 wire UART, 2 wire UART, CSI)	R7F701421.pr6	
RH850	RH850/D1L	R7F701422	✓ (1 wire UART, 2 wire UART, CSI)	R7F701422.pr6	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RH850	RH850/D1L	R7F701423	✓ (1 wire UART, 2 wire UART, CSI)	R7F701423.pr6	
RH850	RH850/D1M	R7F701404	✓ (1 wire UART, 2 wire UART, CSI)	R7F701404.pr6	
RH850	RH850/D1M	R7F701405	✓ (1 wire UART, 2 wire UART, CSI)	R7F701405.pr6	
RH850	RH850/D1M	R7F701406	✓ (1 wire UART, 2 wire UART, CSI)	R7F701406.pr6	
RH850	RH850/D1M	R7F701407	✓ (1 wire UART, 2 wire UART, CSI)	R7F701407.pr6	
RH850	RH850/D1M	R7F701408	✓ (1 wire UART, 2 wire UART, CSI)	R7F701408.pr6	
RH850	RH850/D1M	R7F701410	✓ (1 wire UART, 2 wire UART, CSI)	R7F701410.pr6	
RH850	RH850/D1M	R7F701411	✓ (1 wire UART, 2 wire UART, CSI)	R7F701411.pr6	
RH850	RH850/D1M	R7F701412	✓ (1 wire UART, 2 wire UART, CSI)	R7F701412.pr6	
RH850	RH850/D1M	R7F701428	✓ (1 wire UART, 2 wire UART, CSI)	R7F701428.pr6	
RH850	RH850/D1M	R7F701430	✓ (1 wire UART, 2 wire UART, CSI)	R7F701430.pr6	
RH850	RH850/D1M	R7F701431	✓ (1 wire UART, 2 wire UART, CSI)	R7F701431.pr6	
RH850	RH850/D1M	R7F701432	✓ (1 wire UART, 2 wire UART, CSI)	R7F701432.pr6	
RH850	RH850/D1M	R7F701441	✓ (1 wire UART, 2 wire UART, CSI)	R7F701441.pr6	
RH850	RH850/D1M	R7F701442	✓ (1 wire UART, 2 wire UART, CSI)	R7F701442.pr6	
RH850	RH850/D1M	R7F701461	✓ (1 wire UART, 2 wire UART, CSI)	R7F701461.pr6	
RH850	RH850/D1M	R7F701462	✓ (1 wire UART, 2 wire UART, CSI)	R7F701462.pr6	
RH850	-	R7F701417	✓ (1 wire UART, 2 wire UART, CSI)	R7F701417.pr6	
RH850	-	R7F701437	✓ (1 wire UART, 2 wire UART, CSI)	R7F701437.pr6	
RH850	RH850/E1L	R7F701201	✓ (2 wire UART, CSI)	R7F701201.pr6	
RH850	RH850/E1L	R7F701205	✓ (2 wire UART, CSI)	R7F701205.pr6	
RH850	RH850/E1M-S	R7F701202	✓ (2 wire UART, CSI)	R7F701202.pr6	
RH850	RH850/E1M-S	R7F701204	✓ (2 wire UART, CSI)	R7F701204.pr6	
RH850	-	R7F701Z05A	✓ (2 wire UART, CSI)	R7F701Z05.pr6	
RH850	-	R7F701Z06A	✓ (2 wire UART, CSI)	R7F701Z06.pr6	
RH850	-	R7F701Z07A	✓ (2 wire UART, CSI)	R7F701Z07.pr6	
RH850	RH850/E1M-S2	R7F701215	✓ (2 wire UART, CSI)	R7F701215.pr6	
RH850	RH850/E1M-S2	R7F701216	✓ (2 wire UART, CSI)	R7F701216.pr6	
RH850	-	R7F701Z11	✓ (2 wire UART, CSI)	R7F701Z11.pr6	
RH850	-	R7F701Z12	✓ (2 wire UART, CSI)	R7F701Z12.pr6	
RH850	-	R7F701Z12A	✓ (2 wire UART, CSI)	R7F701Z12.pr6	
RH850	RH850/E2M	R7F702002A	✓ (2 wire UART, CSI)	R7F702002.pr6	
RH850	-	R7F702Z02C	✓ (2 wire UART, CSI)	R7F702Z02.pr6	
RH850	-	R7F702Z04C	✓ (2 wire UART, CSI)	R7F702Z04.pr6	
RH850	RH850/E2H	R7F702011	✓ (2 wire UART, CSI)	R7F702011 C.pr6	Compatible
RH850	RH850/E2H	R7F702011	✓ (2 wire UART, CSI)	R7F702011 S.pr6	Single map
RH850	RH850/E2H	R7F702011	✓ (2 wire UART, CSI)	R7F702011 D.pr6	Double map
RH850	RH850/E2UH	R7F702012A	✓ (2 wire UART, CSI)	R7F702012 C.pr6	Compatible
RH850	RH850/E2UH	R7F702012A	✓ (2 wire UART, CSI)	R7F702012 S.pr6	Single map
RH850	RH850/E2UH	R7F702012A	✓ (2 wire UART, CSI)	R7F702012 D.pr6	Double map
RH850	-	R7F702Z11A	✓ (2 wire UART, CSI)	R7F702Z11.pr6	
RH850	-	R7F702Z12A	✓ (2 wire UART, CSI)	R7F702Z12.pr6	
RH850	RH850/F1H	R7F701501	✓ (1 wire UART, 2 wire UART, CSI)	R7F701501.pr6	
RH850	RH850/F1H	R7F701502	✓ (1 wire UART, 2 wire UART, CSI)	R7F701502.pr6	
RH850	RH850/F1H	R7F701503	✓ (1 wire UART, 2 wire UART, CSI)	R7F701503.pr6	
RH850	RH850/F1H	R7F701506	✓ (1 wire UART, 2 wire UART, CSI)	R7F701506.pr6	
RH850	RH850/F1H	R7F701507	✓ (1 wire UART, 2 wire UART, CSI)	R7F701507.pr6	
RH850	RH850/F1H	R7F701508	✓ (1 wire UART, 2 wire UART, CSI)	R7F701508.pr6	
RH850	RH850/F1H	R7F701511	✓ (1 wire UART, 2 wire UART, CSI)	R7F701511.pr6	
RH850	RH850/F1H	R7F701512	✓ (1 wire UART, 2 wire UART, CSI)	R7F701512.pr6	
RH850	RH850/F1H	R7F701513	✓ (1 wire UART, 2 wire UART, CSI)	R7F701513.pr6	
RH850	RH850/F1H	R7F701521	✓ (1 wire UART, 2 wire UART, CSI)	R7F701521.pr6	
RH850	RH850/F1H	R7F701522	✓ (1 wire UART, 2 wire UART, CSI)	R7F701522.pr6	
RH850	RH850/F1H	R7F701524	✓ (1 wire UART, 2 wire UART, CSI)	R7F701524.pr6	
RH850	RH850/F1H	R7F701525	✓ (1 wire UART, 2 wire UART, CSI)	R7F701525.pr6	
RH850	RH850/F1H	R7F701526	✓ (1 wire UART, 2 wire UART, CSI)	R7F701526.pr6	
RH850	RH850/F1H	R7F701527	✓ (1 wire UART, 2 wire UART, CSI)	R7F701527.pr6	
RH850	RH850/F1H	R7F701528	✓ (1 wire UART, 2 wire UART, CSI)	R7F701528.pr6	
RH850	RH850/F1H	R7F701529	✓ (1 wire UART, 2 wire UART, CSI)	R7F701529.pr6	
RH850	RH850/F1H	R7F701530	✓ (1 wire UART, 2 wire UART, CSI)	R7F701530.pr6	
RH850	RH850/F1H	R7F701531	✓ (1 wire UART, 2 wire UART, CSI)	R7F701531.pr6	
RH850	RH850/F1H	R7F701534	✓ (1 wire UART, 2 wire UART, CSI)	R7F701534.pr6	
RH850	RH850/F1K	R7F701542	✓ (1 wire UART, 2 wire UART, CSI)	R7F701542.pr6	
RH850	RH850/F1K	R7F701543	✓ (1 wire UART, 2 wire UART, CSI)	R7F701543.pr6	
RH850	RH850/F1K	R7F701546	✓ (1 wire UART, 2 wire UART, CSI)	R7F701546.pr6	
RH850	RH850/F1K	R7F701547	✓ (1 wire UART, 2 wire UART, CSI)	R7F701547.pr6	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RH850	RH850/F1M	R7F701545	✓ (1 wire UART, 2 wire UART, CSI)	R7F701545.pr6	
RH850	RH850/F1M	R7F701548	✓ (1 wire UART, 2 wire UART, CSI)	R7F701548.pr6	
RH850	RH850/F1M	R7F701549	✓ (1 wire UART, 2 wire UART, CSI)	R7F701549.pr6	
RH850	RH850/F1M	R7F701552	✓ (1 wire UART, 2 wire UART, CSI)	R7F701552.pr6	
RH850	RH850/F1M	R7F701553	✓ (1 wire UART, 2 wire UART, CSI)	R7F701553.pr6	
RH850	RH850/F1M	R7F701564	✓ (1 wire UART, 2 wire UART, CSI)	R7F701564.pr6	
RH850	RH850/F1M	R7F701565	✓ (1 wire UART, 2 wire UART, CSI)	R7F701565.pr6	
RH850	RH850/F1M	R7F701568	✓ (1 wire UART, 2 wire UART, CSI)	R7F701568.pr6	
RH850	RH850/F1M	R7F701569	✓ (1 wire UART, 2 wire UART, CSI)	R7F701569.pr6	
RH850	RH850/F1M	R7F701572	✓ (1 wire UART, 2 wire UART, CSI)	R7F701572.pr6	
RH850	RH850/F1M	R7F701573	✓ (1 wire UART, 2 wire UART, CSI)	R7F701573.pr6	
RH850	RH850/F1M	R7F701589	✓ (1 wire UART, 2 wire UART, CSI)	R7F701589.pr6	
RH850	RH850/P1H-C	R7F701371	✓ (1 wire UART, 2 wire UART, CSI)	R7F701371.pr6	
RH850	RH850/P1H-C	R7F701372	✓ (1 wire UART, 2 wire UART, CSI)	R7F701372.pr6	
RH850	RH850/P1H-C	R7F701372A	✓ (1 wire UART, 2 wire UART, CSI)	R7F701372A.pr6	
RH850	RH850/P1H-C	R7F701396A	✓ (1 wire UART, 2 wire UART, CSI)	R7F701396A.pr6	
RH850	RH850/P1L-C	R7F701388	✓ (1 wire UART, 2 wire UART, CSI)	R7F701388.pr6	
RH850	RH850/P1L-C	R7F701389	✓ (1 wire UART, 2 wire UART, CSI)	R7F701389.pr6	
RH850	RH850/P1L-C	R7F701390	✓ (1 wire UART, 2 wire UART, CSI)	R7F701390.pr6	
RH850	RH850/P1L-C	R7F701391	✓ (1 wire UART, 2 wire UART, CSI)	R7F701391.pr6	
RH850	RH850/P1M	R7F701304	✓ (1 wire UART, 2 wire UART, CSI)	R7F701304.pr6	
RH850	RH850/P1M	R7F701305	✓ (1 wire UART, 2 wire UART, CSI)	R7F701305.pr6	
RH850	RH850/P1M	R7F701310	✓ (1 wire UART, 2 wire UART, CSI)	R7F701310.pr6	
RH850	RH850/P1M	R7F701311	✓ (1 wire UART, 2 wire UART, CSI)	R7F701311.pr6	
RH850	RH850/P1M	R7F701312	✓ (1 wire UART, 2 wire UART, CSI)	R7F701312.pr6	
RH850	RH850/P1M	R7F701313	✓ (1 wire UART, 2 wire UART, CSI)	R7F701313.pr6	
RH850	RH850/P1M	R7F701314	✓ (1 wire UART, 2 wire UART, CSI)	R7F701314.pr6	
RH850	RH850/P1M	R7F701315	✓ (1 wire UART, 2 wire UART, CSI)	R7F701315.pr6	
RH850	RH850/P1M	R7F701318	✓ (1 wire UART, 2 wire UART, CSI)	R7F701318.pr6	
RH850	RH850/P1M	R7F701319	✓ (1 wire UART, 2 wire UART, CSI)	R7F701319.pr6	
RH850	RH850/P1M	R7F701320	✓ (1 wire UART, 2 wire UART, CSI)	R7F701320.pr6	
RH850	RH850/P1M	R7F701321	✓ (1 wire UART, 2 wire UART, CSI)	R7F701321.pr6	
RH850	RH850/P1M	R7F701322	✓ (1 wire UART, 2 wire UART, CSI)	R7F701322.pr6	
RH850	RH850/P1M	R7F701323	✓ (1 wire UART, 2 wire UART, CSI)	R7F701323.pr6	
RH850	RH850/P1M-C	R7F701373	✓ (1 wire UART, 2 wire UART, CSI)	R7F701373.pr6	
RH850	RH850/P1M-C	R7F701373A	✓ (1 wire UART, 2 wire UART, CSI)	R7F701373A.pr6	
RH850	RH850/P1M-C	R7F701374	✓ (1 wire UART, 2 wire UART, CSI)	R7F701374.pr6	
RH850	RH850/P1M-C	R7F701374A	✓ (1 wire UART, 2 wire UART, CSI)	R7F701374A.pr6	
RH850	RH850/P1M-C	R7F701397A	✓ (1 wire UART, 2 wire UART, CSI)	R7F701397A.pr6	
RH850	RH850/P1M-E	R7F701375	✓ (1 wire UART, 2 wire UART, CSI)	R7F701375.pr6	
RH850	RH850/P1M-E	R7F701376	✓ (1 wire UART, 2 wire UART, CSI)	R7F701376.pr6	
RH850	RH850/P1M-E	R7F701377	✓ (1 wire UART, 2 wire UART, CSI)	R7F701377.pr6	
RH850	RH850/P1M-E	R7F701378	✓ (1 wire UART, 2 wire UART, CSI)	R7F701378.pr6	
RH850	RH850/P1M-E	R7F701379	✓ (1 wire UART, 2 wire UART, CSI)	R7F701379.pr6	
RH850	RH850/P1M-E	R7F701380	✓ (1 wire UART, 2 wire UART, CSI)	R7F701380.pr6	
RH850	RH850/P1M-E	R7F701381	✓ (1 wire UART, 2 wire UART, CSI)	R7F701381.pr6	
RH850	RH850/P1M-E	R7F701382	✓ (1 wire UART, 2 wire UART, CSI)	R7F701382.pr6	
RH850	RH850/P1M-E	R7F701383	✓ (1 wire UART, 2 wire UART, CSI)	R7F701383.pr6	
RH850	RH850/P1M-E	R7F701384	✓ (1 wire UART, 2 wire UART, CSI)	R7F701384.pr6	
RH850	RH850/P1M-E	R7F701385	✓ (1 wire UART, 2 wire UART, CSI)	R7F701385.pr6	
RH850	RH850/P1M-E	R7F701386	✓ (1 wire UART, 2 wire UART, CSI)	R7F701386.pr6	
RH850	-	R7F701062	✓ (2 wire UART, CSI)	R7F701062.pr6	
RH850	-	R7F701064	✓ (2 wire UART, CSI)	R7F701064.pr6	
RH850	-	R7F701067	✓ (2 wire UART, CSI)	R7F701067.pr6	
RH850	-	R7F701069	✓ (2 wire UART, CSI)	R7F701069.pr6	
RH850	-	R7F701071	✓ (2 wire UART, CSI)	R7F701071.pr6	
RH850	RH850/U2A6	R7F702302	✓ (2 wire UART, CSI)	R7F702302 S.pr6	Single map
RH850	RH850/U2A6	R7F702302	✓ (2 wire UART, CSI)	R7F702302 D.pr6	Double map
RH850	RH850/U2A8	R7F702301	✓ (2 wire UART, CSI)	R7F702301 S.pr6	Single map
RH850	RH850/U2A8	R7F702301	✓ (2 wire UART, CSI)	R7F702301 D.pr6	Double map
RH850	RH850/U2A8	R7F702301A	✓ (2 wire UART, CSI)	R7F702301 S.pr6	Single map
RH850	RH850/U2A8	R7F702301A	✓ (2 wire UART, CSI)	R7F702301 D.pr6	Double map
RH850	RH850/U2A8	R7F702301B	✓ (2 wire UART, CSI)	R7F702301 S.pr6	Single map
RH850	RH850/U2A8	R7F702301B	✓ (2 wire UART, CSI)	R7F702301 D.pr6	Double map
RH850	RH850/U2A16	R7F702300	✓ (2 wire UART, CSI)	R7F702300 S.pr6	Single map
RH850	RH850/U2A16	R7F702300	✓ (2 wire UART, CSI)	R7F702300 D.pr6	Double map

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
RH850	RH850/U2A16	R7F702300A	✓ (2 wire UART, CSI)	R7F702300_S.pr6	Single map
RH850	RH850/U2A16	R7F702300A	✓ (2 wire UART, CSI)	R7F702300_D.pr6	Double map
RH850	RH850/U2A16	R7F702300B	✓ (2 wire UART, CSI)	R7F702300_S.pr6	Single map
RH850	RH850/U2A16	R7F702300B	✓ (2 wire UART, CSI)	R7F702300_D.pr6	Double map
RH850	RH850/U2A-EVA	R7F702Z19A	✓ (2 wire UART, CSI)	R7F702Z19_S.pr6	Single map
RH850	RH850/U2A-EVA	R7F702Z19A	✓ (2 wire UART, CSI)	R7F702Z19_D.pr6	Double map
RH850	RH850/U2A-EVA	R7F702Z19B	✓ (2 wire UART, CSI)	R7F702Z19_S.pr6	Single map
RH850	RH850/U2A-EVA	R7F702Z19B	✓ (2 wire UART, CSI)	R7F702Z19_D.pr6	Double map
RH850	RH850/U2B6	R7F70255x	✓ (2 wire UART, CSI)	R7F70255x_S.pr6	Single map
RH850	RH850/U2B6	R7F70255x	✓ (2 wire UART, CSI)	R7F70255x_D.pr6	Double map
RH850	RH850/U2B10	R7F70254x	✓ (2 wire UART, CSI)	R7F70254x_S.pr6	Single map
RH850	RH850/U2B10	R7F70254x	✓ (2 wire UART, CSI)	R7F70254x_D.pr6	Double map
RH850	RH850/U2B-FCC	R7F702Z21	✓ (2 wire UART, CSI)	R7F702Z21_S.pr6	Single map
RH850	RH850/U2B-FCC	R7F702Z21	✓ (2 wire UART, CSI)	R7F702Z21_D.pr6	Double map
RH850	RH850/U2B-FCC	R7F702Z22	✓ (2 wire UART, CSI)	R7F702Z22_S.pr6	Single map
RH850	RH850/U2B-FCC	R7F702Z22	✓ (2 wire UART, CSI)	R7F702Z22_D.pr6	Double map
RH850	RH850/U2B-FCC	R7F702Z23	✓ (2 wire UART, CSI)	R7F702Z23_S.pr6	Single map
RH850	RH850/U2B-FCC	R7F702Z23	✓ (2 wire UART, CSI)	R7F702Z23_D.pr6	Double map
RH850	RH850/U2B-FCC	R7F702Z26	✓ (2 wire UART, CSI)	R7F702Z26_S.pr6	Single map
RH850	RH850/U2B-FCC	R7F702Z26	✓ (2 wire UART, CSI)	R7F702Z26_D.pr6	Double map
RH850	RH850/U2B-FCC	R7F702Z28	✓ (2 wire UART, CSI)	R7F702Z28_S.pr6	Single map
RH850	RH850/U2B-FCC	R7F702Z28	✓ (2 wire UART, CSI)	R7F702Z28_D.pr6	Double map
RISC-V MCU	G021	R9A02G021	✓ (2 wire UART)	R9A02G021.pr6	
Renesas Synergy	S124	R7FS12476	✓ (2 wire UART)	R7FS12476.pr6	
Renesas Synergy	S124	R7FS12477	✓ (2 wire UART)	R7FS12477.pr6	
Renesas Synergy	S128	R7FS12878	✓ (2 wire UART)	R7FS12878.pr6	
Renesas Synergy	S1JA	R7FS1JA78	✓ (2 wire UART)	R7FS1JA78.pr6	
Renesas Synergy	S3A1	R7FS3A17C	✓ (2 wire UART)	R7FS3A17C.pr6	
Renesas Synergy	S3A3	R7FS3A37A	✓ (2 wire UART)	R7FS3A37A.pr6	
Renesas Synergy	S3A6	R7FS3A678	✓ (2 wire UART)	R7FS3A678.pr5	
Renesas Synergy	S3A7	R7FS3A77C	✓ (2 wire UART)	R7FS3A77C.pr5	
Renesas Synergy	S5D3	R7FS5D37A	✓ (2 wire UART)	R7FS5D37A.pr6	
Renesas Synergy	S5D5	R7FS5D57A	✓ (2 wire UART)	R7FS5D57A.pr6	
Renesas Synergy	S5D5	R7FS5D57C	✓ (2 wire UART)	R7FS5D57C.pr6	
Renesas Synergy	S5D9	R7FS5D97C	✓ (2 wire UART)	R7FS5D97C.pr6	
Renesas Synergy	S5D9	R7FS5D97E	✓ (2 wire UART)	R7FS5D97E.pr6	
Renesas Synergy	S7G2	R7FS7G27G	✓ (2 wire UART)	R7FS7G27G.pr6	
Renesas Synergy	S7G2	R7FS7G27H	✓ (2 wire UART)	R7FS7G27H.pr6	
RE	RE01 256KB	R7F0E0108	✓ (2 wire UART)	R7F0E0108.pr6	
RE	RE01 256KB	R7F0E0118	✓ (2 wire UART)	R7F0E0118.pr6	
RE	RE01 1500KB	R7F0E014D	✓ (2 wire UART)	R7F0E01.pr6	
RE	RE01 1500KB	R7F0E015D	✓ (2 wire UART)	R7F0E01.pr6	
RE	RE01 1500KB	R7F0E016D	✓ (2 wire UART)	R7F0E01.pr6	
RE	RE01 1500KB	R7F0E017D	✓ (2 wire UART)	R7F0E01.pr6	
RE	RE01B	R7F0E01BD	✓ (2 wire UART)	R7F0E01.pr6	
Power Management	Battery Management	RAJ240045	✓ (1 wire UART)	RAJ240045.pr5	
Power Management	Battery Management	RAJ240047	✓ (1 wire UART)	RAJ240047.pr5	
Power Management	Battery Management	RAJ240055	✓ (1 wire UART)	RAJ240055.pr5	
Power Management	Battery Management	RAJ240057	✓ (1 wire UART)	RAJ240057.pr5	
Power Management	Battery Management	RAJ240071	✓ (1 wire UART)	RAJ240071.pr5	
Power Management	Battery Management	RAJ240075	✓ (1 wire UART)	RAJ240075.pr5	
Power Management	Battery Management	RAJ240080	✓ (1 wire UART)	RAJ240080.pr5	
Power Management	Battery Management	RAJ240090	✓ (1 wire UART)	RAJ240090.pr5	
Power Management	Battery Management	RAJ240100	✓ (1 wire UART)	RAJ240100.pr5	
Power Management	Battery Management	RAJ240310	✓ (1 wire UART)	RAJ240310.pr5	
Power Management	Battery Management	RAJ240500	✓ (1 wire UART)	RAJ240500.pr5	
Renesas USB Power Delivery	C30	R9A02G011	✓ (1 wire UART)	R9A02G011.pr5	
Renesas USB Power Delivery	C30	R9J02G012	✓ (1 wire UART)	R9J02G012.pr5	
Renesas USB Power Delivery	C30	R9A02G0151	✓ (1 wire UART)	R9A02G0151.pr5	
ICs for Motor Driver/Actuator Driver	ICs for Motor Control	RAJ306000	✓ (1 wire UART)	RAJ306000.pr5	
78K0	78K0/LC3	UPD78F0400	✓	78F0400.pr5	
78K0	78K0/LC3	UPD78F0401	✓	78F0401.pr5	
78K0	78K0/LC3	UPD78F0402	✓	78F0402.pr5	
78K0	78K0/LC3	UPD78F0403	✓	78F0403.pr5	
78K0	78K0/LC3	UPD78F0410	✓	78F0410.pr5	
78K0	78K0/LC3	UPD78F0411	✓	78F0411.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0	78K0/LC3	UPD78F0412	✓	78F0412.pr5	
78K0	78K0/LC3	UPD78F0413	✓	78F0413.pr5	
78K0	78K0/LD3	UPD78F0420	✓	78F0420.pr5	
78K0	78K0/LD3	UPD78F0421	✓	78F0421.pr5	
78K0	78K0/LD3	UPD78F0422	✓	78F0422.pr5	
78K0	78K0/LD3	UPD78F0423	✓	78F0423.pr5	
78K0	78K0/LD3	UPD78F0430	✓	78F0430.pr5	
78K0	78K0/LD3	UPD78F0431	✓	78F0431.pr5	
78K0	78K0/LD3	UPD78F0432	✓	78F0432.pr5	
78K0	78K0/LD3	UPD78F0433	✓	78F0433.pr5	
78K0	78K0/LE3	UPD78F0441	✓	78F0441.pr5	
78K0	78K0/LE3	UPD78F0442	✓	78F0442.pr5	
78K0	78K0/LE3	UPD78F0443	✓	78F0443.pr5	
78K0	78K0/LE3	UPD78F0444	✓	78F0444.pr5	
78K0	78K0/LE3	UPD78F0445	✓	78F0445.pr5	
78K0	78K0/LE3	UPD78F0451	✓	78F0451.pr5	
78K0	78K0/LE3	UPD78F0452	✓	78F0452.pr5	
78K0	78K0/LE3	UPD78F0453	✓	78F0453.pr5	
78K0	78K0/LE3	UPD78F0454	✓	78F0454.pr5	
78K0	78K0/LE3	UPD78F0455	✓	78F0455.pr5	
78K0	78K0/LE3	UPD78F0461	✓	78F0461.pr5	
78K0	78K0/LE3	UPD78F0462	✓	78F0462.pr5	
78K0	78K0/LE3	UPD78F0463	✓	78F0463.pr5	
78K0	78K0/LE3	UPD78F0464	✓	78F0464.pr5	
78K0	78K0/LE3	UPD78F0465	✓	78F0465.pr5	
78K0	78K0/LF3	UPD78F0471	✓	78F0471.pr5	
78K0	78K0/LF3	UPD78F0472	✓	78F0472.pr5	
78K0	78K0/LF3	UPD78F0473	✓	78F0473.pr5	
78K0	78K0/LF3	UPD78F0474	✓	78F0474.pr5	
78K0	78K0/LF3	UPD78F0475	✓	78F0475.pr5	
78K0	78K0/LF3	UPD78F0481	✓	78F0481.pr5	
78K0	78K0/LF3	UPD78F0482	✓	78F0482.pr5	
78K0	78K0/LF3	UPD78F0483	✓	78F0483.pr5	
78K0	78K0/LF3	UPD78F0484	✓	78F0484.pr5	
78K0	78K0/LF3	UPD78F0485	✓	78F0485.pr5	
78K0	78K0/LF3	UPD78F0491	✓	78F0491.pr5	
78K0	78K0/LF3	UPD78F0492	✓	78F0492.pr5	
78K0	78K0/LF3	UPD78F0493	✓	78F0493.pr5	
78K0	78K0/LF3	UPD78F0494	✓	78F0494.pr5	
78K0	78K0/LF3	UPD78F0495	✓	78F0495.pr5	
78K0	78K0/KB2	UPD78F0500	✓	78F0500.pr5	
78K0	78K0/KB2	UPD78F0500A	✓	78F0500A.pr5	
78K0	78K0/KB2	UPD78F0501	✓	78F0501.pr5	
78K0	78K0/KB2	UPD78F0501A	✓	78F0501A.pr5	
78K0	78K0/KB2	UPD78F0502	✓	78F0502.pr5	
78K0	78K0/KB2	UPD78F0502A	✓	78F0502A.pr5	
78K0	78K0/KB2	UPD78F0503	✓	78F0503.pr5	
78K0	78K0/KB2	UPD78F0503A	✓	78F0503A.pr5	
78K0	78K0/KB2	UPD78F0503D	✓	78F0503D.pr5	
78K0	78K0/KB2	UPD78F0503DA	✓	78F0503DA.pr5	
78K0	78K0/KC2	UPD78F0511	✓	78F0511.pr5	
78K0	78K0/KC2	UPD78F0511A	✓	78F0511A.pr5	
78K0	78K0/KC2	UPD78F0512	✓	78F0512.pr5	
78K0	78K0/KC2	UPD78F0512A	✓	78F0512A.pr5	
78K0	78K0/KC2	UPD78F0513	✓	78F0513.pr5	
78K0	78K0/KC2	UPD78F0513A	✓	78F0513A.pr5	
78K0	78K0/KC2	UPD78F0513D	✓	78F0513D.pr5	
78K0	78K0/KC2	UPD78F0513DA	✓	78F0513DA.pr5	
78K0	78K0/KC2	UPD78F0514	✓	78F0514.pr5	
78K0	78K0/KC2	UPD78F0514A	✓	78F0514A.pr5	
78K0	78K0/KC2	UPD78F0515	✓	78F0515.pr5	
78K0	78K0/KC2	UPD78F0515A	✓	78F0515A.pr5	
78K0	78K0/KC2	UPD78F0515D	✓	78F0515D.pr5	
78K0	78K0/KC2	UPD78F0515DA	✓	78F0515DA.pr5	
78K0	78K0/KD2	UPD78F0521	✓	78F0521.pr5	
78K0	78K0/KD2	UPD78F0521A	✓	78F0521A.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0	78K0/KD2	UPD78F0522	✓	78F0522.pr5	
78K0	78K0/KD2	UPD78F0522A	✓	78F0522A.pr5	
78K0	78K0/KD2	UPD78F0523	✓	78F0523.pr5	
78K0	78K0/KD2	UPD78F0523A	✓	78F0523A.pr5	
78K0	78K0/KD2	UPD78F0524	✓	78F0524.pr5	
78K0	78K0/KD2	UPD78F0524A	✓	78F0524A.pr5	
78K0	78K0/KD2	UPD78F0525	✓	78F0525.pr5	
78K0	78K0/KD2	UPD78F0525A	✓	78F0525A.pr5	
78K0	78K0/KD2	UPD78F0526	✓	78F0526.pr5	
78K0	78K0/KD2	UPD78F0526A	✓	78F0526A.pr5	
78K0	78K0/KD2	UPD78F0527	✓	78F0527.pr5	
78K0	78K0/KD2	UPD78F0527A	✓	78F0527A.pr5	
78K0	78K0/KD2	UPD78F0527DA	✓	78F0527DA.pr5	
78K0	78K0/KE2	UPD78F0531	✓	78F0531.pr5	
78K0	78K0/KE2	UPD78F0531A	✓	78F0531A.pr5	
78K0	78K0/KE2	UPD78F0532	✓	78F0532.pr5	
78K0	78K0/KE2	UPD78F0532A	✓	78F0532A.pr5	
78K0	78K0/KE2	UPD78F0533	✓	78F0533.pr5	
78K0	78K0/KE2	UPD78F0533A	✓	78F0533A.pr5	
78K0	78K0/KE2	UPD78F0534	✓	78F0534.pr5	
78K0	78K0/KE2	UPD78F0534A	✓	78F0534A.pr5	
78K0	78K0/KE2	UPD78F0535	✓	78F0535.pr5	
78K0	78K0/KE2	UPD78F0535A	✓	78F0535A.pr5	
78K0	78K0/KE2	UPD78F0536	✓	78F0536.pr5	
78K0	78K0/KE2	UPD78F0536A	✓	78F0536A.pr5	
78K0	78K0/KE2	UPD78F0537	✓	78F0537.pr5	
78K0	78K0/KE2	UPD78F0537A	✓	78F0537A.pr5	
78K0	78K0/KE2	UPD78F0537D	✓	78F0537D.pr5	
78K0	78K0/KE2	UPD78F0537DA	✓	78F0537DA.pr5	
78K0	78K0/KF2	UPD78F0544	✓	78F0544.pr5	
78K0	78K0/KF2	UPD78F0544A	✓	78F0544A.pr5	
78K0	78K0/KF2	UPD78F0545	✓	78F0545.pr5	
78K0	78K0/KF2	UPD78F0545A	✓	78F0545A.pr5	
78K0	78K0/KF2	UPD78F0546	✓	78F0546.pr5	
78K0	78K0/KF2	UPD78F0546A	✓	78F0546A.pr5	
78K0	78K0/KF2	UPD78F0547	✓	78F0547.pr5	
78K0	78K0/KF2	UPD78F0547A	✓	78F0547A.pr5	
78K0	78K0/KF2	UPD78F0547D	✓	78F0547D.pr5	
78K0	78K0/KF2	UPD78F0547DA	✓	78F0547DA.pr5	
78K0	78K0/FC2	UPD78F0881	✓	78F0881.pr5	
78K0	78K0/FC2	UPD78F0881A	✓	78F0881A.pr5	
78K0	78K0/FC2	UPD78F0882	✓	78F0882.pr5	
78K0	78K0/FC2	UPD78F0882A	✓	78F0882A.pr5	
78K0	78K0/FC2	UPD78F0883	✓	78F0883.pr5	
78K0	78K0/FC2	UPD78F0883A	✓	78F0883A.pr5	
78K0	78K0/FC2	UPD78F0884	✓	78F0884.pr5	
78K0	78K0/FC2	UPD78F0884A	✓	78F0884A.pr5	
78K0	78K0/FC2	UPD78F0885	✓	78F0885.pr5	
78K0	78K0/FC2	UPD78F0885A	✓	78F0885A.pr5	
78K0	78K0/FC2	UPD78F0886	✓	78F0886.pr5	
78K0	78K0/FC2	UPD78F0886A	✓	78F0886A.pr5	
78K0	78K0/FC2	UPD78F0894A	✓	78F0894A.pr5	
78K0	78K0/FC2	UPD78F0895A	✓	78F0895A.pr5	
78K0	78K0/FE2	UPD78F0887	✓	78F0887.pr5	
78K0	78K0/FE2	UPD78F0887A	✓	78F0887A.pr5	
78K0	78K0/FE2	UPD78F0888	✓	78F0888.pr5	
78K0	78K0/FE2	UPD78F0888A	✓	78F0888A.pr5	
78K0	78K0/FE2	UPD78F0889	✓	78F0889.pr5	
78K0	78K0/FE2	UPD78F0889A	✓	78F0889A.pr5	
78K0	78K0/FE2	UPD78F0890	✓	78F0890.pr5	
78K0	78K0/FE2	UPD78F0890A	✓	78F0890A.pr5	
78K0	78K0/FF2	UPD78F0891	✓	78F0891.pr5	
78K0	78K0/FF2	UPD78F0891A	✓	78F0891A.pr5	
78K0	78K0/FF2	UPD78F0892	✓	78F0892.pr5	
78K0	78K0/FF2	UPD78F0892A	✓	78F0892A.pr5	
78K0	78K0/FF2	UPD78F0893	✓	78F0893.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0	78K0/FF2	UPD78F0893A	✓	78F0893A.pr5	
78K0	78K0/KY2-L	UPD78F0550	✓	78F0550.pr5	
78K0	78K0/KY2-L	UPD78F0551	✓	78F0551.pr5	
78K0	78K0/KY2-L	UPD78F0552	✓	78F0552.pr5	
78K0	78K0/KY2-L	UPD78F0555	✓	78F0555.pr5	
78K0	78K0/KY2-L	UPD78F0556	✓	78F0556.pr5	
78K0	78K0/KY2-L	UPD78F0557	✓	78F0557.pr5	
78K0	78K0/KA2-L	UPD78F0560	✓	78F0560.pr5	
78K0	78K0/KA2-L	UPD78F0561	✓	78F0561.pr5	
78K0	78K0/KA2-L	UPD78F0562	✓	78F0562.pr5	
78K0	78K0/KA2-L	UPD78F0565	✓	78F0565.pr5	
78K0	78K0/KA2-L	UPD78F0566	✓	78F0566.pr5	
78K0	78K0/KA2-L	UPD78F0567	✓	78F0567.pr5	
78K0	78K0/KB2-L	UPD78F0571	✓	78F0571.pr5	
78K0	78K0/KB2-L	UPD78F0572	✓	78F0572.pr5	
78K0	78K0/KB2-L	UPD78F0573	✓	78F0573.pr5	
78K0	78K0/KB2-L	UPD78F0576	✓	78F0576.pr5	
78K0	78K0/KB2-L	UPD78F0577	✓	78F0577.pr5	
78K0	78K0/KB2-L	UPD78F0578	✓	78F0578.pr5	
78K0	78K0/KC2-L	UPD78F0581	✓	78F0581.pr5	
78K0	78K0/KC2-L	UPD78F0582	✓	78F0582.pr5	
78K0	78K0/KC2-L	UPD78F0583	✓	78F0583.pr5	
78K0	78K0/KC2-L	UPD78F0586	✓	78F0586.pr5	
78K0	78K0/KC2-L	UPD78F0587	✓	78F0587.pr5	
78K0	78K0/KC2-L	UPD78F0588	✓	78F0588.pr5	
78K0	78K0/IY2	UPD78F0740	✓	78F0740.pr5	
78K0	78K0/IY2	UPD78F0741	✓	78F0741.pr5	
78K0	78K0/IY2	UPD78F0742	✓	78F0742.pr5	
78K0	78K0/IY2	UPD78F0750	✓	78F0750.pr5	
78K0	78K0/IY2	UPD78F0751	✓	78F0751.pr5	
78K0	78K0/IY2	UPD78F0752	✓	78F0752.pr5	
78K0	78K0/IA2	UPD78F0743	✓	78F0743.pr5	
78K0	78K0/IA2	UPD78F0744	✓	78F0744.pr5	
78K0	78K0/IA2	UPD78F0753	✓	78F0753.pr5	
78K0	78K0/IA2	UPD78F0754	✓	78F0754.pr5	
78K0	78K0/IB2	UPD78F0745	✓	78F0745.pr5	
78K0	78K0/IB2	UPD78F0746	✓	78F0746.pr5	
78K0	78K0/IB2	UPD78F0755	✓	78F0755.pr5	
78K0	78K0/IB2	UPD78F0756	✓	78F0756.pr5	
78K0	78K0/LE3-M	UPD78F8053	✓	78F8053.pr5	
78K0	78K0/LG3-M	UPD78F8054	✓	78F8054.pr5	
78K0	78K0/LG3-M	UPD78F8055	✓	78F8055.pr5	
78K0	78K0/FY2-L	UPD78F0854	✓	78F0854.pr5	
78K0	78K0/FY2-L	UPD78F0855	✓	78F0855.pr5	
78K0	78K0/FY2-L	UPD78F0856	✓	78F0856.pr5	
78K0	78K0/FA2-L	UPD78F0857	✓	78F0857.pr5	
78K0	78K0/FA2-L	UPD78F0858	✓	78F0858.pr5	
78K0	78K0/FA2-L	UPD78F0859	✓	78F0859.pr5	
78K0	78K0/FB2-L	UPD78F0864	✓	78F0864.pr5	
78K0	78K0/FB2-L	UPD78F0865	✓	78F0865.pr5	
78K0	78K0/KB2-A	UPD78F0590	✓	78F0590.pr5	
78K0	78K0/KB2-A	UPD78F0591	✓	78F0591.pr5	
78K0	78K0/KC2-A	UPD78F0592	✓	78F0592.pr5	
78K0	78K0/KC2-A	UPD78F0593	✓	78F0593.pr5	
78K0	UPD78F0730	UPD78F0730	✓	78F0730.pr5	
78K0	78K0/KC2-C	UPD78F0760	✓	78F0760.pr5	
78K0	78K0/KC2-C	UPD78F0761	✓	78F0761.pr5	
78K0	78K0/KC2-C	UPD78F0762	✓	78F0762.pr5	
78K0	78K0/KE2-C	UPD78F0763	✓	78F0763.pr5	
78K0	78K0/KE2-C	UPD78F0764	✓	78F0764.pr5	
78K0	78K0/KE2-C	UPD78F0765	✓	78F0765.pr5	
78K0	78K0/DE2	UPD78F0836	✓	78F0836.pr5	
78K0	78K0/DE2	UPD78F0837	✓	78F0837.pr5	
78K0	78K0/DE2	UPD78F0844	✓	78F0844.pr5	
78K0	78K0/DE2	UPD78F0845	✓	78F0845.pr5	
78K0	78K0/DF2	UPD78F0838	✓	78F0838.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0	78K0/DF2	UPD78F0839	✓	78F0839.pr5	
78K0	78K0/DF2	UPD78F0840	✓	78F0840.pr5	
78K0	78K0/DF2	UPD78F0841	✓	78F0841.pr5	
78K0	78K0/DF2	UPD78F0842	✓	78F0842.pr5	
78K0	78K0/DF2	UPD78F0843	✓	78F0843.pr5	
78K0	78K0/DF2	UPD78F0846	✓	78F0846.pr5	
78K0	78K0/DF2	UPD78F0847	✓	78F0847.pr5	
78K0	78K0/DF2	UPD78F0848	✓	78F0848.pr5	
78K0	78K0/DF2	UPD78F0849	✓	78F0849.pr5	
78K0	78K0/KB1+	UPD78F0101H	✓	78F0101H.pr5	
78K0	78K0/KB1+	UPD78F0102H	✓	78F0102H.pr5	
78K0	78K0/KB1+	UPD78F0103H	✓	78F0103H.pr5	
78K0	78K0/KC1+	UPD78F0112H	✓	78F0112H.pr5	
78K0	78K0/KC1+	UPD78F0113H	✓	78F0113H.pr5	
78K0	78K0/KC1+	UPD78F0114H	✓	78F0114H.pr5	
78K0	78K0/KC1+	UPD78F0114HD	✓	78F0114HD.pr5	
78K0	78K0/KD1+	UPD78F0122H	✓	78F0122H.pr5	
78K0	78K0/KD1+	UPD78F0123H	✓	78F0123H.pr5	
78K0	78K0/KD1+	UPD78F0124H	✓	78F0124H.pr5	
78K0	78K0/KD1+	UPD78F0124HD	✓	78F0124HD.pr5	
78K0	78K0/KE1+	UPD78F0132H	✓	78F0132H.pr5	
78K0	78K0/KE1+	UPD78F0133H	✓	78F0133H.pr5	
78K0	78K0/KE1+	UPD78F0134H	✓	78F0134H.pr5	
78K0	78K0/KE1+	UPD78F0136H	✓	78F0136H.pr5	
78K0	78K0/KE1+	UPD78F0138H	✓	78F0138H.pr5	
78K0	78K0/KE1+	UPD78F0138HD	✓	78F0138HD.pr5	
78K0	78K0/KF1+	UPD78F0148H	✓	78F0148H.pr5	
78K0	78K0/KF1+	UPD78F0148HD	✓	78F0148HD.pr5	
78K0	78K0/Kxx with LIN	UPD78F8004H	✓	78F8004H.pr5	
78K0	78K0/Kxx with LIN	UPD78F8005H	✓	78F8005H.pr5	
78K0	78K0/Kxx with LIN	UPD78F8006H	✓	78F8006H.pr5	
78K0	UPD78F8019	UPD78F8014	✓	78F8014.pr5	
78K0	UPD78F8019	UPD78F8014A	✓	78F8014A.pr5	
78K0	UPD78F8019	UPD78F8015	✓	78F8015.pr5	
78K0	UPD78F8019	UPD78F8015A	✓	78F8015A.pr5	
78K0	UPD78F8019	UPD78F8016	✓	78F8016.pr5	
78K0	UPD78F8019	UPD78F8016A	✓	78F8016A.pr5	
78K0	UPD78F8019	UPD78F8017	✓	78F8017.pr5	
78K0	UPD78F8019	UPD78F8017A	✓	78F8017A.pr5	
78K0	UPD78F8019	UPD78F8018	✓	78F8018.pr5	
78K0	UPD78F8019	UPD78F8018A	✓	78F8018A.pr5	
78K0	UPD78F8019	UPD78F8019	✓	78F8019.pr5	
78K0	UPD78F8019	UPD78F8019A	✓	78F8019A.pr5	
78K0	UPD78F8020	UPD78F8020A	✓	78F8020A.pr5	
78K0	UPD78F8020	UPD78F8020DA	✓	78F8020DA.pr5	
78K0	UPD78F8032	UPD78F8026	✓	78F8026.pr5	
78K0	UPD78F8032	UPD78F8027	✓	78F8027.pr5	
78K0	UPD78F8032	UPD78F8028	✓	78F8028.pr5	
78K0	UPD78F8032	UPD78F8029	✓	78F8029.pr5	
78K0	UPD78F8032	UPD78F8030	✓	78F8030.pr5	
78K0	UPD78F8032	UPD78F8032D	✓	78F8032D.pr5	
78K0	UPD78F8077	UPD78F8071	✓	78F8071.pr5	
78K0	UPD78F8077	UPD78F8072	✓	78F8072.pr5	
78K0	UPD78F8077	UPD78F8073	✓	78F8073.pr5	
78K0	UPD78F8077	UPD78F8074	✓	78F8074.pr5	
78K0	UPD78F8077	UPD78F8075	✓	78F8075.pr5	
78K0	UPD78F8077	UPD78F8077D	✓	78F8077D.pr5	
78K0	78K0/LE2	UPD78F0361	✓	78F0361.pr5	
78K0	78K0/LE2	UPD78F0362	✓	78F0362.pr5	
78K0	78K0/LE2	UPD78F0363	✓	78F0363.pr5	
78K0	78K0/LE2	UPD78F0363D	✓	78F0363D.pr5	
78K0	78K0/LF2	UPD78F0372	✓	78F0372.pr5	
78K0	78K0/LF2	UPD78F0373	✓	78F0373.pr5	
78K0	78K0/LF2	UPD78F0374	✓	78F0374.pr5	
78K0	78K0/LF2	UPD78F0375	✓	78F0375.pr5	
78K0	78K0/LF2	UPD78F0376	✓	78F0376.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0	78K0/LF2	UPD78F0376D	✓	78F0376D.pr5	
78K0	78K0/LF2	UPD78F0382	✓	78F0382.pr5	
78K0	78K0/LF2	UPD78F0383	✓	78F0383.pr5	
78K0	78K0/LF2	UPD78F0384	✓	78F0384.pr5	
78K0	78K0/LF2	UPD78F0385	✓	78F0385.pr5	
78K0	78K0/LF2	UPD78F0386	✓	78F0386.pr5	
78K0	78K0/LF2	UPD78F0386D	✓	78F0386D.pr5	
78K0	78K0/LG2	UPD78F0393	✓	78F0393.pr5	
78K0	78K0/LG2	UPD78F0394	✓	78F0394.pr5	
78K0	78K0/LG2	UPD78F0395	✓	78F0395.pr5	
78K0	78K0/LG2	UPD78F0396	✓	78F0396.pr5	
78K0	UPD179F11x	UPD179F110	✓	179F110.pr5	
78K0	UPD179F11x	UPD179F111	✓	179F111.pr5	
78K0	UPD179F11x	UPD179F112	✓	179F112.pr5	
78K0	UPD179F11x	UPD179F114	✓	179F114.pr5	
78K0	UPD78F8024/UPD78F8025	UPD78F8024	✓	78F8024.pr5	
78K0	UPD78F8024/UPD78F8025	UPD78F8025	✓	78F8025.pr5	
78K0S	78K0S/KU1+	UPD78F9200	✓	78F9200.pr5	
78K0S	78K0S/KU1+	UPD78F9201	✓	78F9201.pr5	
78K0S	78K0S/KU1+	UPD78F9202	✓	78F9202.pr5	
78K0S	78K0S/KU1+	UPD78F9500	✓	78F9500.pr5	
78K0S	78K0S/KU1+	UPD78F9501	✓	78F9501.pr5	
78K0S	78K0S/KU1+	UPD78F9502	✓	78F9502.pr5	
78K0S	78K0S/KY1+	UPD78F9210	✓	78F9210.pr5	
78K0S	78K0S/KY1+	UPD78F9211	✓	78F9211.pr5	
78K0S	78K0S/KY1+	UPD78F9212	✓	78F9212.pr5	
78K0S	78K0S/KY1+	UPD78F9510	✓	78F9510.pr5	
78K0S	78K0S/KY1+	UPD78F9511	✓	78F9511.pr5	
78K0S	78K0S/KY1+	UPD78F9512	✓	78F9512.pr5	
78K0S	78K0S/KA1+	UPD78F9221	✓	78F9221.pr5	
78K0S	78K0S/KA1+	UPD78F9222	✓	78F9222.pr5	
78K0S	78K0S/KA1+	UPD78F9224	✓	78F9224.pr5	
78K0S	78K0S/KB1+	UPD78F9232	✓	78F9232.pr5	
78K0S	78K0S/KB1+	UPD78F9234	✓	78F9234.pr5	
78K0R	78K0R/KC3-L	UPD78F1000	✓	78F1000.pr5	
78K0R	78K0R/KC3-L	UPD78F1001	✓	78F1001.pr5	
78K0R	78K0R/KC3-L	UPD78F1002	✓	78F1002.pr5	
78K0R	78K0R/KC3-L	UPD78F1003	✓	78F1003.pr5	
78K0R	78K0R/KD3-L	UPD78F1004	✓	78F1004.pr5	
78K0R	78K0R/KD3-L	UPD78F1005	✓	78F1005.pr5	
78K0R	78K0R/KD3-L	UPD78F1006	✓	78F1006.pr5	
78K0R	78K0R/KE3-L	UPD78F1007	✓	78F1007.pr5	
78K0R	78K0R/KE3-L	UPD78F1008	✓	78F1008.pr5	
78K0R	78K0R/KE3-L	UPD78F1009	✓	78F1009.pr5	
78K0R	78K0R/KF3-L	UPD78F1010	✓	78F1010.pr5	
78K0R	78K0R/KF3-L	UPD78F1011	✓	78F1011.pr5	
78K0R	78K0R/KF3-L	UPD78F1012	✓	78F1012.pr5	
78K0R	78K0R/KF3-L	UPD78F1027	✓	78F1027.pr5	
78K0R	78K0R/KF3-L	UPD78F1028	✓	78F1028.pr5	
78K0R	78K0R/KG3-L	UPD78F1013	✓	78F1013.pr5	
78K0R	78K0R/KG3-L	UPD78F1014	✓	78F1014.pr5	
78K0R	78K0R/KG3-L	UPD78F1029	✓	78F1029.pr5	
78K0R	78K0R/KG3-L	UPD78F1030	✓	78F1030.pr5	
78K0R	78K0R/KE3	UPD78F1142	✓	78F1142.pr5	
78K0R	78K0R/KE3	UPD78F1142A	✓	78F1142.pr5	
78K0R	78K0R/KE3	UPD78F1143	✓	78F1143.pr5	
78K0R	78K0R/KE3	UPD78F1143A	✓	78F1143.pr5	
78K0R	78K0R/KE3	UPD78F1144	✓	78F1144.pr5	
78K0R	78K0R/KE3	UPD78F1144A	✓	78F1144.pr5	
78K0R	78K0R/KE3	UPD78F1145	✓	78F1145.pr5	
78K0R	78K0R/KE3	UPD78F1145A	✓	78F1145.pr5	
78K0R	78K0R/KE3	UPD78F1146	✓	78F1146.pr5	
78K0R	78K0R/KE3	UPD78F1146A	✓	78F1146.pr5	
78K0R	78K0R/KF3	UPD78F1152	✓	78F1152.pr5	
78K0R	78K0R/KF3	UPD78F1152A	✓	78F1152.pr5	
78K0R	78K0R/KF3	UPD78F1153	✓	78F1153.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0R	78K0R/KF3	UPD78F1153A	✓	78F1153.pr5	
78K0R	78K0R/KF3	UPD78F1154	✓	78F1154.pr5	
78K0R	78K0R/KF3	UPD78F1154A	✓	78F1154.pr5	
78K0R	78K0R/KF3	UPD78F1155	✓	78F1155.pr5	
78K0R	78K0R/KF3	UPD78F1155A	✓	78F1155.pr5	
78K0R	78K0R/KF3	UPD78F1156	✓	78F1156.pr5	
78K0R	78K0R/KF3	UPD78F1156A	✓	78F1156.pr5	
78K0R	78K0R/KG3	UPD78F1162	✓	78F1162.pr5	
78K0R	78K0R/KG3	UPD78F1162A	✓	78F1162.pr5	
78K0R	78K0R/KG3	UPD78F1163	✓	78F1163.pr5	
78K0R	78K0R/KG3	UPD78F1163A	✓	78F1163.pr5	
78K0R	78K0R/KG3	UPD78F1164	✓	78F1164.pr5	
78K0R	78K0R/KG3	UPD78F1164A	✓	78F1164.pr5	
78K0R	78K0R/KG3	UPD78F1165	✓	78F1165.pr5	
78K0R	78K0R/KG3	UPD78F1165A	✓	78F1165.pr5	
78K0R	78K0R/KG3	UPD78F1166	✓	78F1166.pr5	
78K0R	78K0R/KG3	UPD78F1166A	✓	78F1166.pr5	
78K0R	78K0R/KG3	UPD78F1167	✓	78F1167.pr5	
78K0R	78K0R/KG3	UPD78F1167A	✓	78F1167.pr5	
78K0R	78K0R/KG3	UPD78F1168	✓	78F1168.pr5	
78K0R	78K0R/KG3	UPD78F1168A	✓	78F1168.pr5	
78K0R	78K0R/KH3	UPD78F1174	✓	78F1174.pr5	
78K0R	78K0R/KH3	UPD78F1174A	✓	78F1174.pr5	
78K0R	78K0R/KH3	UPD78F1175	✓	78F1175.pr5	
78K0R	78K0R/KH3	UPD78F1175A	✓	78F1175.pr5	
78K0R	78K0R/KH3	UPD78F1176	✓	78F1176.pr5	
78K0R	78K0R/KH3	UPD78F1176A	✓	78F1176.pr5	
78K0R	78K0R/KH3	UPD78F1177	✓	78F1177.pr5	
78K0R	78K0R/KH3	UPD78F1177A	✓	78F1177.pr5	
78K0R	78K0R/KH3	UPD78F1178	✓	78F1178.pr5	
78K0R	78K0R/KH3	UPD78F1178A	✓	78F1178.pr5	
78K0R	78K0R/KJ3	UPD78F1184A	✓	78F1184.pr5	
78K0R	78K0R/KJ3	UPD78F1185A	✓	78F1185.pr5	
78K0R	78K0R/KJ3	UPD78F1186A	✓	78F1186.pr5	
78K0R	78K0R/KJ3	UPD78F1187A	✓	78F1187.pr5	
78K0R	78K0R/KJ3	UPD78F1188A	✓	78F1188.pr5	
78K0R	78K0R/IB3	UPD78F1201	✓	78F1201.pr5	
78K0R	78K0R/IB3	UPD78F1203	✓	78F1203.pr5	
78K0R	78K0R/IC3	UPD78F1211	✓	78F1211.pr5	
78K0R	78K0R/IC3	UPD78F1213	✓	78F1213.pr5	
78K0R	78K0R/IC3	UPD78F1214	✓	78F1214.pr5	
78K0R	78K0R/IC3	UPD78F1215	✓	78F1215.pr5	
78K0R	78K0R/ID3	UPD78F1223	✓	78F1223.pr5	
78K0R	78K0R/ID3	UPD78F1224	✓	78F1224.pr5	
78K0R	78K0R/ID3	UPD78F1225	✓	78F1225.pr5	
78K0R	78K0R/IE3	UPD78F1233	✓	78F1233.pr5	
78K0R	78K0R/IE3	UPD78F1234	✓	78F1234.pr5	
78K0R	78K0R/IE3	UPD78F1235	✓	78F1235.pr5	
78K0R	78K0R/KF3-C	UPD78F1846A	✓	78F1846A.pr5	
78K0R	78K0R/KF3-C	UPD78F1847	✓	78F1847.pr5	
78K0R	78K0R/KF3-C	UPD78F1847A	✓	78F1847A.pr5	
78K0R	78K0R/KG3-C	UPD78F1848A	✓	78F1848A.pr5	
78K0R	78K0R/KG3-C	UPD78F1849	✓	78F1849.pr5	
78K0R	78K0R/KG3-C	UPD78F1849A	✓	78F1849A.pr5	
78K0R	78K0R/LF3	UPD78F1500	✓	78F1500.pr5	
78K0R	78K0R/LF3	UPD78F1500A	✓	78F1500.pr5	
78K0R	78K0R/LF3	UPD78F1501	✓	78F1501.pr5	
78K0R	78K0R/LF3	UPD78F1501A	✓	78F1501.pr5	
78K0R	78K0R/LF3	UPD78F1502	✓	78F1502.pr5	
78K0R	78K0R/LF3	UPD78F1502A	✓	78F1502.pr5	
78K0R	78K0R/LF3	UPD78F1510A	✓	78F1510.pr5	
78K0R	78K0R/LF3	UPD78F1512A	✓	78F1512.pr5	
78K0R	78K0R/LG3	UPD78F1503	✓	78F1503.pr5	
78K0R	78K0R/LG3	UPD78F1503A	✓	78F1503.pr5	
78K0R	78K0R/LG3	UPD78F1504	✓	78F1504.pr5	
78K0R	78K0R/LG3	UPD78F1504A	✓	78F1504.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0R	78K0R/LG3	UPD78F1505	✓	78F1505.pr5	
78K0R	78K0R/LG3	UPD78F1505A	✓	78F1505.pr5	
78K0R	78K0R/LG3	UPD78F1513A	✓	78F1513.pr5	
78K0R	78K0R/LG3	UPD78F1515A	✓	78F1515.pr5	
78K0R	78K0R/LH3	UPD78F1506	✓	78F1506.pr5	
78K0R	78K0R/LH3	UPD78F1506A	✓	78F1506.pr5	
78K0R	78K0R/LH3	UPD78F1507	✓	78F1507.pr5	
78K0R	78K0R/LH3	UPD78F1507A	✓	78F1507.pr5	
78K0R	78K0R/LH3	UPD78F1508	✓	78F1508.pr5	
78K0R	78K0R/LH3	UPD78F1508A	✓	78F1508.pr5	
78K0R	78K0R/LH3	UPD78F1516A	✓	78F1516.pr5	
78K0R	78K0R/LH3	UPD78F1518A	✓	78F1518.pr5	
78K0R	78K0R/FB3	UPD78F1804	✓	78F1804.pr5	
78K0R	78K0R/FB3	UPD78F1804A	✓	78F1804.pr5	
78K0R	78K0R/FB3	UPD78F1805	✓	78F1805.pr5	
78K0R	78K0R/FB3	UPD78F1805A	✓	78F1805.pr5	
78K0R	78K0R/FB3	UPD78F1806	✓	78F1806.pr5	
78K0R	78K0R/FB3	UPD78F1806A	✓	78F1806.pr5	
78K0R	78K0R/FB3	UPD78F1807	✓	78F1807.pr5	
78K0R	78K0R/FB3	UPD78F1807A	✓	78F1807.pr5	
78K0R	78K0R/FC3	UPD78F1808	✓	78F1808.pr5	
78K0R	78K0R/FC3	UPD78F1808A	✓	78F1808.pr5	
78K0R	78K0R/FC3	UPD78F1809	✓	78F1809.pr5	
78K0R	78K0R/FC3	UPD78F1809A	✓	78F1809.pr5	
78K0R	78K0R/FC3	UPD78F1810	✓	78F1810.pr5	
78K0R	78K0R/FC3	UPD78F1810A	✓	78F1810.pr5	
78K0R	78K0R/FC3	UPD78F1811	✓	78F1811.pr5	
78K0R	78K0R/FC3	UPD78F1811A	✓	78F1811.pr5	
78K0R	78K0R/FC3	UPD78F1812	✓	78F1812.pr5	
78K0R	78K0R/FC3	UPD78F1812A	✓	78F1812.pr5	
78K0R	78K0R/FC3	UPD78F1813	✓	78F1813.pr5	
78K0R	78K0R/FC3	UPD78F1813A	✓	78F1813.pr5	
78K0R	78K0R/FC3	UPD78F1814	✓	78F1814.pr5	
78K0R	78K0R/FC3	UPD78F1814A	✓	78F1814.pr5	
78K0R	78K0R/FC3	UPD78F1815	✓	78F1815.pr5	
78K0R	78K0R/FC3	UPD78F1815A	✓	78F1815.pr5	
78K0R	78K0R/FC3	UPD78F1816	✓	78F1816.pr5	
78K0R	78K0R/FC3	UPD78F1816A	✓	78F1816.pr5	
78K0R	78K0R/FC3	UPD78F1817	✓	78F1817.pr5	
78K0R	78K0R/FC3	UPD78F1817A	✓	78F1817.pr5	
78K0R	78K0R/FC3	UPD78F1826	✓	78F1826.pr5	
78K0R	78K0R/FC3	UPD78F1826A	✓	78F1826.pr5	
78K0R	78K0R/FC3	UPD78F1827	✓	78F1827.pr5	
78K0R	78K0R/FC3	UPD78F1827A	✓	78F1827.pr5	
78K0R	78K0R/FC3	UPD78F1828	✓	78F1828.pr5	
78K0R	78K0R/FC3	UPD78F1828A	✓	78F1828.pr5	
78K0R	78K0R/FC3	UPD78F1829	✓	78F1829.pr5	
78K0R	78K0R/FC3	UPD78F1829A	✓	78F1829.pr5	
78K0R	78K0R/FC3	UPD78F1830	✓	78F1830.pr5	
78K0R	78K0R/FC3	UPD78F1830A	✓	78F1830.pr5	
78K0R	78K0R/FE3	UPD78F1818	✓	78F1818.pr5	
78K0R	78K0R/FE3	UPD78F1818A	✓	78F1818.pr5	
78K0R	78K0R/FE3	UPD78F1819	✓	78F1819.pr5	
78K0R	78K0R/FE3	UPD78F1819A	✓	78F1819.pr5	
78K0R	78K0R/FE3	UPD78F1820	✓	78F1820.pr5	
78K0R	78K0R/FE3	UPD78F1820A	✓	78F1820.pr5	
78K0R	78K0R/FE3	UPD78F1821	✓	78F1821.pr5	
78K0R	78K0R/FE3	UPD78F1821A	✓	78F1821.pr5	
78K0R	78K0R/FE3	UPD78F1822	✓	78F1822.pr5	
78K0R	78K0R/FE3	UPD78F1822A	✓	78F1822.pr5	
78K0R	78K0R/FE3	UPD78F1831	✓	78F1831.pr5	
78K0R	78K0R/FE3	UPD78F1831A	✓	78F1831.pr5	
78K0R	78K0R/FE3	UPD78F1832	✓	78F1832.pr5	
78K0R	78K0R/FE3	UPD78F1832A	✓	78F1832.pr5	
78K0R	78K0R/FE3	UPD78F1833	✓	78F1833.pr5	
78K0R	78K0R/FE3	UPD78F1833A	✓	78F1833.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0R	78K0R/FE3	UPD78F1834	✓	78F1834.pr5	
78K0R	78K0R/FE3	UPD78F1834A	✓	78F1834.pr5	
78K0R	78K0R/FE3	UPD78F1835	✓	78F1835.pr5	
78K0R	78K0R/FE3	UPD78F1835A	✓	78F1835.pr5	
78K0R	78K0R/FF3	UPD78F1823	✓	78F1823.pr5	
78K0R	78K0R/FF3	UPD78F1823A	✓	78F1823.pr5	
78K0R	78K0R/FF3	UPD78F1824	✓	78F1824.pr5	
78K0R	78K0R/FF3	UPD78F1824A	✓	78F1824.pr5	
78K0R	78K0R/FF3	UPD78F1825	✓	78F1825.pr5	
78K0R	78K0R/FF3	UPD78F1825A	✓	78F1825.pr5	
78K0R	78K0R/FF3	UPD78F1836	✓	78F1836.pr5	
78K0R	78K0R/FF3	UPD78F1836A	✓	78F1836.pr5	
78K0R	78K0R/FF3	UPD78F1837	✓	78F1837.pr5	
78K0R	78K0R/FF3	UPD78F1837A	✓	78F1837.pr5	
78K0R	78K0R/FF3	UPD78F1838	✓	78F1838.pr5	
78K0R	78K0R/FF3	UPD78F1838A	✓	78F1838.pr5	
78K0R	78K0R/FF3	UPD78F1839	✓	78F1839.pr5	
78K0R	78K0R/FF3	UPD78F1839A	✓	78F1839.pr5	
78K0R	78K0R/FF3	UPD78F1840	✓	78F1840.pr5	
78K0R	78K0R/FF3	UPD78F1840A	✓	78F1840.pr5	
78K0R	78K0R/FG3	UPD78F1841	✓	78F1841.pr5	
78K0R	78K0R/FG3	UPD78F1841A	✓	78F1841.pr5	
78K0R	78K0R/FG3	UPD78F1842	✓	78F1842.pr5	
78K0R	78K0R/FG3	UPD78F1842A	✓	78F1842.pr5	
78K0R	78K0R/FG3	UPD78F1843	✓	78F1843.pr5	
78K0R	78K0R/FG3	UPD78F1843A	✓	78F1843.pr5	
78K0R	78K0R/FG3	UPD78F1844	✓	78F1844.pr5	
78K0R	78K0R/FG3	UPD78F1844A	✓	78F1844.pr5	
78K0R	78K0R/FG3	UPD78F1845	✓	78F1845.pr5	
78K0R	78K0R/FG3	UPD78F1845A	✓	78F1845.pr5	
78K0R	78K0R/HC3	UPD78F1031	✓	78F1031.pr5	
78K0R	78K0R/HC3	UPD78F1032	✓	78F1032.pr5	
78K0R	78K0R/HC3	UPD78F1033	✓	78F1033.pr5	
78K0R	78K0R/HC3	UPD78F1034	✓	78F1034.pr5	
78K0R	78K0R/HC3	UPD78F1035	✓	78F1035.pr5	
78K0R	78K0R/HE3	UPD78F1036	✓	78F1036.pr5	
78K0R	78K0R/HE3	UPD78F1037	✓	78F1037.pr5	
78K0R	78K0R/HE3	UPD78F1038	✓	78F1038.pr5	
78K0R	78K0R/HE3	UPD78F1039	✓	78F1039.pr5	
78K0R	78K0R/HE3	UPD78F1040	✓	78F1040.pr5	
78K0R	78K0R/HF3	UPD78F1041	✓	78F1041.pr5	
78K0R	78K0R/HF3	UPD78F1042	✓	78F1042.pr5	
78K0R	78K0R/HF3	UPD78F1043	✓	78F1043.pr5	
78K0R	78K0R/HF3	UPD78F1044	✓	78F1044.pr5	
78K0R	78K0R/HF3	UPD78F1045	✓	78F1045.pr5	
78K0R	78K0R/HG3	UPD78F1046	✓	78F1046.pr5	
78K0R	78K0R/HG3	UPD78F1047	✓	78F1047.pr5	
78K0R	78K0R/HG3	UPD78F1048	✓	78F1048.pr5	
78K0R	78K0R/HG3	UPD78F1049	✓	78F1049.pr5	
78K0R	78K0R/HG3	UPD78F1050	✓	78F1050.pr5	
78K0R	78K0R/KE3-A	UPD78F1016	✓	78F1016.pr5	
78K0R	78K0R/KE3-A	UPD78F1017	✓	78F1017.pr5	
78K0R	78K0R/KE3-A	UPD78F1018	✓	78F1018.pr5	
78K0R	UPD78F8043	UPD78F8041	✓	78F8041.pr5	
78K0R	UPD78F8043	UPD78F8043	✓	78F8043.pr5	
78K0R	UPD78F8058	UPD78F8056	✓	78F8056.pr5	
78K0R	UPD78F8058	UPD78F8058	✓	78F8058.pr5	
78K0R	78K0R/KC3-L(USB)	UPD78F1022	✓	78F1022.pr5	
78K0R	78K0R/KC3-L(USB)	UPD78F1023	✓	78F1023.pr5	
78K0R	78K0R/KC3-L(USB)	UPD78F1024	✓	78F1024.pr5	
78K0R	78K0R/KE3-L(USB)	UPD78F1025	✓	78F1025.pr5	
78K0R	78K0R/KE3-L(USB)	UPD78F1026	✓	78F1026.pr5	
78K0R	UPD78F8069	UPD78F8064	✓	78F8064.pr5	
78K0R	UPD78F8069	UPD78F8065	✓	78F8065.pr5	
78K0R	UPD78F8069	UPD78F8066	✓	78F8066.pr5	
78K0R	UPD78F8069	UPD78F8067	✓	78F8067.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
78K0R	UPD78F8069	UPD78F8068	✓	78F8068.pr5	
78K0R	UPD78F8069	UPD78F8069	✓	78F8069.pr5	
78K0R	78K0R/LG3-M	UPD78F8070	✓	78F8070.pr5	
V850	V850E/MA3	UPD70F3134B	✓	70F3134B.pr5	Device version:ES2.0 or later
V850	V850E/IA3	UPD70F3184	✓	70F3184.pr5	
V850	V850E/IA4	UPD70F3186	✓	70F3186.pr5	
V850	V850E/SJ3-H	UPD70F3474A	✓	70F3474 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3474A	✓	70F3474 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3475	✓	70F3475 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3475	✓	70F3475 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3475A	✓	70F3475 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3475A	✓	70F3475 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3476	✓	70F3476 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3476	✓	70F3476 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3476A	✓	70F3476 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3476A	✓	70F3476 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3477	✓	70F3477 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3477	✓	70F3477 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3477A	✓	70F3477 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3477A	✓	70F3477 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3478	✓	70F3478 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3478	✓	70F3478 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3478A	✓	70F3478 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3478A	✓	70F3478 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3479	✓	70F3479 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3479	✓	70F3479 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3479A	✓	70F3479 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3479A	✓	70F3479 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3931B	✓	70F3931 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3931B	✓	70F3931 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3932B	✓	70F3932 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3932B	✓	70F3932 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3933B	✓	70F3933 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3933B	✓	70F3933 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3934B	✓	70F3934 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3934B	✓	70F3934 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3935B	✓	70F3935 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3935B	✓	70F3935 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3936A	✓	70F3936 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3936A	✓	70F3936 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3936B	✓	70F3936 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3936B	✓	70F3936 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3937	✓	70F3937 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3937	✓	70F3937 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3937A	✓	70F3937 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3937A	✓	70F3937 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3937B	✓	70F3937 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3937B	✓	70F3937 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3938	✓	70F3938 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3938	✓	70F3938 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3938A	✓	70F3938 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3938A	✓	70F3938 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3938B	✓	70F3938 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3938B	✓	70F3938 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3939	✓	70F3939 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3939	✓	70F3939 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3939A	✓	70F3939 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3939A	✓	70F3939 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3939B	✓	70F3939 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SJ3-H	UPD70F3939B	✓	70F3939 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3480	✓	70F3480 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3480	✓	70F3480 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3480A	✓	70F3480 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3480A	✓	70F3480 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3481	✓	70F3481 CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3481	✓	70F3481 CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
V850	V850E/SK3-H	UPD70F3481A	✓	70F3481_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3481A	✓	70F3481_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3482	✓	70F3482_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3482	✓	70F3482_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3482A	✓	70F3482_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3482A	✓	70F3482_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3486A	✓	70F3486_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3486A	✓	70F3486_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3487A	✓	70F3487_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3487A	✓	70F3487_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3488A	✓	70F3488_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3488A	✓	70F3488_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3925	✓	70F3925_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3925	✓	70F3925_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3925A	✓	70F3925_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3925A	✓	70F3925_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3926	✓	70F3926_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3926	✓	70F3926_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3926A	✓	70F3926_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3926A	✓	70F3926_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3927	✓	70F3927_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3927	✓	70F3927_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/SK3-H	UPD70F3927A	✓	70F3927_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850E/SK3-H	UPD70F3927A	✓	70F3927_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/FE2	UPD70F3231	✓	70F3231.pr5	
V850	V850ES/FF2	UPD70F3232	✓	70F3232.pr5	
V850	V850ES/FF2	UPD70F3233	✓	70F3233.pr5	
V850	V850ES/FG2	UPD70F3234	✓	70F3234.pr5	
V850	V850ES/FG2	UPD70F3235	✓	70F3235.pr5	
V850	V850ES/FJ2	UPD70F3237	✓	70F3237.pr5	
V850	V850ES/SG2	UPD70F3261	✓	70F3261_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2	UPD70F3261	✓	70F3261_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG2	UPD70F3263	✓	70F3263_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2	UPD70F3263	✓	70F3263_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG2	UPD70F3271	✓	70F3271_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2	UPD70F3271	✓	70F3271_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG2	UPD70F3273	✓	70F3273_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2	UPD70F3273	✓	70F3273_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG2	UPD70F3281	✓	70F3281_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2	UPD70F3281	✓	70F3281_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG2	UPD70F3283	✓	70F3283_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2	UPD70F3283	✓	70F3283_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ2	UPD70F3264	✓	70F3264_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ2	UPD70F3264	✓	70F3264_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ2	UPD70F3266	✓	70F3266_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ2	UPD70F3266	✓	70F3266_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ2	UPD70F3274	✓	70F3274_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ2	UPD70F3274	✓	70F3274_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ2	UPD70F3276	✓	70F3276_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ2	UPD70F3276	✓	70F3276_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ2	UPD70F3284	✓	70F3284_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ2	UPD70F3284	✓	70F3284_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ2	UPD70F3286	✓	70F3286_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ2	UPD70F3286	✓	70F3286_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ2	UPD70F3288	✓	70F3288_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ2	UPD70F3288	✓	70F3288_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG2-H	UPD70F3263H	✓	70F3263H_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2-H	UPD70F3263H	✓	70F3263H_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG2-H	UPD70F3273H	✓	70F3273H_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2-H	UPD70F3273H	✓	70F3273H_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG2-H	UPD70F3283H	✓	70F3283H_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG2-H	UPD70F3283H	✓	70F3283H_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/IK1	UPD70F3329	✓	70F3329.pr5	
V850	V850ES/SG3	UPD70F3333	✓	70F3333_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3333	✓	70F3333_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3334	✓	70F3334_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
V850	V850ES/SG3	UPD70F3334	✓	70F3334_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3335	✓	70F3335_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3335	✓	70F3335_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3336	✓	70F3336_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3336	✓	70F3336_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3340	✓	70F3340_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3340	✓	70F3340_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3341	✓	70F3341_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3341	✓	70F3341_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3342	✓	70F3342_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3342	✓	70F3342_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3343	✓	70F3343_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3343	✓	70F3343_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3350	✓	70F3350_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3350	✓	70F3350_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3351	✓	70F3351_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3351	✓	70F3351_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3352	✓	70F3352_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3352	✓	70F3352_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SG3	UPD70F3353	✓	70F3353_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SG3	UPD70F3353	✓	70F3353_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3344	✓	70F3344_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3344	✓	70F3344_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3345	✓	70F3345_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3345	✓	70F3345_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3346	✓	70F3346_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3346	✓	70F3346_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3347	✓	70F3347_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3347	✓	70F3347_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3348	✓	70F3348_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3348	✓	70F3348_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3354	✓	70F3354_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3354	✓	70F3354_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3355	✓	70F3355_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3355	✓	70F3355_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3356	✓	70F3356_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3356	✓	70F3356_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3357	✓	70F3357_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3357	✓	70F3357_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3358	✓	70F3358_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3358	✓	70F3358_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3364	✓	70F3364_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3364	✓	70F3364_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3365	✓	70F3365_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3365	✓	70F3365_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3366	✓	70F3366_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3366	✓	70F3366_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3367	✓	70F3367_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3367	✓	70F3367_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/SJ3	UPD70F3368	✓	70F3368_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/SJ3	UPD70F3368	✓	70F3368_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850E/IF3	UPD70F3451	✓	70F3451.pr5	
V850	V850E/IF3	UPD70F3452	✓	70F3452.pr5	
V850	V850E/IG3	UPD70F3453	✓	70F3453.pr5	
V850	V850E/IG3	UPD70F3454	✓	70F3454.pr5	
V850	V850ES/HE2	UPD70F3700	✓	70F3700.pr5	
V850	V850ES/HE2	UPD70F3701	✓	70F3701.pr5	
V850	V850ES/HF2	UPD70F3702	✓	70F3702.pr5	
V850	V850ES/HF2	UPD70F3703	✓	70F3703.pr5	
V850	V850ES/HF2	UPD70F3704	✓	70F3704.pr5	
V850	V850ES/HG2	UPD70F3706	✓	70F3706.pr5	
V850	V850ES/HG2	UPD70F3707	✓	70F3707.pr5	
V850	V850ES/HJ2	UPD70F3709	✓	70F3709.pr5	
V850	V850ES/HJ2	UPD70F3710	✓	70F3710.pr5	
V850	V850ES/IE2	UPD70F3713	✓	70F3713.pr5	
V850	V850ES/IE2	UPD70F3714	✓	70F3714.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
V850	V850ES/JG2	UPD70F3715	✓	70F3715_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG2	UPD70F3715	✓	70F3715_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG2	UPD70F3716	✓	70F3716_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG2	UPD70F3716	✓	70F3716_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG2	UPD70F3717	✓	70F3717_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG2	UPD70F3717	✓	70F3717_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG2	UPD70F3718	✓	70F3718_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG2	UPD70F3718	✓	70F3718_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG2	UPD70F3719	✓	70F3719_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG2	UPD70F3719	✓	70F3719_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ2	UPD70F3720	✓	70F3720_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ2	UPD70F3720	✓	70F3720_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ2	UPD70F3721	✓	70F3721_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ2	UPD70F3721	✓	70F3721_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ2	UPD70F3722	✓	70F3722_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ2	UPD70F3722	✓	70F3722_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ2	UPD70F3723	✓	70F3723_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ2	UPD70F3723	✓	70F3723_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ2	UPD70F3724	✓	70F3724_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ2	UPD70F3724	✓	70F3724_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/KE2	UPD70F3726	✓	70F3726.pr5	
V850	V850ES/KF2	UPD70F3728	✓	70F3728.pr5	
V850	V850ES/KG2	UPD70F3731	✓	70F3731.pr5	
V850	V850ES/KJ2	UPD70F3733	✓	70F3733.pr5	
V850	V850ES/JC3-L	UPD70F3838	✓	70F3838_CSI0.pr5	
V850	V850ES/JC3-L	UPD70F3801	✓	70F3801_CSI0.pr5	
V850	V850ES/JC3-L	UPD70F3803	✓	70F3803_CSI0.pr5	
V850	V850ES/JC3-L	UPD70F3839	✓	70F3839_CSI0.pr5	
V850	V850ES/JE3-L	UPD70F3805	✓	70F3805_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3805	✓	70F3805_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3806	✓	70F3806_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3806	✓	70F3806_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3807	✓	70F3807_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3807	✓	70F3807_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3808	✓	70F3808_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3808	✓	70F3808_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3840	✓	70F3840_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JE3-L	UPD70F3840	✓	70F3840_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JF3-L	UPD70F3735	✓	70F3735_CSI0.pr5	
V850	V850ES/JF3-L	UPD70F3736	✓	70F3736_CSI0.pr5	
V850	V850ES/JG3-L	UPD70F3737	✓	70F3737_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3737	✓	70F3737_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3738	✓	70F3738_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3738	✓	70F3738_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3792	✓	70F3792_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3792	✓	70F3792_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3793	✓	70F3793_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3793	✓	70F3793_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3794	✓	70F3794_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3794	✓	70F3794_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3795	✓	70F3795_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3795	✓	70F3795_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3796	✓	70F3796_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3796	✓	70F3796_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3841	✓	70F3841_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3841	✓	70F3841_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3842	✓	70F3842_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3842	✓	70F3842_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3844	✓	70F3844_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3-L	UPD70F3844	✓	70F3844_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3	UPD70F3739	✓	70F3739_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3	UPD70F3739	✓	70F3739_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3	UPD70F3740	✓	70F3740_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3	UPD70F3740	✓	70F3740_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JG3	UPD70F3741	✓	70F3741_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3	UPD70F3741	✓	70F3741_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
V850	V850ES/JG3	UPD70F3742	✓	70F3742_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JG3	UPD70F3742	✓	70F3742_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ3	UPD70F3743	✓	70F3743_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ3	UPD70F3743	✓	70F3743_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ3	UPD70F3744	✓	70F3744_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ3	UPD70F3744	✓	70F3744_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ3	UPD70F3745	✓	70F3745_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ3	UPD70F3745	✓	70F3745_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/JJ3	UPD70F3746	✓	70F3746_CSI0.pr5	For CSIB0, CSIB0+HS, UARTA0
V850	V850ES/JJ3	UPD70F3746	✓	70F3746_CSI3.pr5	For CSIB3, CSIB3+HS, UARTA0
V850	V850ES/HE3	UPD70F3747	✓	70F3747.pr5	
V850	V850ES/HF3	UPD70F3750	✓	70F3750.pr5	
V850	V850ES/HG3	UPD70F3752	✓	70F3752.pr5	
V850	V850ES/HJ3	UPD70F3755	✓	70F3755.pr5	
V850	V850ES/HJ3	UPD70F3757	✓	70F3757.pr5	
V850	V850ES/JC3-H	UPD70F3814	✓	70F3814_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3814	✓	70F3814_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3815	✓	70F3815_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3815	✓	70F3815_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3816	✓	70F3816_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3816	✓	70F3816_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3817	✓	70F3817_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3817	✓	70F3817_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3818	✓	70F3818_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3818	✓	70F3818_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3819	✓	70F3819_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JC3-H	UPD70F3819	✓	70F3819_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3820	✓	70F3820_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3820	✓	70F3820_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3821	✓	70F3821_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3821	✓	70F3821_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3822	✓	70F3822_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3822	✓	70F3822_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3823	✓	70F3823_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3823	✓	70F3823_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3824	✓	70F3824_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3824	✓	70F3824_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3825	✓	70F3825_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JE3-H	UPD70F3825	✓	70F3825_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-H	UPD70F3760	✓	70F3760_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-H	UPD70F3760	✓	70F3760_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-H	UPD70F3761	✓	70F3761_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-H	UPD70F3761	✓	70F3761_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-H	UPD70F3762	✓	70F3762_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-H	UPD70F3762	✓	70F3762_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-H	UPD70F3770	✓	70F3770_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-H	UPD70F3770	✓	70F3770_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-H	UPD70F3765	✓	70F3765_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-H	UPD70F3765	✓	70F3765_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-H	UPD70F3766	✓	70F3766_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-H	UPD70F3766	✓	70F3766_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-H	UPD70F3767	✓	70F3767_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-H	UPD70F3767	✓	70F3767_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-H	UPD70F3771	✓	70F3771_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-H	UPD70F3771	✓	70F3771_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-U	UPD70F3763	✓	70F3763_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-U	UPD70F3763	✓	70F3763_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-U	UPD70F3764	✓	70F3764_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-U	UPD70F3764	✓	70F3764_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-U	UPD70F3768	✓	70F3768_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-U	UPD70F3768	✓	70F3768_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-U	UPD70F3769	✓	70F3769_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-U	UPD70F3769	✓	70F3769_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JE3-E	UPD70F3826	✓	70F3826_CSI0.pr5	
V850	V850ES/JE3-E	UPD70F3827	✓	70F3827_CSI0.pr5	
V850	V850ES/JE3-E	UPD70F3828	✓	70F3828_CSI0.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
V850	V850ES/JE3-E	UPD70F3829	✓	70F3829_CSI0.pr5	
V850	V850ES/JG3-E	UPD70F3834	✓	70F3834_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-E	UPD70F3834	✓	70F3834_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-E	UPD70F3835	✓	70F3835_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-E	UPD70F3835	✓	70F3835_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-E	UPD70F3836	✓	70F3836_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-E	UPD70F3836	✓	70F3836_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JG3-E	UPD70F3837	✓	70F3837_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JG3-E	UPD70F3837	✓	70F3837_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3778	✓	70F3778_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3778	✓	70F3778_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3779	✓	70F3779_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3779	✓	70F3779_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3780	✓	70F3780_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3780	✓	70F3780_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3781	✓	70F3781_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3781	✓	70F3781_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3782	✓	70F3782_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3782	✓	70F3782_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3783	✓	70F3783_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JH3-E	UPD70F3783	✓	70F3783_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JJ3-E	UPD70F3784	✓	70F3784_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JJ3-E	UPD70F3784	✓	70F3784_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JJ3-E	UPD70F3785	✓	70F3785_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JJ3-E	UPD70F3785	✓	70F3785_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850ES/JJ3-E	UPD70F3786	✓	70F3786_CSI0.pr5	For CSIF0, CSIF0+HS, UARTC0
V850	V850ES/JJ3-E	UPD70F3786	✓	70F3786_CSI3.pr5	For CSIF3, CSIF3+HS, UARTC0
V850	V850E/IG4	UPD70F3913	✓	70F3913.pr5	
V850	V850E/IG4	UPD70F3914	✓	70F3914.pr5	
V850	V850E/IG4	UPD70F3915	✓	70F3915.pr5	
V850	V850E/IH4	UPD70F3916	✓	70F3916.pr5	
V850	V850E/IH4	UPD70F3917	✓	70F3917.pr5	
V850	V850E/IH4	UPD70F3918	✓	70F3918.pr5	
V850	V850E/IG4-H	UPD70F3919	✓	70F3919.pr5	
V850	V850E/IG4-H	UPD70F3920	✓	70F3920.pr5	
V850	V850E/IG4-H	UPD70F3921	✓	70F3921.pr5	
V850	V850E/IH4-H	UPD70F3922	✓	70F3922.pr5	
V850	V850E/IH4-H	UPD70F3923	✓	70F3923.pr5	
V850	V850E/IH4-H	UPD70F3924	✓	70F3924.pr5	
V850	V850ES/FE3	UPD70F3370A	✓	70F3370.pr5	
V850	V850ES/FE3	UPD70F3371	✓	70F3371.pr5	
V850	V850ES/FF3	UPD70F3372	✓	70F3372.pr5	
V850	V850ES/FF3	UPD70F3373	✓	70F3373.pr5	
V850	V850ES/FG3	UPD70F3374	✓	70F3374.pr5	
V850	V850ES/FG3	UPD70F3375	✓	70F3375.pr5	
V850	V850ES/FG3	UPD70F3376A	✓	70F3376.pr5	
V850	V850ES/FG3	UPD70F3377A	✓	70F3377.pr5	
V850	V850ES/FJ3	UPD70F3378	✓	70F3378.pr5	
V850	V850ES/FJ3	UPD70F3379	✓	70F3379.pr5	
V850	V850ES/FJ3	UPD70F3380	✓	70F3380.pr5	
V850	V850ES/FJ3	UPD70F3381	✓	70F3381.pr5	
V850	V850ES/FJ3	UPD70F3382	✓	70F3382.pr5	
V850	V850ES/FK3	UPD70F3383	✓	70F3383.pr5	
V850	V850ES/FK3	UPD70F3384	✓	70F3384.pr5	
V850	V850ES/FK3	UPD70F3385	✓	70F3385.pr5	
V850	V850ES/FE3-L	UPD70F3610	✓	70F3610.pr5	
V850	V850ES/FE3-L	UPD70F3611	✓	70F3611.pr5	
V850	V850ES/FE3-L	UPD70F3612	✓	70F3612.pr5	
V850	V850ES/FE3-L	UPD70F3613	✓	70F3613.pr5	
V850	V850ES/FE3-L	UPD70F3614	✓	70F3614.pr5	
V850	V850ES/FF3-L	UPD70F3615	✓	70F3615.pr5	
V850	V850ES/FF3-L	UPD70F3616	✓	70F3616.pr5	
V850	V850ES/FF3-L	UPD70F3617	✓	70F3617.pr5	
V850	V850ES/FF3-L	UPD70F3618	✓	70F3618.pr5	
V850	V850ES/FF3-L	UPD70F3619	✓	70F3619.pr5	
V850	V850ES/FG3-L	UPD70F3620	✓	70F3620.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
V850	V850ES/FG3-L	UPD70F3622	✓	70F3622.pr5	
V850	V850E2/DJ4	UPD70F3522	✓	70F3522.pr5	
V850	V850E2/DJ4	UPD70F3523	✓	70F3523.pr5	
V850	V850E2/DJ4	UPD70F3524	✓	70F3524.pr5	
V850	V850E2/DJ4	UPD70F3525	✓	70F3525.pr5	
V850	V850E2/DJ4	UPD70F3526	✓	70F3526.pr5	
V850	V850E2/DK4-H	UPD70F3529	✓	70F3529.pr5	
V850	V850E2/DN4-H	UPD70F3532	✓	70F3532.pr5	
V850	V850E2/DP4-H	UPD70F3535	✓	70F3535.pr5	
V850	V850E2/DP4-H	UPD70F3536	✓	70F3536.pr5	
V850	V850E2/DP4-H	UPD70F3537	✓	70F3537.pr5	
V850	V850E2/FG4	UPD70F3548	✓	70F3548.pr5	
V850	V850E2/FG4	UPD70F3549	✓	70F3549.pr5	
V850	V850E2/FG4	UPD70F3550	✓	70F3550.pr5	
V850	V850E2/FG4	UPD70F4000	✓	70F4000.pr5	
V850	V850E2/FG4	UPD70F4001	✓	70F4001.pr5	
V850	V850E2/FG4	UPD70F4002	✓	70F4002.pr5	
V850	V850E2/FJ4	UPD70F3551	✓	70F3551.pr5	
V850	V850E2/FJ4	UPD70F3552	✓	70F3552.pr5	
V850	V850E2/FJ4	UPD70F3553	✓	70F3553.pr5	
V850	V850E2/FJ4	UPD70F3554	✓	70F3554.pr5	
V850	V850E2/FJ4	UPD70F4003	✓	70F4003.pr5	
V850	V850E2/FJ4	UPD70F4004	✓	70F4004.pr5	
V850	V850E2/FJ4	UPD70F4005	✓	70F4005.pr5	
V850	V850E2/FJ4	UPD70F4006	✓	70F4006.pr5	
V850	V850E2/FK4	UPD70F3555	✓	70F3555.pr5	
V850	V850E2/FK4	UPD70F3556	✓	70F3556.pr5	
V850	V850E2/FK4	UPD70F3557	✓	70F3557.pr5	
V850	V850E2/FK4	UPD70F3558	✓	70F3558.pr5	
V850	V850E2/FK4	UPD70F4007	✓	70F4007.pr5	
V850	V850E2/FK4	UPD70F4009	✓	70F4009.pr5	
V850	V850E2/FK4	UPD70F4010	✓	70F4010.pr5	
V850	V850E2/FL4	UPD70F4012	✓	70F4012.pr5	
V850	V850E2/FF4-G	UPD70F4177	✓	70F4177.pr5	
V850	V850E2/FF4-G	UPD70F4178	✓	70F4178.pr5	
V850	V850E2/FG4-G	UPD70F4179	✓	70F4179.pr5	
V850	V850E2/FG4-G	UPD70F4180	✓	70F4180.pr5	
V850	V850E2/FK4-G	UPD70F3592	✓	70F3592.pr5	
V850	V850E2/FK4-H	UPD70F3561	✓	70F3561.pr5	
V850	V850E2/FL4-H	UPD70F3564	✓	70F3564.pr5	
V850	V850E2/FE4-L	UPD70F3570	✓	70F3570.pr5	
V850	V850E2/FE4-L	UPD70F3571	✓	70F3571.pr5	
V850	V850E2/FE4-L	UPD70F3572	✓	70F3572.pr5	
V850	V850E2/FF4-L	UPD70F3573	✓	70F3573.pr5	
V850	V850E2/FF4-L	UPD70F3574	✓	70F3574.pr5	
V850	V850E2/FF4-L	UPD70F3575	✓	70F3575.pr5	
V850	V850E2/FG4-L	UPD70F3576	✓	70F3576.pr5	
V850	V850E2/FG4-L	UPD70F3577	✓	70F3577.pr5	
V850	V850E2/FG4-L	UPD70F3578	✓	70F3578.pr5	
V850	V850E2/FG4-L	UPD70F3579	✓	70F3579.pr5	
V850	V850E2/FG4-L	UPD70F3580	✓	70F3580.pr5	
V850	V850E2/FJ4-L	UPD70F3582	✓	70F3582.pr5	
V850	V850E2/FJ4-L	UPD70F3583	✓	70F3583.pr5	
V850	V850E2/FJ4-L	UPD70F3584	✓	70F3584.pr5	
V850	V850E2/FJ4-L	UPD70F3585	✓	70F3585.pr5	
V850	V850E2/FF4-M	UPD70F3543	✓	70F3543.pr5	
V850	V850E2/FF4-M	UPD70F3544	✓	70F3544.pr5	
V850	V850E2/FF4-M	UPD70F3545	✓	70F3545.pr5	
V850	V850E2/ML4	UPD70F4021	✓	70F4021.pr5	
V850	V850E2/ML4	UPD70F4022	✓	70F4022.pr5	
V850	V850E2/MN4	UPD70F3510	✓	70F3510.pr5	
V850	V850E2/MN4	UPD70F3512	✓	70F3512.pr5	
V850	V850E2/MN4	UPD70F3514	✓	70F3514.pr5	
V850	V850E2/MN4	UPD70F3515	✓	70F3515.pr5	
V850	V850E2/PG4	UPD70F3505A	✓	70F3505A.pr5	
V850	V850E2/PJ4	UPD70F3506	✓	70F3506.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
V850	V850E2/PJ4	UPD70F3507M1	✓	70F3507M1.pr5	
V850	V850E2/PJ4	UPD70F3507M2	✓	70F3507M2.pr5	
V850	V850E2/PJ4	UPD70F3508	✓	70F3508.pr5	
V850	V850E2/PJ4	UPD70F3509M1	✓	70F3509M1.pr5	
V850	V850E2/PJ4	UPD70F3509M2	✓	70F3509M2.pr5	
V850	V850E2/PG4-L	UPD70F4154	✓	70F4154.pr5	
V850	V850E2/PG4-L	UPD70F4155	✓	70F4155.pr5	
V850	V850E2/PG4-S	UPD70F4159	✓	70F4159.pr5	
V850	V850E2/SK4-H	UPD70F4018	✓	70F4018.pr5	
V850	V850E/DG3	UPD70F3416	✓	70F3416.pr5	
V850	V850E/DG3	UPD70F3417	✓	70F3417.pr5	
V850	V850E/DJ3	UPD70F3421	✓	70F3421.pr5	
V850	V850E/DJ3	UPD70F3422	✓	70F3422.pr5	
V850	V850E/DJ3	UPD70F3423	✓	70F3423.pr5	
V850	V850E/DJ3	UPD70F3424	✓	70F3424.pr5	
V850	V850E/DJ3	UPD70F3425	✓	70F3425.pr5	
V850	V850E/DJ3	UPD70F3426	✓	70F3426.pr5	
V850	V850E/DJ3	UPD70F3426A	✓	70F3426.pr5	
V850	V850E/PG2	UPD70F3413	✓	70F3413.pr5	
V850	V850E/PG2	UPD70F3414	✓	70F3414.pr5	
V850	V850E/PHO3	UPD70F3441	✓	70F3441.pr5	
V850	V850ES/DG2	UPD70F3319A	✓	70F3319A.pr5	
V850	V850ES/KE1+	UPD70F3302	✓	70F3302.pr5	
V850	V850ES/KF1+	UPD70F3306	✓	70F3306.pr5	
V850	V850ES/KF1+	UPD70F3308	✓	70F3308.pr5	
V850	V850ES/KG1+	UPD70F3311	✓	70F3311.pr5	
V850	V850ES/KG1+	UPD70F3313	✓	70F3313.pr5	
V850	V850ES/KJ1+	UPD70F3316	✓	70F3316.pr5	
V850	V850ES/KJ1+	UPD70F3318	✓	70F3318.pr5	
V850	V850ES/KE1	UPD70F3207H	✓	70F3207H.pr5	
V850	V850ES/KF1	UPD70F3210H	✓	70F3210H.pr5	
V850	V850ES/KF1	UPD70F3211H	✓	70F3211H.pr5	
V850	V850ES/KG1	UPD70F3214H	✓	70F3214H.pr5	
V850	V850ES/KG1	UPD70F3215H	✓	70F3215H.pr5	
V850	V850ES/KJ1	UPD70F3217H	✓	70F3217H.pr5	
V850	V850ES/KJ1	UPD70F3218H	✓	70F3218H.pr5	
R8C	R8C/32C	R5F21321C	✓	R5F21321C.pr5	
R8C	R8C/32C	R5F21322C	✓	R5F21322C.pr5	
R8C	R8C/32C	R5F21324C	✓	R5F21324C.pr5	
R8C	R8C/32G	R5F21324G	✓	R5F21324G.pr5	
R8C	R8C/32G	R5F21326G	✓	R5F21326G.pr5	
R8C	R8C/32H	R5F21324H	✓	R5F21324H.pr5	
R8C	R8C/32H	R5F21326H	✓	R5F21326H.pr5	
R8C	R8C/32M	R5F21321M	✓	R5F21321M.pr5	
R8C	R8C/32M	R5F21322M	✓	R5F21322M.pr5	
R8C	R8C/32M	R5F21324M	✓	R5F21324M.pr5	
R8C	R8C/33C	R5F21331C	✓	R5F21331C.pr5	
R8C	R8C/33C	R5F21332C	✓	R5F21332C.pr5	
R8C	R8C/33C	R5F21334C	✓	R5F21334C.pr5	
R8C	R8C/33C	R5F21335C	✓	R5F21335C.pr5	
R8C	R8C/33C	R5F21336C	✓	R5F21336C.pr5	
R8C	R8C/33G	R5F21334G	✓	R5F21334G.pr5	
R8C	R8C/33G	R5F21336G	✓	R5F21336G.pr5	
R8C	R8C/33H	R5F21334H	✓	R5F21334H.pr5	
R8C	R8C/33H	R5F21336H	✓	R5F21336H.pr5	
R8C	R8C/33M	R5F21331M	✓	R5F21331M.pr5	
R8C	R8C/33M	R5F21332M	✓	R5F21332M.pr5	
R8C	R8C/33M	R5F21334M	✓	R5F21334M.pr5	
R8C	R8C/33M	R5F21335M	✓	R5F21335M.pr5	
R8C	R8C/33M	R5F21336M	✓	R5F21336M.pr5	
R8C	R8C/33T	R5F21334T	✓	R5F21334T.pr5	
R8C	R8C/33T	R5F21335T	✓	R5F21335T.pr5	
R8C	R8C/33T	R5F21336T	✓	R5F21336T.pr5	
R8C	R8C/34C	R5F21344C	✓	R5F21344C.pr5	
R8C	R8C/34C	R5F21345C	✓	R5F21345C.pr5	
R8C	R8C/34C	R5F21346C	✓	R5F21346C.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
R8C	R8C/34K	R5F21348K	✓	R5F21348K.pr5	
R8C	R8C/34K	R5F2134CK	✓	R5F2134CK.pr5	
R8C	R8C/34M	R5F21344M	✓	R5F21344M.pr5	
R8C	R8C/34M	R5F21345M	✓	R5F21345M.pr5	
R8C	R8C/34M	R5F21346M	✓	R5F21346M.pr5	
R8C	R8C/34P	R5F21344P	✓	R5F21344P.pr5	
R8C	R8C/34P	R5F21346P	✓	R5F21346P.pr5	
R8C	R8C/34R	R5F21344R	✓	R5F21344R.pr5	
R8C	R8C/34R	R5F21346R	✓	R5F21346R.pr5	
R8C	R8C/34U	R5F21346U	✓	R5F21346U.pr5	
R8C	R8C/34U	R5F21348U	✓	R5F21348U.pr5	
R8C	R8C/34W	R5F21346W	✓	R5F21346W.pr5	
R8C	R8C/34W	R5F21347W	✓	R5F21347W.pr5	
R8C	R8C/34W	R5F21348W	✓	R5F21348W.pr5	
R8C	R8C/34W	R5F2134AW	✓	R5F2134AW.pr5	
R8C	R8C/34W	R5F2134CW	✓	R5F2134CW.pr5	
R8C	R8C/34X	R5F21346X	✓	R5F21346X.pr5	
R8C	R8C/34X	R5F21347X	✓	R5F21347X.pr5	
R8C	R8C/34X	R5F21348X	✓	R5F21348X.pr5	
R8C	R8C/34X	R5F2134AX	✓	R5F2134AX.pr5	
R8C	R8C/34X	R5F2134CX	✓	R5F2134CX.pr5	
R8C	R8C/34Y	R5F21346Y	✓	R5F21346Y.pr5	
R8C	R8C/34Y	R5F21347Y	✓	R5F21347Y.pr5	
R8C	R8C/34Y	R5F21348Y	✓	R5F21348Y.pr5	
R8C	R8C/34Y	R5F2134AY	✓	R5F2134AY.pr5	
R8C	R8C/34Y	R5F2134CY	✓	R5F2134CY.pr5	
R8C	R8C/34Z	R5F21346Z	✓	R5F21346Z.pr5	
R8C	R8C/34Z	R5F21347Z	✓	R5F21347Z.pr5	
R8C	R8C/34Z	R5F21348Z	✓	R5F21348Z.pr5	
R8C	R8C/34Z	R5F2134AZ	✓	R5F2134AZ.pr5	
R8C	R8C/34Z	R5F2134CZ	✓	R5F2134CZ.pr5	
R8C	R8C/35C	R5F21354C	✓	R5F21354C.pr5	
R8C	R8C/35C	R5F21355C	✓	R5F21355C.pr5	
R8C	R8C/35C	R5F21356C	✓	R5F21356C.pr5	
R8C	R8C/35C	R5F21357C	✓	R5F21357C.pr5	
R8C	R8C/35C	R5F21358C	✓	R5F21358C.pr5	
R8C	R8C/35C	R5F2135AC	✓	R5F2135AC.pr5	
R8C	R8C/35C	R5F2135CC	✓	R5F2135CC.pr5	
R8C	R8C/35M	R5F21354M	✓	R5F21354M.pr5	
R8C	R8C/35M	R5F21355M	✓	R5F21355M.pr5	
R8C	R8C/35M	R5F21356M	✓	R5F21356M.pr5	
R8C	R8C/35M	R5F21357M	✓	R5F21357M.pr5	
R8C	R8C/35M	R5F21358M	✓	R5F21358M.pr5	
R8C	R8C/35M	R5F2135AM	✓	R5F2135AM.pr5	
R8C	R8C/35M	R5F2135CM	✓	R5F2135CM.pr5	
R8C	R8C/36C	R5F21364C	✓	R5F21364C.pr5	
R8C	R8C/36C	R5F21365C	✓	R5F21365C.pr5	
R8C	R8C/36C	R5F21366C	✓	R5F21366C.pr5	
R8C	R8C/36C	R5F21367C	✓	R5F21367C.pr5	
R8C	R8C/36C	R5F21368C	✓	R5F21368C.pr5	
R8C	R8C/36C	R5F2136AC	✓	R5F2136AC.pr5	
R8C	R8C/36C	R5F2136CC	✓	R5F2136CC.pr5	
R8C	R8C/36M	R5F21364M	✓	R5F21364M.pr5	
R8C	R8C/36M	R5F21365M	✓	R5F21365M.pr5	
R8C	R8C/36M	R5F21366M	✓	R5F21366M.pr5	
R8C	R8C/36M	R5F21367M	✓	R5F21367M.pr5	
R8C	R8C/36M	R5F21368M	✓	R5F21368M.pr5	
R8C	R8C/36M	R5F2136AM	✓	R5F2136AM.pr5	
R8C	R8C/36M	R5F2136CM	✓	R5F2136CM.pr5	
R8C	R8C/36T-A	R5F21368S	✓	R5F21368S.pr5	
R8C	R8C/36T-A	R5F2136AS	✓	R5F2136AS.pr5	
R8C	R8C/36T-A	R5F2136CS	✓	R5F2136CS.pr5	
R8C	R8C/36W	R5F21368W	✓	R5F21368W.pr5	
R8C	R8C/36W	R5F2136AW	✓	R5F2136AW.pr5	
R8C	R8C/36W	R5F2136CW	✓	R5F2136CW.pr5	
R8C	R8C/36X	R5F21368X	✓	R5F21368X.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
R8C	R8C/36X	R5F2136AX	✓	R5F2136AX.pr5	
R8C	R8C/36X	R5F2136CX	✓	R5F2136CX.pr5	
R8C	R8C/36Y	R5F21368Y	✓	R5F21368Y.pr5	
R8C	R8C/36Y	R5F2136AY	✓	R5F2136AY.pr5	
R8C	R8C/36Y	R5F2136CY	✓	R5F2136CY.pr5	
R8C	R8C/36Z	R5F21368Z	✓	R5F21368Z.pr5	
R8C	R8C/36Z	R5F2136AZ	✓	R5F2136AZ.pr5	
R8C	R8C/36Z	R5F2136CZ	✓	R5F2136CZ.pr5	
R8C	R8C/38C	R5F21386C	✓	R5F21386C.pr5	
R8C	R8C/38C	R5F21387C	✓	R5F21387C.pr5	
R8C	R8C/38C	R5F21388C	✓	R5F21388C.pr5	
R8C	R8C/38C	R5F2138AC	✓	R5F2138AC.pr5	
R8C	R8C/38C	R5F2138CC	✓	R5F2138CC.pr5	
R8C	R8C/38M	R5F21386M	✓	R5F21386M.pr5	
R8C	R8C/38M	R5F21387M	✓	R5F21387M.pr5	
R8C	R8C/38M	R5F21388M	✓	R5F21388M.pr5	
R8C	R8C/38M	R5F2138AM	✓	R5F2138AM.pr5	
R8C	R8C/38M	R5F2138CM	✓	R5F2138CM.pr5	
R8C	R8C/38T-A	R5F21388S	✓	R5F21388S.pr5	
R8C	R8C/38T-A	R5F2138AS	✓	R5F2138AS.pr5	
R8C	R8C/38T-A	R5F2138CS	✓	R5F2138CS.pr5	
R8C	R8C/38W	R5F21388W	✓	R5F21388W.pr5	
R8C	R8C/38W	R5F2138AW	✓	R5F2138AW.pr5	
R8C	R8C/38W	R5F2138CW	✓	R5F2138CW.pr5	
R8C	R8C/38X	R5F21388X	✓	R5F21388X.pr5	
R8C	R8C/38X	R5F2138AX	✓	R5F2138AX.pr5	
R8C	R8C/38X	R5F2138CX	✓	R5F2138CX.pr5	
R8C	R8C/38Y	R5F21388Y	✓	R5F21388Y.pr5	
R8C	R8C/38Y	R5F2138AY	✓	R5F2138AY.pr5	
R8C	R8C/38Y	R5F2138CY	✓	R5F2138CY.pr5	
R8C	R8C/38Z	R5F21388Z	✓	R5F21388Z.pr5	
R8C	R8C/38Z	R5F2138AZ	✓	R5F2138AZ.pr5	
R8C	R8C/38Z	R5F2138CZ	✓	R5F2138CZ.pr5	
R8C	R8C/3GC	R5F213G1C	✓	R5F213G1C.pr5	
R8C	R8C/3GC	R5F213G2C	✓	R5F213G2C.pr5	
R8C	R8C/3GC	R5F213G4C	✓	R5F213G4C.pr5	
R8C	R8C/3GC	R5F213G5C	✓	R5F213G5C.pr5	
R8C	R8C/3GC	R5F213G6C	✓	R5F213G6C.pr5	
R8C	R8C/3GM	R5F213G2M	✓	R5F213G2M.pr5	
R8C	R8C/3GM	R5F213G4M	✓	R5F213G4M.pr5	
R8C	R8C/3GM	R5F213G5M	✓	R5F213G5M.pr5	
R8C	R8C/3GM	R5F213G6M	✓	R5F213G6M.pr5	
R8C	R8C/3JC	R5F213J2C	✓	R5F213J2C.pr5	
R8C	R8C/3JC	R5F213J4C	✓	R5F213J4C.pr5	
R8C	R8C/3JC	R5F213J5C	✓	R5F213J5C.pr5	
R8C	R8C/3JC	R5F213J6C	✓	R5F213J6C.pr5	
R8C	R8C/3JM	R5F213J2M	✓	R5F213J2M.pr5	
R8C	R8C/3JM	R5F213J4M	✓	R5F213J4M.pr5	
R8C	R8C/3JM	R5F213J5M	✓	R5F213J5M.pr5	
R8C	R8C/3JM	R5F213J6M	✓	R5F213J6M.pr5	
R8C	R8C/3JT	R5F213J4T	✓	R5F213J4T.pr5	
R8C	R8C/3JT	R5F213J5T	✓	R5F213J5T.pr5	
R8C	R8C/3JT	R5F213J6T	✓	R5F213J6T.pr5	
R8C	R8C/3MK	R5F213M8K	✓	R5F213M8K.pr5	
R8C	R8C/3MK	R5F213MCK	✓	R5F213MCK.pr5	
R8C	R8C/3MQ	R5F213M6Q	✓	R5F213M6Q.pr5	
R8C	R8C/3MQ	R5F213M7Q	✓	R5F213M7Q.pr5	
R8C	R8C/3MQ	R5F213M8Q	✓	R5F213M8Q.pr5	
R8C	R8C/3MQ	R5F213MAQ	✓	R5F213MAQ.pr5	
R8C	R8C/3MQ	R5F213MCQ	✓	R5F213MCQ.pr5	
R8C	R8C/3MU	R5F213M6U	✓	R5F213M6U.pr5	
R8C	R8C/3MU	R5F213M8U	✓	R5F213M8U.pr5	
R8C	R8C/3NT	R5F213N7T	✓	R5F213N7T.pr5	
R8C	R8C/3NT	R5F213N8T	✓	R5F213N8T.pr5	
R8C	R8C/3NT	R5F213NAT	✓	R5F213NAT.pr5	
R8C	R8C/3NT	R5F213NCT	✓	R5F213NCT.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
R8C	R8C/54E	R5F21546E	✓	R5F21546E.pr5	
R8C	R8C/54E	R5F21547E	✓	R5F21547E.pr5	
R8C	R8C/54E	R5F21548E	✓	R5F21548E.pr5	
R8C	R8C/54E	R5F2154AE	✓	R5F2154AE.pr5	
R8C	R8C/54E	R5F2154CE	✓	R5F2154CE.pr5	
R8C	R8C/54F	R5F21546F	✓	R5F21546F.pr5	
R8C	R8C/54F	R5F21547F	✓	R5F21547F.pr5	
R8C	R8C/54F	R5F21548F	✓	R5F21548F.pr5	
R8C	R8C/54F	R5F2154AF	✓	R5F2154AF.pr5	
R8C	R8C/54F	R5F2154CF	✓	R5F2154CF.pr5	
R8C	R8C/54G	R5F21546G	✓	R5F21546G.pr5	
R8C	R8C/54G	R5F21547G	✓	R5F21547G.pr5	
R8C	R8C/54G	R5F21548G	✓	R5F21548G.pr5	
R8C	R8C/54G	R5F2154AG	✓	R5F2154AG.pr5	
R8C	R8C/54G	R5F2154CG	✓	R5F2154CG.pr5	
R8C	R8C/54H	R5F21546H	✓	R5F21546H.pr5	
R8C	R8C/54H	R5F21547H	✓	R5F21547H.pr5	
R8C	R8C/54H	R5F21548H	✓	R5F21548H.pr5	
R8C	R8C/54H	R5F2154AH	✓	R5F2154AH.pr5	
R8C	R8C/54H	R5F2154CH	✓	R5F2154CH.pr5	
R8C	R8C/56E	R5F21566E	✓	R5F21566E.pr5	
R8C	R8C/56E	R5F21567E	✓	R5F21567E.pr5	
R8C	R8C/56E	R5F21568E	✓	R5F21568E.pr5	
R8C	R8C/56E	R5F2156AE	✓	R5F2156AE.pr5	
R8C	R8C/56E	R5F2156CE	✓	R5F2156CE.pr5	
R8C	R8C/56F	R5F21566F	✓	R5F21566F.pr5	
R8C	R8C/56F	R5F21567F	✓	R5F21567F.pr5	
R8C	R8C/56F	R5F21568F	✓	R5F21568F.pr5	
R8C	R8C/56F	R5F2156AF	✓	R5F2156AF.pr5	
R8C	R8C/56F	R5F2156CF	✓	R5F2156CF.pr5	
R8C	R8C/56G	R5F21566G	✓	R5F21566G.pr5	
R8C	R8C/56G	R5F21567G	✓	R5F21567G.pr5	
R8C	R8C/56G	R5F21568G	✓	R5F21568G.pr5	
R8C	R8C/56G	R5F2156AG	✓	R5F2156AG.pr5	
R8C	R8C/56G	R5F2156CG	✓	R5F2156CG.pr5	
R8C	R8C/56H	R5F21566H	✓	R5F21566H.pr5	
R8C	R8C/56H	R5F21567H	✓	R5F21567H.pr5	
R8C	R8C/56H	R5F21568H	✓	R5F21568H.pr5	
R8C	R8C/56H	R5F2156AH	✓	R5F2156AH.pr5	
R8C	R8C/56H	R5F2156CH	✓	R5F2156CH.pr5	
R8C	R8C/L35C	R5F2L357C	✓	R5F2L357C.pr5	
R8C	R8C/L35C	R5F2L358C	✓	R5F2L358C.pr5	
R8C	R8C/L35C	R5F2L35AC	✓	R5F2L35AC.pr5	
R8C	R8C/L35C	R5F2L35CC	✓	R5F2L35CC.pr5	
R8C	R8C/L35M	R5F2L357M	✓	R5F2L357M.pr5	
R8C	R8C/L35M	R5F2L358M	✓	R5F2L358M.pr5	
R8C	R8C/L35M	R5F2L35AM	✓	R5F2L35AM.pr5	
R8C	R8C/L35M	R5F2L35CM	✓	R5F2L35CM.pr5	
R8C	R8C/L36C	R5F2L367C	✓	R5F2L367C.pr5	
R8C	R8C/L36C	R5F2L368C	✓	R5F2L368C.pr5	
R8C	R8C/L36C	R5F2L36AC	✓	R5F2L36AC.pr5	
R8C	R8C/L36C	R5F2L36CC	✓	R5F2L36CC.pr5	
R8C	R8C/L36M	R5F2L367M	✓	R5F2L367M.pr5	
R8C	R8C/L36M	R5F2L368M	✓	R5F2L368M.pr5	
R8C	R8C/L36M	R5F2L36AM	✓	R5F2L36AM.pr5	
R8C	R8C/L36M	R5F2L36CM	✓	R5F2L36CM.pr5	
R8C	R8C/L38C	R5F2L387C	✓	R5F2L387C.pr5	
R8C	R8C/L38C	R5F2L388C	✓	R5F2L388C.pr5	
R8C	R8C/L38C	R5F2L38AC	✓	R5F2L38AC.pr5	
R8C	R8C/L38C	R5F2L38CC	✓	R5F2L38CC.pr5	
R8C	R8C/L38M	R5F2L387M	✓	R5F2L387M.pr5	
R8C	R8C/L38M	R5F2L388M	✓	R5F2L388M.pr5	
R8C	R8C/L38M	R5F2L38AM	✓	R5F2L38AM.pr5	
R8C	R8C/L38M	R5F2L38CM	✓	R5F2L38CM.pr5	
R8C	R8C/L3AC	R5F2L3A7C	✓	R5F2L3A7C.pr5	
R8C	R8C/L3AC	R5F2L3A8C	✓	R5F2L3A8C.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
R8C	R8C/L3AC	R5F2L3AAC	✓	R5F2L3AAC.pr5	
R8C	R8C/L3AC	R5F2L3ACC	✓	R5F2L3ACC.pr5	
R8C	R8C/L3AM	R5F2L3A7M	✓	R5F2L3A7M.pr5	
R8C	R8C/L3AM	R5F2L3A8M	✓	R5F2L3A8M.pr5	
R8C	R8C/L3AM	R5F2L3AAM	✓	R5F2L3AAM.pr5	
R8C	R8C/L3AM	R5F2L3ACM	✓	R5F2L3ACM.pr5	
R8C	R8C/LA3A	R5F2LA32A	✓	R5F2LA32A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA3A	R5F2LA32A	✓	R5F2LA32A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA3A	R5F2LA34A	✓	R5F2LA34A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA3A	R5F2LA34A	✓	R5F2LA34A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA3A	R5F2LA36A	✓	R5F2LA36A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA3A	R5F2LA36A	✓	R5F2LA36A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA3A	R5F2LA38A	✓	R5F2LA38A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA3A	R5F2LA38A	✓	R5F2LA38A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA5A	R5F2LA52A	✓	R5F2LA52A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA5A	R5F2LA52A	✓	R5F2LA52A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA5A	R5F2LA54A	✓	R5F2LA54A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA5A	R5F2LA54A	✓	R5F2LA54A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA5A	R5F2LA56A	✓	R5F2LA56A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA5A	R5F2LA56A	✓	R5F2LA56A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA5A	R5F2LA58A	✓	R5F2LA58A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA5A	R5F2LA58A	✓	R5F2LA58A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA6A	R5F2LA64A	✓	R5F2LA64A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA6A	R5F2LA64A	✓	R5F2LA64A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA6A	R5F2LA66A	✓	R5F2LA66A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA6A	R5F2LA66A	✓	R5F2LA66A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA6A	R5F2LA67A	✓	R5F2LA67A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA6A	R5F2LA67A	✓	R5F2LA67A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA6A	R5F2LA68A	✓	R5F2LA68A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA6A	R5F2LA68A	✓	R5F2LA68A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA6A	R5F2LA6AA	✓	R5F2LA6AA.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA6A	R5F2LA6AA	✓	R5F2LA6AA LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA6A	R5F2LA6CA	✓	R5F2LA6CA.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA6A	R5F2LA6CA	✓	R5F2LA6CA LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA8A	R5F2LA84A	✓	R5F2LA84A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA8A	R5F2LA84A	✓	R5F2LA84A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA8A	R5F2LA86A	✓	R5F2LA86A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA8A	R5F2LA86A	✓	R5F2LA86A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA8A	R5F2LA87A	✓	R5F2LA87A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA8A	R5F2LA87A	✓	R5F2LA87A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA8A	R5F2LA88A	✓	R5F2LA88A.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA8A	R5F2LA88A	✓	R5F2LA88A LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA8A	R5F2LA8AA	✓	R5F2LA8AA.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA8A	R5F2LA8AA	✓	R5F2LA8AA LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LA8A	R5F2LA8CA	✓	R5F2LA8CA.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LA8A	R5F2LA8CA	✓	R5F2LA8CA LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LAPS	R5F2LAP6S	✓	R5F2LAP6S.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LAPS	R5F2LAP6S	✓	R5F2LAP6S LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LAPS	R5F2LAP7S	✓	R5F2LAP7S.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LAPS	R5F2LAP7S	✓	R5F2LAP7S LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LAPS	R5F2LAP8S	✓	R5F2LAP8S.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LAPS	R5F2LAP8S	✓	R5F2LAP8S LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LAPS	R5F2LAPAS	✓	R5F2LAPAS.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LAPS	R5F2LAPAS	✓	R5F2LAPAS LV.pr5	for 1.8V<=VCC and VCC<2.7V
R8C	R8C/LAPS	R5F2LAPCS	✓	R5F2LAPCS.pr5	for 2.7V<=VCC and VCC<=5.5V
R8C	R8C/LAPS	R5F2LAPCS	✓	R5F2LAPCS LV.pr5	for 1.8V<=VCC and VCC<2.7V
SuperH	SH7146	R5F71464	✓	R5F71464.pr5	
SuperH	SH7149	R5F71494	✓	R5F71494.pr5	
SuperH	SH7214	R5F72145	✓	R5F72145.pr5	
SuperH	SH7214	R5F72146	✓	R5F72146.pr5	
SuperH	SH7214	R5F72147	✓	R5F72147.pr5	
SuperH	SH7216	R5F72165	✓	R5F72165.pr5	
SuperH	SH7216	R5F72166	✓	R5F72166.pr5	
SuperH	SH7216	R5F72167	✓	R5F72167.pr5	
SuperH	SH7253	R5F72531	✓	R5F72531.pr5	
SuperH	SH7253	R5F72533	✓	R5F72533.pr5	

Family	Group	Target Device	PG-FP6	Parameter File	Additional information
				File Name	
SuperH	SH7253	R5F72533D	✓	R5F72533D.pr5	
SuperH	SH72A0	R5F72A06x2	✓	R5F72A06x2.pr5	
SuperH	SH72A0	R5F72A06x3	✓	R5F72A06x3.pr5	
SuperH	SH72A0	R5F72A08xA	✓	R5F72A08xA.pr5	
SuperH	SH72A2	R5F72A26x2	✓	R5F72A26x2.pr5	
SuperH	SH72A2	R5F72A26x3	✓	R5F72A26x3.pr5	
SuperH	SH72A2	R5F72A28xA	✓	R5F72A28xA.pr5	