
IDT[®]
Migrating from the Intel
21150 to the Tsi350[™]
PCI-to-PCI Bridge

80D5000_AN004_03

September 20, 2009

6024 Silver Creek Valley Road San Jose, California 95138

Telephone: (408) 284-8200 • FAX: (408) 284-3572

Printed in U.S.A.

©2009 Integrated Device Technology, Inc.

GENERAL DISCLAIMER

Integrated Device Technology, Inc. ("IDT") reserves the right to make changes to its products or specifications at any time, without notice, in order to improve design or performance. IDT does not assume responsibility for use of any circuitry described herein other than the circuitry embodied in an IDT product. Disclosure of the information herein does not convey a license or any other right, by implication or otherwise, in any patent, trademark, or other intellectual property right of IDT. IDT products may contain errata which can affect product performance to a minor or immaterial degree. Current characterized errata will be made available upon request. Items identified herein as "reserved" or "undefined" are reserved for future definition. IDT does not assume responsibility for conflicts or incompatibilities arising from the future definition of such items. IDT products have not been designed, tested, or manufactured for use in, and thus are not warranted for, applications where the failure, malfunction, or any inaccuracy in the application carries a risk of death, serious bodily injury, or damage to tangible property. Code examples provided herein by IDT are for illustrative purposes only and should not be relied upon for developing applications. Any use of such code examples shall be at the user's sole risk.

Copyright © 2009 Integrated Device Technology, Inc.
All Rights Reserved.

The IDT logo is registered to Integrated Device Technology, Inc. IDT is a trademark of Integrated Device Technology, Inc.

1. Migrating from the Intel 21150 to the Tsi350 PCI-to-PCI Bridge

This application note details the differences between the Tsi350 and the Intel 21150. The following topics are discussed in this application note:

- “Overview” on page 3
- “Feature Compatibility” on page 3
- “Software Compatibility” on page 4
- “Package Compatibility” on page 5

1.1 Overview

The Tsi350 can be used as a drop in replacement for the Intel 21150 without any modifications to an existing board design.

1.2 Feature Compatibility

The Tsi350 is feature and pinout compatible with the Intel 21150 with the exception of the following.

1.2.1 Mode Select Inputs

The Mode Select Inputs are a Tsi350 feature that can be used to configure the Tsi350 for different modes of operation. [Table 1 on page 4](#) describes the Tsi350 Mode Select Input functionality.

1.2.1.1 208-pin PQFP

The Tsi350 defines the Mode Select Inputs (MS0 and MS1) on pins 155 and 106. The Intel 21150 defines pin 155 as VDD and pin 106 as VSS. The Tsi350 is a direct replacement for the Intel 21150 without making any board modification.

1.2.1.2 256-pin PBGA

The Tsi350 defines the Mode Select Inputs (MS0 and MS1) on pins B14 and R16. The Intel 21150 defines pin B14 as VDD and pin R16 as VSS. The Tsi350 is a direct replacement for the Intel 21150 without making any board modification.

Table 1: Tsi350 Mode Select Inputs

MS0 (Pin 155)	MS1 (Pin 106)	Mode
0	0	Compact PCI Hot-swap friendly PCI Bus Power Management Interface Specification (Rev. 1.1). GPIO[3] functions as HS_SWITCH_N. Synchronous Mode (P_CLK used as source for S_CLK_O[9:0]).
1	X	Compact PCI Hot-swap disabled. PCI Bus Power Management Interface Specification (Rev. 1.1). GPIO[3] functions as GPIO[3]. Synchronous Mode (P_CLK used as source for S_CLK_O[9:0]).
0	1	Compact PCI Hot-swap disabled. PCI Bus Power Management Interface Specification (Rev. 1.1). GPIO[3] functions as GPIO[3]. Synchronous Mode (P_CLK used as source for S_CLK_O[9:0]).
1	1	Asynchronous Mode (MSK_IN is used as the source for S_CLK_O[9:0]).

1.2.2 Fast Back-to-Back Transactions

The Intel 21150 supports fast back-to-back transactions as both a target and a master. The Tsi350 supports fast back-to-back transactions as a target, but does not have the ability to generate fast back-to-back transactions as a master.

1.3 Software Compatibility

The Tsi350 is fully software compatible with the Intel 21150 within the standard PCI configuration space, with the exception of the values returned by the vendor ID, device ID, and revision ID registers.



Refer to the *Tsi350 User Manual* for more information on using device specific features and registers which are outside the standard PCI configuration space.

1.3.1 Vendor ID Register, Offset 01h – 00h

The Intel 21150 returns 16'h104C when this register is read.

Bits	Type	Value on Reset	Description
15:0	R	16'h1142	Vendor ID This 16-bit read only field contains vendor ID allocated by the PCI SIG. All bits in this register are read only.

1.3.2 Device ID Register, Offset 03h – 02h

The Intel 21150 returns 16'hAC28 when this register is read.

Bits	Type	Value on Reset	Description
15:0	R	16'h0150	Device ID This 16-bit field represents Tsi350 bridge device.

1.3.3 Revision ID Register, Offset 08h

The Intel 21150 returns 8'h02 for a read to this register.

Bits	Type	Value on Reset	Description
7:4	R	8'h0	Revision ID This field specifies the Revision ID for the Tsi350 bridge device.

1.4 Package Compatibility

The Tsi350 is drop in pin compatible with the Intel 21150. The Tsi350 is available in 208-QFP and 256-BGA packages.



CORPORATE HEADQUARTERS
6024 Silver Creek Valley Road
San Jose, CA 95138

for SALES:
800-345-7015 or 408-284-8200
fax: 408-284-2775
www.idt.com

for Tech Support:
email: ssdhelp@idt.com
phone: 408-284-8208
document: 80D5000_AN004_03