


REVISIONS			DATE	APPROVED
REV	DESCRIPTION			
00	INITIAL RELEASE		04/28/00	KLB
01	COMBINED PAD & LAND PATTERN		4/05/13	KLB

SYMBOL	JEDEC VARIATION			NOTE
	MIN	NOM	MAX	
A	1.30	1.40	1.50	
A1	.31	.36	.41	
A2	.65	.70	.75	
D	11.00 BSC			
D1	9.00 BSC			
E	11.00 BSC			
E1	9.00 BSC			
MD	10			3
ME	10			3
N	100			3
e	1.00 BSC			
b	.41	.46	.51	4
ddd	-	-	.15	
bbb	-	-	.08	
ccc	-	-	.10	
ddd	-	-	.12	



TOP VIEW

SIDE VIEW

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS
DECIMAL
XX ±0.10
XXX ±0.05
XXXX ±0.03



IDT 6024 SILVER CREEK VALLEY ROAD
San Jose, CA 95138
PHONE: (408) 284-8200
FAX: (408) 492-8674
www.idt.com

APPROVALS
DRAWN: pyp
CHECKED: []
DATE: 04/28/00

DRAWING No. BC100 PACKAGE OUTLINE
11 X 11 mm BODY CABGA

PSC-4084
DO NOT SCALE DRAWING
SIZE: C
SCALE: N/A
REV: 01
SHEET 1 OF 3

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	04/28/00	DP
01	COMBINED POD & LAND PATTERN	04/05/13	KLB



BOTTOM VIEW
(100 SOLDER BALLS)

NOTES: UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS AND TOLERANCES CONFORM TO ASME Y14.5M-1994.
 2. SEATING PLANE AND PRIMARY DATUM C ARE DEFINED BY THE SPHERICAL CROWNS OF THE SOLDER BALLS.
 3. "AD" IS THE BALL MATRIX SIZE IN THE "D" DIRECTION.
"AE" IS THE BALL MATRIX SIZE IN THE "E" DIRECTION.
"N" IS THE NUMBER OF SOLDER BALLS.
 4. DIMENSION "a" IS MEASURED AT THE MAXIMUM SOLDER BALL DIAMETER, PARALLEL TO PRIMARY DATUM C.
 5. "A1" ID CORNER MUST BE IDENTIFIED. IDENTIFICATION MAY BE BY MEANS OF CHAMFER, METALLIZED OR INK MARK, INDENTATION OR OTHER FEATURE OF THE PACKAGE BODY.
- ALL DIMENSIONS ARE IN MILLIMETERS.


UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS

DECIMAL XX.XX ±0.10	ANGULAR °
XX.X ±0.06	
XXXX ±0.03	

IDT 6024 SILVER CREEK VALLEY ROAD
www.idt.com San Jose, CA 95138
PHONE: (408) 284-8200
FAX: (408) 492-8674

APPROVALS	DATE	DRAWING No.	SIZE	SCALE	REV
DRAWN P3C/P	04/28/00	BC100 PACKAGE OUTLINE	C	N/A	01
CHECKED		11.0 X 11.0 mm BODY CABGA			
		PSC-4084			
		DO NOT SCALE DRAWING			SHEET 2 OF 3

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	4/16/12	DP
01	COMBINED POD & LAND PATTERN	4/05/13	KLB



RECOMMENDED LAND PATTERN DIMENSION

- NOTE:
- 1) ALL dimensions are in mm, Angles in degrees.
 - 2) Top down view, as view on PCB.
 - 3) NSMD Land Pattern Assumed
 - 4) Land Pattern Recommendation as per IPC-7351B generic requirement for surface mount design and Land Pattern.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS		DATE	
DECIMAL	ANGULAR	1/12/12	
XX.XX	XX°XX'XX"		
XXX.XXX	°XX'XX"		
APPROVALS			
DRAWN <i>DP</i>			
CHECKED			
DRAWING No. BC/BCG100 LAND PATTERN 11.0 X 11.0 mm BODY CABGA		SIZE	SCALE
PSC-4084		C	N/A
DO NOT SCALE DRAWING		REV	01
		SHEET	3 OF 3

IDT 6024 SILVER CREEK VALLEY ROAD
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 492-8674
 www.IDT.com