




REVISIONS			
DATE CREATED	REV	DESCRIPTION	AUTHOR
10/14/16	00	INITIAL RELEASE	CM
REFER TO DCP FOR OFFICIAL RELEASE DATE			



TOP VIEW



BOTTOM VIEW



SIDE VIEW

SYMBOL	DIMENSION		
	MIN	NOM	MAX
b	0.15	0.20	0.25
D	5.00 BSC		
E	5.00 BSC		
D2	3.50	3.60	3.70
E2	3.50	3.60	3.70
L	0.30	0.35	0.40
L1	0.45 REF		
L2	0.30 REF		
e	0.40 BSC		
A	0.70	0.75	0.80
A1	0.00	0.02	0.05
A3	0.2 REF		
k	0.25 REF		
aaa	0.10		
bbb	0.07		
ccc	0.10		
ddd	0.05		
eee	0.08		
fff	0.10		

NOTES:

1. ALL DIMENSIONING AND TOLERANCING CONFORM TO ANSI Y14.5M-1982
2. ALL DIMENSIONS ARE IN MILLIMETERS.
3. ND AND NE REFER TO THE NUMBER OF TERMINALS ON EACH D AND E SIDE RESPECTIVELY.

TOLERANCES UNLESS SPECIFIED
 DECIMAL:
 X±.1
 XX±.05
 XXX±.030
 ANGULAR: ±1°




6024 SILVER CREEK VALLEY ROAD. SAN JOSE, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572

TITLND/NDG44 PACKAGE OUTLINE
 5.0 x 5.0 mm BODY,EPAD 3.60mm SQ.
 0.40 mm PITCH QFN

SIZE	DRAWING No.	REV
C	PSC-4678	00

REVISIONS			
DATE CREATED	REV	DESCRIPTION	AUTHOR
10/14/16	00	INITIAL RELEASE	CM
REFER TO DCP FOR OFFICIAL RELEASE DATE			



RECOMMENDED LAND PATTERN

NOTES:

1. ALL DIMENSIONS ARE IN mm. ANGLES IN DEGREES.
2. TOP DOWN VIEW AS VIEWED ON PCB.
3. COMPONENT OUTLINE SHOWS FOR REFERENCE IN GREEN.
4. LAND PATTERN IN BLUE. NSMD PATTERN ASSUMED.
5. LAND PATTERN RECOMMENDATION PER IPC-7351B GENERIC REQUIREMENT FOR SURFACE MOUNT DESIGN AND LAND PATTERN.

TOLERANCES
UNLESS SPECIFIED
DECIMAL:
X±.1
XX±.05
XXX±.030

ANGULAR: ±1°



6024 SILVER CREEK
VALLEY ROAD. SAN JOSE,
CA 95138
PHONE: (408) 284-8200
FAX: (408) 284-3572

TITLE/NDG44 PACKAGE OUTLINE
5.0 x 5.0 mm BODY, EPAD 3.60mm SQ.
0.40 mm PITCH QFN

SIZE	DRAWING No.	REV
C	PSC-4678	00

DO NOT SCALE DRAWING

SHEET 2 OF 2