


DATE		REVISIONS	
CREATED	REV	DESCRIPTION	AUTHOR
3/7/17	00	INITIAL RELEASE	JH
NOTE: REFER TO DCP FOR OFFICIAL RELEASE DATE			


NOTES:

1. ALL DIMENSIONS AND TOLERANCES ARE PER ASME Y14.5M-1994.
 2. ALL DIMENSIONS ARE IN MILLIMETERS.
- Ⓜ SEATING PLANE AND PRIMARY DATUM -C- ARE DEFINED BY THE CONTACT POINTS OF THREE OR MORE SOLDER BALLS THAT SUPPORT THE DEVICE WHEN PLACED ON A TOP OF A PLANAR SURFACE.
- Ⓜ BOTTOM PIN#1 INDICATOR OPTIONAL.




TOP VIEW

SIDE VIEW




BOTTOM VIEW



TOLERANCES UNLESS SPECIFIED DECIMAL ANGULAR XXX± 0.05 ± XXX± 0.012 XXXX±			6024 SILVER CREEK VALLEY ROAD, SAN JOSE, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-3572
	www.IDT.com		
TITLE: AXG119 PACKAGE OUTLINE 4.756x 4.756mm BODY 0.4mm PITCH DSBGA			
SIZE	DRAWING No.	REV	
C	PSC-4498	00	
DO NOT SCALE DRAWING			SHEET 1 OF 2


DATE CREATED		REVISIONS	
REV	DESCRIPTION	AUTHOR	
3/7/17	00	INITIAL RELEASE	
NOTE: REFER TO DCP FOR OFFICIAL RELEASE DATE			



RECOMMENDED LAND PATTERN DIMENSION

NOTES:

- 1) ALL DIMENSIONS ARE IN mm, ANGLES IN DEGREES
- 2) TOP DOWN VIEW, AS VIEW ON PCB
- 3) NSMD LAND PATTERN ASSUMED
- 4) LAND PATTERN RECOMMENDATION AS PER IPC-7351B
GENERIC REQUIREMENT FOR SURFACE MOUNT DESIG AND LAND PATTERN

TOLERANCES UNLESS SPECIFIED DECIMAL ANGULAR XX± 0.05 ± XXX± 0.012 XXXX±			6024 SILVER CREEK VALLEY ROAD, SAN JOSE, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-3572
	www.IDT.com		
TITLE: AXG119 PACKAGE OUTLINE 4.756x 4.756mm BODY 0.4mm PITCH DSBGA			
SIZE	DRAWING No.	REV	
C	PSC-4498	00	
DO NOT SCALE DRAWING			SHEET 2 OF 2