

Separate Sheet

Product Specifications of the RX130 Group

Group name		RX130			
Part No.*		R5F51305ADxx	R5F51303ADxx	R5F51305AGxx	R5F5130AGxx
Internal memory	Flash ROM	128 KB	64 KB	128 KB	64 KB
	RAM	16 KB	10 KB	16 KB	10 KB
	E2 data flash	8 KB			
Power supply voltage		1.8 - 5.5 V			
Maximum operating frequency		32 MHz			
Operating temperature		-40 - +85 °C		-40 - +105 °C	
CPU core		RX CPU <ul style="list-style-type: none"> • General purpose: Sixteen 32-bit registers • Control : Eight 32-bit registers • Accumulator: 64-bit registers • Multiplier: 32-bit multiplier • Divider: Yes • Multiply-accumulator: Yes (two types: memory-to-memory operations and register-to-register operations) • Basic instructions: 73 Variable-length instruction format • DSP instructions: 23 			
On-chip peripheral functions		Transfer functions	<ul style="list-style-type: none"> • Data transfer controller (DTCa) 		
		Timers	<ul style="list-style-type: none"> • Multi-function timer pulse unit 2: 16 bits × 6 channels (MTU2a) • Port output enable 2 (POE2a) • Compare match timer (CMT): 16 bits × 2 channels × 1 units • Independent watchdog timer (IWDTa): 14 bit × 1 channel • Real-time clock (RTCc) : 1 channel • Low Power Timer (LPT) : 16 bit × 1 channel • 8-bit timer (TMR) : (8 bit × 2 channels) × 2 units 		
		Communication functions	<ul style="list-style-type: none"> • Serial communications interface (SCIg) : 3 channels • Serial communications interface (SCIh) : 1 channels • I2C bus interface (RIICa) : 1 channels • Serial peripheral interface (RSPIa) : 1 channels 		
		Cap touch functions	<ul style="list-style-type: none"> • 80-pin [36 channels], 64-pin [32 channels], 48-pin [24 		

		channels], Self-capacitance and mutual capacitance are supported.
	Analog functions	<ul style="list-style-type: none"> • 12-bit A/D converter (S12ADE) : 80-pin [17 channels], 64-pin [14 channels], 48-pin [10 channels] • D/A converter (DAa): 80-pin [2 channels], 64-pin [2 channels]、 48-pin [N/A] • Comparator B(CMPBa) : 2 channels
	Safety functions	<ul style="list-style-type: none"> • Clock frequency accuracy measurement circuit (CAC) • Data operation circuit (DOC) • 14-bit Independent watchdog timer (IWDTa) • Detection of 12-bit A/D converter analog input disconnection • CRC calculator (CRC)
	Clock generation circuit	<ul style="list-style-type: none"> • Main clock oscillator • Sub-clock oscillator • Low-speed on-chip oscillator (LOCO) • High-speed on-chip oscillator (HOCO) • IWDT-dedicated on-chip oscillator • PLL frequency synthesizer
	Others	<ul style="list-style-type: none"> • Event Link Controller (ELC) • Multi-function Pin Controller (MPC) • Power-on Reset Circuit (POR) • Voltage Detection Circuit (LVDAb) • Temperature Sensor (TEMPSA) • Unique ID
On-chip debugging function	Yes (with trace function)	
Low power consumption modes	3 modes <ul style="list-style-type: none"> • Sleep mode • Deep sleep mode • Software standby mode 	
Packages	80-pin LFQFP(PLQP0080KB-B)12 × 12 mm, 0.5 mm pitch 64-pin LFQFP(PLQP0064KB-C)10 × 10 mm, 0.5 mm pitch 64-pin LQFP(PLQP0064GA-A)14 × 14 mm, 0.8mm pitch 48-pin LFQFP(PLQP0048KB-B)7 × 7 mm, 0.5 mm pitch 48-pin HWQFN(PWQN0048KB-A)7 × 7 mm, 0.5 mm pitch	

(Remarks) SuperFlash memory technology used in Renesas Electronics' RX231 MCUs is licensed from Silicon Storage Technology Inc. SuperFlash is a registered trademark of Silicon Storage Technology in the U.S., Japan, and other countries. All registered trademarks or trademarks are the property of their respective owners.