

---

**M16C/5LD, 5L, 5M, 6C Groups**

Outputting a PWM Waveform  
Using Timer S in Inverted Waveform Output Mode

R01AN0392EJ0101  
Rev. 1.01  
June 30, 2011

---

**Abstract**

This document describes a method for outputting a PWM waveform using timer S in inverted waveform output mode with the M16C/5LD, 5L, 5M, and 6C Group microcomputers (MCUs).

**Products**

MCUs: M16C/5LD, 5L, 5M, 6C Groups

When using this application note with other Renesas MCUs, careful evaluation is recommended after making modifications to comply with the alternate MCU.

## Contents

Abstract .....	1
Products .....	1
1. Introduction .....	3
1.1 Waveform Generation Function .....	3
1.2 Inverted Waveform Output Mode .....	3
2. Software .....	5
2.1 Operation Overview .....	5
2.2 Flowcharts .....	6
2.2.1 Main Processing .....	6
2.2.2 Peripheral Function Initialization Function .....	7
2.2.3 Base Timer Interrupt Handling Function .....	8
3. Application Example .....	9
3.1 Changing the Period .....	9
4. Sample Code .....	11
5. Reference Documents .....	11

## 1. Introduction

Timer S has an input capture/output compare function (IC/OC). The input capture (IC) is used for time measurement and the output compare (OC) is used for waveform generation. The IC/OC has one 16-bit free-running base timer and eight channels for timer measurement and waveform generation.

### 1.1 Waveform Generation Function

Waveforms are generated based on the values of the base timer and the G1POj register (j = 0 to 7). Table 1.1 lists the Waveform Generation Function Settings. Items marked with a check mark (✓) are described in this chapter.

**Table 1.1 Waveform Generation Function Settings**

Item	Setting
Waveform generation function	Single-phase waveform output mode
	✓ Inverted waveform output mode
	Set/reset waveform output mode (SR waveform output mode)
Base timer reset source	✓ Base timer is reset when the base timer and G1BTRR register values match
	Base timer is reset when the base timer and G1PO0 register values match
	Base timer is reset when the input level to the INT1 pin is low
Initial output level selection	✓ Output low as default level
	Output high as default level
Output level inversion selection	✓ Output level not inverted
	Output level inverted
Channels	✓ Channel 0
	Channel 1
	✓ Channel 2
	Channel 3
	✓ Channel 4
	Channel 5
	✓ Channel 6
	Channel 7
Interrupts	✓ IC/OC base timer interrupt
	IC/OC interrupt 0
	IC/OC interrupt 1
	IC/OC channel 0 interrupt
	IC/OC channel 1 interrupt
	IC/OC channel 2 interrupt
	IC/OC channel 3 interrupt

### 1.2 Inverted Waveform Output Mode

When the base timer and G1POj register values match, the output level from the OUTC1\_j pin becomes inverted (j = 0, 2, 4, 6). When using inverted waveform output mode, set the base timer to increment mode or increment/decrement mode.

The following is an explanation for setting the PWM period using the G1BTRR register, and setting low and high widths using the G1POj register (j = 0 to 7). PWM waveforms are output from the OUTC1\_j pin corresponding to channel j. fBT1 is the operating clock for the base timer.

(1) PWM period setting

The base timer is reset when the base timer and G1BTRR register values match. If the G1BTRR register setting value is n, the PWM period is as follows:

$$\text{PWM period: } \frac{2(n+2)}{f_{BT1}}$$

When changing the period, change the G1BT register in the interrupt handling without changing the G1BTRR register, or set the BTS bit in the G1BCR1 register to 0 before changing the G1BTRR register.

(2) High width and low width settings

Use the waveform generation function while in inverted waveform output mode for channel j. If the G1BTRR register setting value is n, the high width and low width are as follows:

$$\text{High width, low width: } \frac{n+2}{f_{BT1}}$$

Figure 1.1 shows the operation of inverted waveform output mode when the base timer is reset by the base timer and G1BTRR register values matching.




Figure 1.1 Inverted Waveform Output Mode Operation

## 2. Software

### 2.1 Operation Overview

The OUTC1\_k (P2\_k) pin is used by timer S and outputs a PWM waveform (k = 0, 2, 4, 6). Every 10 times a base timer interrupt is generated, the G1POk register is rewritten in the base timer interrupt handler, and the width from the base timer becoming 0 to the waveform inverting changes.

Clock statistics are as follows:

- Main clock: 20 MHz
- Base timer operating clock (fBT1): 1 MHz

Figure 2.1 shows the Pin Output, and Table 2.1 lists the Inverted Width Setting Values.




Figure 2.1 Pin Output

Table 2.1 Inverted Width Setting Values

Output Pin	Register	Inverted Width: $\frac{m}{f_{BT1}}$	
		(1)	(2)
OUTC1_0 (P2_0)	G1PO0	1.0 ms (m = 1000)	2.0 ms (m = 2000)
OUTC1_2 (P2_2)	G1PO2	1.5 ms (m = 1500)	2.5 ms (m = 2500)
OUTC1_4 (P2_4)	G1PO4	2.0 ms (m = 2000)	3.0 ms (m = 3000)
OUTC1_6 (P2_6)	G1PO6	2.5 ms (m = 2500)	3.5 ms (m = 3500)

## 2.2 Flowcharts

### 2.2.1 Main Processing

Figure 2.2 shows the Main Processing.




Figure 2.2 Main Processing

## 2.2.2 Peripheral Function Initialization Function

Figure 2.3 shows the Peripheral Function Initialization Function.




Figure 2.3 Peripheral Function Initialization Function

### 2.2.3 Base Timer Interrupt Handling Function

Figure 2.4 shows the Base Timer Interrupt Handling Function.




Figure 2.4 Base Timer Interrupt Handling Function



### 3. Application Example

#### 3.1 Changing the Period


The PWM output period can be set using the G1BTRR register when the RST4 bit in the G1BCR0 register is 1, or it can be set using the G1PO0 register when the RST1 bit in the G1BCR1 register is 1. When changing the period during a count operation, after setting the BTS bit in the G1BCR1 register to 0 (base timer reset), wait at least one cycle of fBT1, and rewrite the G1BTRR or G1PO0 register. The procedure is as follows:

- (1) Set the BTS bit to 0. (1)
- (2) Wait at least one cycle of fBT1.
- (3) Rewrite the register where the period was set.
- (4) Set the BTS bit to 1.


Note:

1. One cycle of fBT1 passes between setting the BTS bit to 0 and the count stopping.

Figure 3.1 shows Output when Changing the Period Before the Base Timer and G1POj Register Values Match. Figure 3.2 shows Output when Changing the Period After the Base Timer and G1POj Register Values Match.



**Figure 3.1 Output when Changing the Period Before the Base Timer and G1POj Register Values Match**



**Figure 3.2 Output when Changing the Period After the Base Timer and G1PO $j$  Register Values Match**

## 4. Sample Code

Sample code can be downloaded from the Renesas Electronics website.

## 5. Reference Documents

M16C/5LD, M16C/56D Group User's Manual: Hardware Rev.1.10

M16C/5L, M16C/56 Group User's Manual: Hardware Rev.1.00

M16C/5M, M16C/57 Group User's Manual: Hardware Rev.1.01

M16C/6C Group User's Manual: Hardware Rev.2.00

The latest versions can be downloaded from the Renesas Electronics website.

Technical Update/Technical News

The latest information can be downloaded from the Renesas Electronics website.

C Compiler Manual

M16C Series, R8C Family C Compiler Package V.5.45

C Compiler User's Manual Rev.2.00

The latest version can be downloaded from the Renesas Electronics website.

## Website and Support

Renesas Electronics website

<http://www.renesas.com/>

Inquiries

<http://www.renesas.com/inquiry>

Revision History	M16C/5LD, 5L, 5M, 6C Groups Outputting a PWM Waveform Using Timer S in Inverted Waveform Output Mode
------------------	--

Rev.	Date	Description	
		Page	Summary
1.00	Sep. 30, 2010	—	First edition issued
1.01	June 30, 2011	—	Added chapter 3

All trademarks and registered trademarks are the property of their respective owners.
---

## General Precautions in the Handling of MPU/MCU Products

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this manual, refer to the relevant sections of the manual. If the descriptions under General Precautions in the Handling of MPU/MCU Products and in the body of the manual differ from each other, the description in the body of the manual takes precedence.

### 1. Handling of Unused Pins

Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.

- The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.

### 2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.

In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

### 3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

- The reserved addresses are provided for the possible future expansion of functions. Do not access these addresses; the correct operation of LSI is not guaranteed if they are accessed.

### 4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

- When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.

### 5. Differences between Products

Before changing from one product to another, i.e. to one with a different part number, confirm that the change will not lead to problems.

- The characteristics of MPU/MCU in the same group but having different part numbers may differ because of the differences in internal memory capacity and layout pattern. When changing to products of different part numbers, implement a system-evaluation test for each of the products.

## Notice

- All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.  
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.  
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.  
"Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.  
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.  
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



### SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

**Renesas Electronics America Inc.**  
2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A.  
Tel: +1-408-586-6000, Fax: +1-408-588-6130

**Renesas Electronics Canada Limited**  
1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada  
Tel: +1-905-898-5441, Fax: +1-905-898-3220

**Renesas Electronics Europe Limited**  
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.  
Tel: +44-1628-585-100, Fax: +44-1628-585-900

**Renesas Electronics Europe GmbH**  
Arcadiastrasse 10, 40472 Düsseldorf, Germany  
Tel: +49-211-65030, Fax: +49-211-6503-1327

**Renesas Electronics (China) Co., Ltd.**  
7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China  
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

**Renesas Electronics (Shanghai) Co., Ltd.**  
Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China  
Tel: +86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

**Renesas Electronics Hong Kong Limited**  
Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong  
Tel: +852-2886-9318, Fax: +852 2886-9022/9044

**Renesas Electronics Taiwan Co., Ltd.**  
7F, No. 363 Fu Shing North Road Taipei, Taiwan  
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

**Renesas Electronics Singapore Pte. Ltd.**  
1 HarbourFront Avenue, #06-10, Keppel Bay Tower, Singapore 098632  
Tel: +65-6213-0200, Fax: +65-6276-8001

**Renesas Electronics Malaysia Sdn.Bhd.**  
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jin Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

**Renesas Electronics Korea Co., Ltd.**  
11F., Samik Lavied' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea  
Tel: +82-2-558-3737, Fax: +82-2-558-5141