
RX72M Group

R01AN6882EJ0110

Rev.1.10

Aug. 31, 2023

Communications Board Sample program Package

Introduction

This document is an application note for the industrial network protocol stack sample program package for RX72M. This application note describes the structures of this package and usage of the sample programs.

Target Device

RX72M Group

Related Documents

- RX72M Group User's Manual: Hardware (R01UH0804EJ0100)

Contents

1. Overview	3
1.1 Operating Environment	3
2. About sample program package	4
2.1 Overall structure	4
2.2 Package folder structure	5
3. Usage	6

1. Overview

This application note applies to the industrial network protocol stack sample program package for RX72M and the protocol stack common API library.

1.1 Operating Environment

This sample program package runs under the operating environment below.

Table 1.1 Operating Environment

Item	Description
Board	RX72M communications board TS-TCS07298 from Tessera Technology
CPU	RX CPU (RXv3)
Operating frequency	CPU clock (CPUCLK): 240 MHz
Operating voltage	3.3 V
Operating modes	Single chip mode
Device requirements	R5F572MNDDBD <ul style="list-style-type: none"> • Code flash memory Capacity: 4 Mbytes ROM cache: 8 Kbytes • Data flash memory Capacity: 32 Kbytes • RAM/extended RAM Capacity: 512 Kbytes / 512 Kbytes
Integrated development environment	e ² studio (V7.5.0 or later) with the CC-RX compiler (V3.01.00)
Emulator (ICE)	Renesas E2 Lite

2. About sample program package

This sample program package gathers the software of industrial network protocol stack for RX72M and the software of common API library for protocol stacks together as a one package. Sample programs for multiple protocol stacks are packaged in this.

2.1 Overall structure

Figure 2.1 shows the overall structure of the industrial network protocol stack software for RX72M.




Figure 2.1 overall structure of protocol stack software for RX72M

This software supports the major protocol stacks for Industrial Ethernet and Field Bus. In Industrial Ethernet, EtherCAT, OPC UA, Modbus TCP, EtherNet/IP and PROFINET RT. In Field Bus, CANopen, Modbus RTU/ASCII, DeviceNet and PROFIBUS DP. For detailed information of each sample program, refer to the corresponding sample program package.

You can develop the user application layer immediately by using these sample programs which contained in this package.

Note: 1. The common API library is software that defines the interface that enhances the applicability of user applications for variable industrial network protocols. For detailed information, refer to “RX72M Group Industrial Network Common API Library Package”.

2.2 Package folder structure

The folder structure of this sample program package is below.

```
an-r01an4882xx0110-rx72m-sample-package
| r01an4882ej0110-rx72m-sample-package.pdf // This file (English version)
| r01an4882jj0110-rx72m-sample-package.pdf // This file (Japanese version)
|
|—Communications_Board // Communications Board folder
|   r01an4661ej0100-rx72m-comboard.pdf // Communications Board Hardware Manual (English version)
|   r01an4661jj0100-rx72m-comboard.pdf // Communications Board Hardware Manual (Japanese version)
|
|—Common_API_library // Common API library folder
|   an-r01an4852xx0100-rx72m-commonapi.zip // Common API library package
|
|—Protcol_stack_samples // Industrial network protocol stack folder
|   an-r01an4741xx0100-rx72m-canopen-master.zip
|       // CANopen Master sample program package
|   an-r01an4740xx0100-rx72m-canopen.zip
|       // CANopen Slave sample program package
|   an-r01an4738xx0100-rx72m-devicenet.zip
|       // DeviceNet Slave sample program package
|   an-r01an4881xx0121-rx-ecat.zip
|       // EtherCAT Slave sample program package
|   an-r01an4884xx0105-rx72m-ethernetip.zip
|       // EtherNet/IP Slave sample program package
|   an-r01an4862xx0103-rx72m-modbus.zip
|       // Modbus TCP Gateway/Server, RTU/ASCII Master/Slave sample program package
|   an-r01an4778xx0100-rx72m-opcua.zip
|       // OPC UA(Micro/Nano) Server sample program package
|   an-r01an4853xx0100-rx72m-profibus-master.zip
|       // PROFIBUS DP Master sample program package
|   an-r01an4739xx0100-rx72m-profibus.zip
|       // PROFIBUS DP Slave sample program package
|   an-r01an4885xx0104-rx72m-profinet.zip
|       // PROFINET RT(CC-A) Slave sample program package
|   an-r01an6977xx0100-rx72m-ccietsna.zip
|       // CC-Link IE TSN ClassA sample program package
```

3. Usage

For usage of each sample program, refer to the document which contained in the corresponding sample program package.

Website and Support

Renesas Electronics Website

<http://www.renesas.com/>

Inquiries

<http://www.renesas.com/contact/>

All other logos and trademarks are the property of the respective trademark owners.

Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Sep. 11, 2019	-	First edition issued
1.01	Nov. 1, 2019	-	Add EtherCAT Startup Manual
		-	Modbus documentation improvements
		-	Add an assessment tool
1.02	Dec. 5, 2019	-	Add EtherCAT RSK Board Sample Program
		-	EtherNetIP documentation improvements
		-	PROFINET documentation improvements
1.03	Jan. 31, 2020	-	Add CC-Link IE TSN ClassA Sample Package
		-	Modify the DeviceNet Slave document
		-	Modify the CANopen Master document
		-	Modify the CANopen Slave document
1.04	May. 5, 2020	-	Modify the PROFIBUS Master document
		-	Support EWRX (refer to r01an4881xx0110 for details)
		-	Modify Modbus Sample Program (refer to r01an4862xx0102 for details)
		-	Modify PROFINET Sample Program (refer to r01an4885xx0102 for details)
		-	Modify EtherNetIP Sample Program (refer to r01an4884xx0102 for details)
1.05	Aug. 31, 2020	-	Modify EtherCAT Sample Program (refer to r01an4881xx0111 for details)
		-	Modify PROFINET Sample Program (refer to r01an4885xx0103 for details)
		-	Modify EtherNetIP Sample Program (refer to r01an4884xx0103 for details)
1.06	Nov. 20, 2020	-	Modify Modbus Sample Program (refer to r01an4862xx0103 for details)
1.07	Aug. 31, 2021	-	Modify EtherCAT Sample Program (refer to r01an4881xx0120 for details)
		-	Modify PROFINET Sample Program (refer to r01an4885xx0104 for details)
		-	Modify EtherNetIP Sample Program (refer to r01an4884xx0104 for details)
1.08	Jan. 31, 2022	-	Modify EtherCAT Sample Program (refer to r01an4881xx0121 for details)
		-	Modify EtherNetIP Sample Program (refer to r01an4884xx0105 for details)
1.09	Jan. 31, 2023	-	Modify EtherCAT Sample Program (refer to r01an4881xx0130 for details)
		-	Modify EtherNetIP Sample Program (refer to r01an4884xx0106 for details)
1.10	Aug. 31, 2023	-	Add CC-Link IE TSN ClassA Sample Package

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity. Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power reaches the level at which resetting is specified.

3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

5. Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

6. Voltage application waveform at input pin

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (Max.) and V_{IH} (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (Max.) and V_{IH} (Min.).

7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

- Ethernet is a registered trademark of Fuji Xerox Co., Ltd.
- EtherCAT® and TwinCAT® are registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany.
- PROFIBUS and PROFINET are registered trademarks of PROFIBUS and PROFINET International (PI).
- EtherNet/IP™ and DeviceNet™ are registered trademarks of ODVA, Inc..
- OPC and OPC UA are registered trademark and patented technology, licensed by OPC Foundation.
- Modbus is registered trademarks of Modbus-IDA.
- CANopen® and CiA® are registered trademarks of CAN in Automation.
- CC-Link IE Field and CC-Link IE TSN are registered trademarks of Mitsubishi Electric Corporation.
- Additionally, all product names and service names in this document are the trademarks or registered trademarks which belong to the respective owners.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
- Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
 11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/