


# MEMORY INTERFACE PRODUCTS

THE ONLY COMPLETE PROVIDER OF ALL MEMORY INTERFACE PRODUCTS FOR DDR5 SERVERS AND CLIENT DIMMS




#### **CONTENTS**

DDR5 Solutions	04
DDR4 Solutions	06
DDR3 Solutions	07
13°C Intelligent Switches and Evnanders	nΩ







#### **Memory Interface Products**

As the industry leader for over 20 years and the only full system solution supplier of memory interface products for DDR5 modules, Renesas offers a wide array of JEDEC-compliant registered clock drivers (RCD), client clock driver (CKD), data buffers (DB), power management ICs (PMIC), temperature sensors, and SPD hubs to meet the tight timing budget requirement of dual in-line memory modules (DIMM).

With a focus on low power, high performance and thorough validation through each new generation of memory technology, Renesas has established its position as the unquestioned market leader in memory interface solutions.

#### **DDR5 Solutions**

For DDR5 RDIMM, MRDIMM, UDIMM, SODIMM, CUDIMM, CSODIMM, CAMM, LPCAMM, gaming DIMM, and memory down applications.

#### **DDR4 Solutions**

For DDR4 RDIMM, UDIMM, SODIMM, and memory down applications.

#### **DDR3 Solutions**

For DDR3 RDIMM, ECC UDIMM, and memory down applications.

#### I<sup>3</sup>C Intelligent Switches and Expanders

For memory and control plane expanders to improve signal integrity and performance on server motherboards.


## **DDR5 Solutions**





**DDR5 CAMM** 

**LPCAMM** 

## **DDR5 Server DIMM** Sub-Channel A SPD Hub 읊 **Client DIMM**







DDR5 memory is projected to double the bandwidth of DDR4, and as with previous generations of DDR memory, Renesas' devices are leading the market in performance and reliability. Renesas has a complete family of ICs to develop high-performance DDR5 RDIMM, MRDIMM, UDIMM, SODIMM, CUDIMM, CSODIMM, CAMM, LPCAMM, gaming DIMM, and memory interface products for server and client memory down applications. Renesas' portfolio includes power management ICs (PMICs), SPD hubs, registered clock drivers, temperature sensors, data buffers, 13C Intelligence Switches, and 13C re-driver and expander products. Renesas' family of DDR5 and 13C expander ICs enables the next generation of server and client DIMM as well as server and client motherboard solutions to efficiently scale to greater performance, density, and reliability while reducing overall system power.

Renesas also offers an industrial temp DDR5 RCD that supports temperatures as low as -40°C and as high as 105°C for DDR5 industrial temperature dual inline memory modules (DIMMs) and memory-down applications.

With a deep history of delivering industry-leading memory interface chipsets for all DDR generations, Renesas' devices will provide reliable performance to meet the most demanding enterprise and data center applications.


## **DDR5 Solutions**

Part No.	Product Title	Function	Input Voltage Range (V)
5DB0148	Data Buffer for DDR5 Memory Modules	DDR5 Data Buffer	1.1
5RCD0148	DDR5 Register Command Address up to 4800MT/s	DDR5 Gen 1 Server RCD	1.04 - 1.16
P8900	PMIC for DDR5 RDIMM	DDR5 Server PMIC	12, 3.3
P8910	PMIC for DDR5 RDIMM	DDR5 Server PMIC	12, 3.3
RRG5321	JEDEC P5020 compliant PMIC for RDIMM and MRDIMM	DDR5 Gen 1 MRDIMM PMIC	12, 3.3
RRG5322	JEDEC P5030 compliant PMIC for RDIMM and MRDIMM	DDR5 Gen 2 MRDIMM PMIC	15, 3.6
P8911	PMIC for DDR5 UDIMM and SODIMM	DDR5 Client PMIC	5
RRG5332	JEDEC P5120 compliant PMIC for UDIMM and SODIMM	DDR5 Gen 2 Client PMIC	5
RRG5341	JEDEC P5200 compliant PMIC for LPCAMM	DDR5 LLPMIC	5
RG5C172	DDR5 Gen 1 Client Clock Driver for UDIMM, SODIMMs, Over Clocking DIMMs and Memory Down. Address up to 7200MT/s	DDR5 Gen 1 Client Clock Driver	1.07 – 1.17
RRG52021	DDR5 Gen 2 Client Clock Driver for UDIMM, SODIMMs, Over Clocking DIMMs and Memory Down. Address up to 8800MT/s	DDR5 Gen 2 Client Clock Driver	1.1
RG5D188	Gen 1 MDB for DDR5 MRDIMM. Address up to 8800MT/s	DDR5 Gen 1 MDB	1.07 – 1.17
RRG51021	Gen 2 MDB for DDR5 MRDIMM. Address up to 12800MT/s	DDR5 Gen 2 MDB	1.07 – 1.17
RG5R188	Gen 1 MRCD for DDR5 MRDIMM. Address up to 8800MT/s	DDR5 Gen 1 MRCD	1.1
RRG50121	Gen 2 MRCD for DDR5 MRDIMM. Address up to 12800MT/s	DDR5 Gen 2 MRCD	1.1
RG5R256	DDR5 Register Command Address up to 5600MT/s	DDR5 Gen 2 Server RCD	1.06 – 1.16
RG5R364	DDR5 Register Command Address up to 6400MT/s	DDR5 Gen 3 Server RCD	1.06 - 1.16
RRG50041	DDR5 Register Command Address up to 7200MT/s	DDR5 Gen 4 Server RCD	1.1
RRG50051	DDR5 Register Command Address up to 8800MT/s	DDR5 Gen 5 Server RCD	1.1
SPD5118	SPD HUB for DDR5 Memory Modules	SPD Hub for DDR5 Memory Modules	1.8, 1.0
TS5111	Temperature Sensor for DDR5 Memory Modules	Temperature Sensor	1.8, 1.0


## **DDR4 Solutions**



#### **DDR4 RDIMM**



#### **DDR4 LRDIMM**



Renesas' DDR4 registered clock driver, data buffer and temp sensor make up the industry's first complete chipset for DDR4 registered dual inline memory modules (RDIMMs) and load reduced dual inline memory modules (LRDIMMs). With DDR4 data rates climbing to 3.2Gb/s and higher, the clear advantages afforded by RDIMM and LRDIMM as a speed-scalable memory technology are expected to drive adoption across a broad array of memory-intensive computing and storage applications.

Renesas also offers an industrial temp DDR4 RCD that supports temperatures as low as -40 °C and as high as 105 °C for existing DDR4 applications.

Through flexible I/O control, timing and voltage calibration, and control register programmability, the Renesas DDR4 registered clock drivers and data buffers enable faster data rates at higher densities on all JEDEC® defined DDR4 LRDIMM and RDIMM topologies. DIMM topology configuration and DRAM information are stored in Renesas' temperature sensor EEPROM.

With a deep knowledge of memory interface chipsets based on successful chipset introductions for all DDR generations, Renesas' devices will provide reliable performance for your application.

Part No.	Product Title	Function	Input Voltage Range (V)
4DB0232KD	Data Buffer for DDR4 Memory Modules	DDR4 Data Buffer	1.2, 1.14 – 1.26
4RCD0124K	DDR4 Register Command Address up to 2400MT/s	DDR4 Gen 1 Server RCD	1.2
4RCD0229K	DDR4 Register Command Address up to 2667MT/s	DDR4 Gen 2 Server RCD	1.2
4RCD0232K	DDR4 Register Command Address up to 3200MT/s	DDR4 Gen 2.5 Server RCD	1.2
TSE2004GB2	DDR4 Temp Sensor with SPD	DDR4 Temp Sensor	2.2 – 3.6

## **DDR3 Solutions**



DDR3 memory offers significant advantages in power, bandwidth, capacity, and reliability versus previous generations of memory technology. Renesas offers both Register/PLL and temperature sensor products for the DDR3 memory module market.

Fully compliant with all JEDEC specifications, the Renesas DDR3 Register/PLL is an essential building block for advanced memory subsystems in applications such as servers, workstations and communications equipment.

DDR3 RDIMMs and ECC UDIMMs all require the use of a temperature sensor with an integrated SPD. Renesas offers digital temperature sensors with accuracy up to  $\pm 0.5^{\circ}$ C typical, that is designed for memory modules demanding the highest level of temperature readout.

Part No.	Product Title	Function	Input Voltage Range (V)
SSTE32882KB1	LOW POWER DDR3 Register + PLL	DDR3 Register	1.25, 1.35, 1.5

## I<sup>3</sup>C Intelligent Switches and Expanders



Renesas has a family of control plane (I³C) switches and expanders to significantly improve signal integrity and performance in a wide variety of applications, including CPU/BMC/DIMM management for servers and data centers.

Renesas control plane (I<sup>3</sup>C) switches and expanders enable intelligent management of CPU, BMC, DIMM, and other peripherals with significant performance and power benefits over other serial communication interfaces with easy-to-use bidirectional signaling capabilities in a small footprint.

Part No.	Product Title	Function	Supply Voltage (V)	Temp. Range	Package Type	Lead Count
RG3M47B12	2:4 Hub, Downstream Ports default disabled	I <sup>3</sup> C 2:4 Intelligence Switch	3.3	-40 to 85°C	VFQFPN	28
RG3M48B12	2:4 Hub, Downstream Ports default enabled	I <sup>3</sup> C 2:4 Intelligence Switch	3.3	-40 to 85°C	VFQFPN	28
RG3M49B12	2:4 Hub, Downstream Ports default disabled and VIO LDOs Enabled	I <sup>3</sup> C 2:4 Intelligence Switch	3.3	-40 to 85°C	VFQFPN	28
RG3M87B12	2:8 Hub, Downstream Ports default disabled	I <sup>3</sup> C 2:8 Intelligence Switch	3.3	-40 to 85°C	VFQFPN	28
RG3M88B12	2:8 Hub, Downstream Ports default enabled	I <sup>3</sup> C 2:8 Intelligence Switch	3.3	-40 to 85°C	VFQFPN	28
RG3M89B12	2:8 Hub, Downstream Ports default disabled and VIO LDOs Enabled	I <sup>3</sup> C 2:8 Intelligence Switch	3.3	-40 to 85°C	VFQFPN	28
IMX3112	I <sup>3</sup> C 1:2 Bus Multiplexer	I <sup>3</sup> C 1:2 Bus Multiplexer	1.8	0 to 125°C	DFN	8
IMX3102	I <sup>3</sup> C 2:1 Bus Multiplexer	I <sup>3</sup> C 2:1 Bus Multiplexer	1.8	-40 to 85°C	DFN	8
IML3112	I <sup>3</sup> C 1:2 Multiplexer with Level Shift	I <sup>3</sup> C 1:2 Multiplexer with Level Shift	1.8	0 to 125°C	DFN	8

MEMO	



#### Renesas Electronics Corporation TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan

#### Notice

- Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the
- design of your product or system. Renease Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.

  Renease Electronics hereby expressly disclaims any warranties against and liability for any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renease Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.

- No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.

  You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.

  You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copyring or reverse
- requirements.

  Reneasas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. "Standard": Computers; office equipment; communications equipment, test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc. "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

  - Unless expressly designated as a high preliability product or a product for harsh environments in a Reneasa Electronics advantage leaves the environment of the Reneasa Electronics are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Reneasa Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
- No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including The property of the property o ACCOMPANYING SOFTWARE OR HARDWARE. INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY. OR FITNESS FOR A PARTICULAR PURPOSE.
- When using Reneasa Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
- Authough Reneasa Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate
- retartment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impactical, you are responsible for evaluating the safety of the final protections or systems. Because the evaluation of microcomputer software alone is very difficult and impactical, you are responsible for evaluating the safety of the final protection or systems manufactured by you.

  Please contact a Renessa Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renessa Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renessa Electronics products in compliance with all these applicable laws and regulations. Renessa Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- Reneasa Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.

  It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
- This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics
- Please contact a Renessas Electronics sales office if you have any questions regarding the information contained in this document or Renessas Electronics products to 1) "Renessas Electronics" as used in this document means Renessas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 2020.10)

■Contact Us https://www.renesas.com/contact-us



#### Renesas Electronics Corporation

www.renesas.com