



Ref. Certif. No.

US-23950-A1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE CERTIFICATS D'ESSAIS DES EQUIPEMENTS ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product
Produit

Component IC Current Limiter

Name and address of the applicant
Nom et adresse du demandeur

SILEGO TECHNOLOGY INC.
1515 WYATT DRIVE
SANTA CLARA, CA. 95054
USA

Name and address of the manufacturer
Nom et adresse du fabricant

SILEGO TECHNOLOGY INC.
1515 WYATT DRIVE
SANTA CLARA, CA. 95054
USA

Name and address of the factory
Nom et adresse de l'usine

GREATEK ELECTRONICS INC.
136 GUNG YI ROAD CHUNAN CHENG, MIAOLI HSIEN
TAIWAN

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{eme} page

Additional Information on page 2

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

See Page 2

Trademark (if any)
Marque de fabrique (si elle existe)



Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

Model / Type Ref.
Ref. De type

SLG55544, SLG55546, SLGC55544, SLGC55546
See Page 2

Additional information (if necessary may also be reported on page 2)
Les informations complémentaires (si nécessaire,, peuvent être indiqués sur la 2^{eme} page

Additional Information on page 2

A sample of the product was tested and found to be in conformity with
Un échantillon de ce produit a été essayé et a été considéré conforme à la

IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1

As shown in the Test Report Ref. No. which forms part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de référence qui constitue partie de ce Certificat

E468659-A1-CB-1 issued on 2015-02-26

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2015-02-26
Original Issue Date: 2014-09-23

Signature:

Jolanta M. Wroblewska

Ratings:

Input Voltage:

4.5 Vdc to 5.5 Vdc

Output Continuous Rating:

0.2 A to 2.5 A

Output Current Limit:

0.3 A to 3.17 A

Ambient:

-40 to 85°C

Model Details:

SLG55544, SLG55546, SLGC55544, SLGC55546, maybe followed by V or VTR

Factories:

ASE GROUP CHUNG-LI (ASE-CL)

550 CHUNG-HWA ROAD, SECTION 1 CHUNG-LI 320

TAIWAN

Additional Information:

The original report was modified to include the following:

Addition of models, see test report.

Additionally evaluated to EN 60950-1:2006 /A11:2009 /A1:2010 /A12:2011; National Differences specified in the CB Test Report.

Additional information (if necessary)**Information complémentaire (si nécessaire)**

UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA



UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK



UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN



UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-02-26

Original Issue Date: 2014-09-23

Signature:



Jolanta M. Wroblewska