

IS-1009RH, IS-1009EH

Radiation Hardened 2.5V Reference

FN4780

Rev 8.0

May 18, 2021

The Radiation Hardened [IS-1009RH](#), [IS-1009EH](#) are a 2.5V shunt regulator diode is designed to provide a stable 2.5V reference over a wide current range.

These devices are designed to maintain stability over the full military temperature range and over time. The 0.2% reference tolerance is achieved by on-chip trimming.

An adjustment terminal is provided to allow for the calibration of system errors. The use of this terminal to adjust the reference voltage does not effect the temperature coefficient.

Constructed with the dielectrically isolated EBHF process, these devices are immune to single event latch-up and have been specifically designed to provide highly reliable performance in harsh radiation environments.

The IS-1009EH replaces the obsoleted IS-1009RH.

Features


- Electrically screened to SMD #[5962-00523](#)
- QML qualified per MIL-PRF-38535 requirements
- EH version acceptance tested to 50krad(Si) (LDR)
- Radiation environment - IS-1009EH
 - High dose rate (50-300rad(Si)/s) 300 krad(Si)
 - Low dose rate (0.01rad(Si)/s) 50krad(Si)
- Radiation environment - IS-1009RH
 - High dose rate (50-300rad(Si)/s) 300 krad(Si)
- Latch-up immune dielectrically isolated
- Reverse breakdown voltage (V_Z) 2.5V
- Change in V_Z vs current (400 μ A to 10mA) 6mV
- Change in V_Z vs temperature (-55°C to +125°C)15mV
- Maximum reverse breakdown current 20mA
- Device is tested with 10 μ F shunt capacitance connected from V+ to V-, which provides optimum stability
- Interchangeable with 1009 and 136 industry types

Applications


- Power supply monitoring
- Reference for 5V systems
- A/D and D/A reference

Pin Configurations

IS2-1009RH, IS2-1009EH
(TO-206AB CAN)
BOTTOM VIEW



ISYE-1009RH, ISYE-1009EH
(SMD.5)
BOTTOM VIEW



Ordering Information

ORDERING SMD NUMBER (Note 2)	INTERNAL MKT. NUMBER (Note 1)	RADIATION HARDNESS (Total Ionizing Dose)	PACKAGE DESCRIPTION (RoHS Compliant)	PKG. DWG.#	CARRIER TYPE	TEMP. RANGE
5962F0052302VXC	IS2-1009EH-Q	HDR to 300krad(Si), LDR to 50krad(Si)	3 Lead Metal Can package TO-206AB (TO-46)	T3.B	Tray	-55 to +125 °C
5962F0052302VYC	ISYE-1009EH-Q		3 Pad Hermetic CLCC	J3.A	Tube	
5962F0052302V9A	ISO-1009EH-Q (Note 3)		Die	-	-	
N/A	IS2-1009EH/PROTO (Note 4)	N/A	3 Lead Metal Can package TO-206AB (TO-46)	T3.B	Tray	
	ISYE-1009EH/PROTO (Note 4)		3 Pad Hermetic CLCC	J3.A	Tube	
	ISO-1009EH/SAMPLE (Notes 3, 4)		Die	-	-	
5962F0052301VXC	IS2-1009RH-Q No longer available or supported	HDR to 300krad(Si)	3 Lead Metal Can package TO-206AB (TO-46)	T3.B	Tray	
5962F0052301QXC	IS2-1009RH-8 No longer available or supported					
5962F0052301VYC	ISYE-1009RH-Q No longer available or supported		3 Pad Hermetic CLCC	J3.A	Tube	
5962F0052301QYC	ISYE-1009RH-8 No longer available or supported					
5962F0052301V9A	ISO-1009RH-Q (Note 3) No longer available or supported		Die	-	-	
N/A	IS2-1009RH/PROTO (Note 4) No longer available or supported	N/A	3 Lead Metal Can package TO-206AB (TO-46)	T3.B	Tray	
	ISYE-1009RH/PROTO (Note 4) No longer available or supported		3 Pad Hermetic CLCC	J3.A	Tube	
ISO-1009RH/SAMPLE	ISO-1009RH/SAMPLE (Notes 3, 4) No longer available or supported		Die	-	-	

NOTES:

- These Pb-free Hermetic packaged products employ 100% Au plate - e4 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations.
- Specifications for Rad Hard QML devices are controlled by the Defense Logistics Agency Land and Maritime (DLA). The SMD numbers listed must be used when ordering.
- Die product tested at $T_A = +25^\circ\text{C}$. The wafer probe test includes functional and parametric testing sufficient to make the die capable of meeting the electrical performance outlined in the SMD.
- The /PROTO and /SAMPLE are not rated or certified for Total Ionizing Dose (TID) or Single Event Effect (SEE) immunity. These parts are intended for engineering evaluation purposes only. The /PROTO parts meet the electrical limits and conditions across temperature specified in the DLA SMD and are in the same form and fit as the qualified device. The /SAMPLE parts are capable of meeting the electrical limits and conditions specified in the DLA SMD. The /SAMPLE parts do not receive 100% screening across temperature to the DLA SMD electrical limits. These part types do not come with a Certificate of Conformance because they are not DLA qualified devices.

Die Characteristics

DIE DIMENSIONS

1270 μ m x 1778 μ m (50 mils x 70 mils)
Thickness: 356 μ m \pm 25.4 μ m (14 mils \pm 1 mil)

INTERFACE MATERIALS

Glassivation

Type: Silox (SiO₂) 1:6:1
Thickness: 8k Å \pm 0.8k Å (1k Å undoped, 6k Å doped, cap 1k Å undoped)

Top Metallization

Type: Al Si Cu
Thickness: 16.0k Å \pm 2k Å

Substrate

EFSTDB: Single-poly dielectrically isolated complementary bipolar

Backside Finish

Silicon

ASSEMBLY RELATED INFORMATION

Substrate Potential

Unbiased (DI)

ADDITIONAL INFORMATION

Worst Case Current Density


$<1.0 \times 10^5$ A/cm²

Transistor Count

26

Metallization Mask Layout

IS-1009RH, IS-1009EH



Revision History

The revision history provided is for informational purposes only and is believed to be accurate, but not warranted. Please go to the web to make sure that you have the latest revision.

DATE	REVISION	CHANGE
May 18, 2021	8.0	Updated Radiation Acceptance testing features bullets. Updated the Ordering Information table. Updated Die Characteristics for Glassivation and Substrate to match information in the SMD. Removed About Intersil section.
Nov 19, 2015	7.0	Added Rev History and About Intersil verbiage. Added to page 1 introduction "The IS-1009EH replaces the obsoleted IS-1009RH." Updated Ordering Information on page 2 as follows: Marked RH obsolete parts "No longer available or supported" Added EH Proto and Sample parts.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Rev.1.0 Mar 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.