

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

### NPN SILICON TRIPLE DIFFUSED TRANSISTORS

### COLOR TV CHROMA AND SOUND OUTPUT AMPLIFIERS

#### DESCRIPTION

The 2SC1505, 2SC1506 and 2SC1507 are high voltage triple diffused silicon transistors. These transistors are designed for use in line-operated color TV chroma output circuits and sound output circuits.

Three types of different lead configuration are prepared for designer's convenience.

#### FEATURES

- Suitable for chroma output circuits and sound output circuits ( $P_o=1.5W$ ) in line-operated color TV receivers.
- High voltage, high  $f_T$  and low  $C_{ob}$ .
- Three types of different lead configuration available.
  - 2SC1505 . . . . . Standard type
  - 2SC1506 . . . . . T0-66 replacement
  - 2SC1507 . . . . . Upright mounting

#### ABSOLUTE MAXIMUM RATINGS ( $T_a=25^\circ C$ )


Collector to Base Voltage	$V_{CBO}$	300	V
Collector to Emitter Voltage	$V_{CEO}$	300	V
Emitter to Base Voltage	$V_{EB0}$	7.0	V
Collector Current	$I_C$	200	mA
Total Power Dissipation	$P_T(T_C=25^\circ C)$	15	W
Total Power Dissipation	$P_T(T_a=25^\circ C)$	1.2	W
Junction Temperature	$T_j$	150	$^\circ C$
Storage Temperature	$T_{stg}$	-55 to +150	$^\circ C$

#### ELECTRICAL CHARACTERISTICS ( $T_a=25^\circ C$ )


CHARACTERISTIC	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITIONS
Collector Cutoff Current	$I_{CBO}$			100	nA	$V_{CB}=200V, I_E=0$
Emitter Cutoff Current	$I_{EB0}$			100	nA	$V_{EB}=5.0V, I_C=0$
DC Current Gain	$h_{FE}$	40	80	200		$V_{CE}=10V, I_C=10mA$ *
Collector Saturation Voltage	$V_{CE(sat)}$			2.0	V	$I_C=50mA, I_B=5.0mA$ *
Gain Bandwidth Product	$f_T$	50	80		MHz	$V_{CE}=30V, I_E=-10mA$
Collector to Base Capacitance	$C_{ob}$			4.5	pF	$V_{CB}=50V, I_E=0, f=1.0MHz$

\* Pulse test  $PW \leq 350\mu s$ , duty cycle  $\leq 2.0\%$   
 $h_{FE}$  classification /M: 40-80 L: 60-120 K: 100-200

PACKAGE DIMENSIONS (Unit:mm)



MOUNTING HOLE LAYOUT DIMENSIONS



LEAD CONNECTION

- 1. Base EIAJ :SC-46
- 2. Collector(Fin) JEDEC:TO-220AB
- 3. Emitter IEC :-
- 4. Fin

As the clearance between collector and Base, Emitter is narrow, care should be taken at high voltage use.


- 1. Base EIAJ :SC-45
- 2. - JEDEC:TO-220AA
- 3. Emitter IEC :-
- 4. Collector(Fin)

As the collector lead is cut, solder lug is used instead of it.



- 1. Base EIAJ :-
- 2. Collector(Fin) JEDEC:-
- 3. Emitter IEC :-
- 4. Fin

Convenient in case of free-air use.



SUGGESTED MOUNTING METHODS




POWER-TEMPERATURE DERATING CURVES




TYPICAL CHARACTERISTICS ( $T_a=25^\circ\text{C}$ )




COLLECTOR CURRENT vs.  
COLLECTOR TO EMITTER VOLTAGE




DC CURRENT GAIN vs.  
COLLECTOR CURRENT




BASE AND COLLECTOR SATURATION VOLTAGE vs. COLLECTOR CURRENT



OUTPUT CAPACITANCE vs. COLLECTOR TO BASE VOLTAGE



GAIN BANDWIDTH PRODUCT vs.  
EMITTER CURRENT



**Nippon Electric Co., Ltd.**

NEC Building, 33-1, Shiba Gochome, Minato-ku, Tokyo 108, Japan  
Tel.: Tokyo 454-1111  
Telex Address: NECTOK A J22686  
Cable Address: MICROPHONE TOKYO

TC-1010B  
APR-20-79K  
Printed in Japan