

HS-4424RH, HS-4424EH, HS-4424BRH, HS-4424BEH

Radiation Hardened Dual, Non-Inverting Power MOSFET Drivers

The radiation hardened [HS-4424RH](#), [HS-4424EH](#), [HS-4424BRH](#) and [HS-4424BEH](#) are non-inverting, dual, monolithic high-speed MOSFET drivers designed to convert TTL level signals into high current outputs at voltages up to 18V.

The inputs of these devices are TTL compatible and can be directly driven by our HS-1825ARH PWM device or by our ACS/ACTS and HCS/HCTS type logic devices. The fast rise times and high current outputs allow very quick control of high gate capacitance power MOSFETs in high frequency applications.

The high current outputs minimize power losses in MOSFETs by rapidly charging and discharging the gate capacitance. The output stage incorporates a low voltage lockout circuit that puts the outputs into a three-state mode when the supply voltage drops below 10V for the HS-4424RH, HS-4424EH and 7.5V for the HS-4424BRH, HS-4424BEH.

Constructed with the dielectrically isolated Rad Hard Silicon Gate (RSG) BiCMOS process, these devices are immune to single event latch-up and have been specifically designed to provide highly reliable performance in harsh radiation environments.

Detailed Electrical Specifications for these devices are contained in SMD [5962-99560](#).

Related Literature

For a full list of related documents, visit our website:

- [HS-4424RH](#), [HS-4424EH](#), [HS-4424BRH](#) and [HS-4424BEH](#) device pages

Features

- Electrically screened to DESC SMD # [5962-99560](#)
- QML qualified per MIL-PRF-38535 requirements
- Radiation environment
 - High dose rate (50-300rad(Si)/s): 300krad(Si)
 - Latch-up immune
 - Low dose rate (0.01rad(Si)/s): 50krad(Si) (EH products only)
- I_{PEAK}: >2A (min)
- Matched rise and fall times (C_L = 4300pF): 75ns (maximum)
- Low voltage lockout feature
 - HS-4424RH, HS-4424EH: <10.0V
 - HS-4424BRH, HS-4424BEH: <7.5V
- Wide supply voltage range: 12V to 18V
- Prop delay: 250ns (maximum)
- Consistent delay times with V_{CC} changes
- Low power consumption
 - 40mW with inputs high
 - 20mW with inputs low
- Low equivalent input capacitance: 3.2pF (typical)
- ESD protected: >4000V

Applications

- Switching power supplies
- DC/DC converters
- Motor controllers

Table 1. Table of Differences

Part Number	Dose Rate (rad(Si)/s)
HS-4424RH, HS-4424BRH	50-300
HS-4424EH, HS-4424BEH	0.01

1. Overview

1.1 Ordering Information


Ordering SMD Number (Note 2)	Part Number (Notes 1, 3)	Temperature Range (°C)	Package (RoHS Compliant)	Pkg. Dwg. #
5962F9956004V9A	HS0-4424BEH-Q	-55 to +125	DIE	
5962F9956002V9A	HS0-4424BRH-Q	-55 to +125	DIE	
N/A	HS0-4424BRH/SAMPLE	-55 to +125	DIE SAMPLE	
5962F9956003V9A	HS0-4424EH-Q	-55 to +125	DIE	
5962F9956001V9A	HS0-4424RH-Q	-55 to +125	DIE	
N/A	HS0-4424RH/SAMPLE	-55 to +125	DIE SAMPLE	
5962F9956001VXC	HS9-4424RH-Q	-55 to +125	16 Ld Flatpack	K16.A
5962F9956004VXC	HS9-4424BEH-Q	-55 to +125	16 Ld Flatpack	K16.A
5962F9956003VXC	HS9-4424EH-Q	-55 to +125	16 Ld Flatpack	K16.A
5962F9956002QXC	HS9-4424BRH-8	-55 to +125	16 Ld Flatpack	K16.A
5962F9956002VXC	HS9-4424BRH-Q	-55 to +125	16 Ld Flatpack	K16.A
N/A	HS9-4424BRH/PROTO	-55 to +125	16 Ld Flatpack	K16.A
N/A	HS9-4424RH/PROTO	-55 to +125	16 Ld Flatpack	K16.A
5962F9956001QXC	HS9-4424RH-8	-55 to +125	16 Ld Flatpack	K16.A

Notes:

1. These Pb-free Hermetic packaged products employ 100% Au plate - e4 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations.
2. Specifications for Rad Hard QML devices are controlled by the Defense Logistics Agency Land and Maritime (DLA). The SMD numbers must be used when ordering.
3. The /PROTO and /SAMPLE are not rated or certified for Total Ionizing Dose (TID) or Single Event Effect (SEE) immunity. These parts are intended for engineering evaluation purposes only. The /PROTO parts meet the electrical limits and conditions across temperature specified in the DLA SMD and are in the same form and fit as the qualified device. The /SAMPLE parts are capable of meeting the electrical limits and conditions specified in the DLA SMD at +25°C only. The /SAMPLE parts do not receive 100% screening across temperature to the DLA SMD electrical limits. These part types do not come with a Certificate of Conformance because they are not DLA qualified devices.

1.2 Pin Configuration

Flatpack CDFP4-F16
Top View




2. Die Characteristics

Table 2. Die and Assembly Related Information

Die Information	
Dimensions	4890µm x 3370µm (193 mils x 133 mils) Thickness: 483µm ±25.4µm (19 mils ±1 mil)
Interface Materials	
Glassivation	Type: PSG (Phosphorous Silicon Glass) Thickness: 8.0kÅ ±1.0kÅ
Top Metallization	Type: AlSiCu Thickness: 16.0kÅ ±2kÅ
Substrate	Radiation Hardened Silicon Gate, Dielectric Isolation
Backside Finish	Silicon
Assembly Information	
Substrate Potential	Unbiased (DI)
Additional Information	
Worst Case Current Density	<2.0 x 10 ⁵ A/cm ²
Transistor Count	125

2.1 Metallization Mask Layout






3. Revision History

Rev.	Date	Description
3.00	Jun.11.19	Applied new formatting. Added Related Literature. Added Table 1. Removed 3rd bullet Updated third sub-bullet under radiation environment feature bullet. Removed Note from pin configuration. Added Note 3. Added package outline drawing. Added Revision History Updated disclaimer.

4. Package Outline Drawing

For the most recent package outline drawing, see [K16.A](#).

K16.A
 16 LEAD CERAMIC METAL SEAL FLATPACK PACKAGE
 Rev 2, 1/10



NOTES:

- 1. Index area: A notch or a pin one identification mark shall be located adjacent to pin one and shall be located within the shaded area shown. The manufacturer's identification shall not be used as a pin one identification mark. Alternately, a tab may be used to identify pin one.
- 2. If a pin one identification mark is used in addition to a tab, the limits of the tab dimension do not apply.
- 3. The maximum limits of lead dimensions (section A-A) shall be measured at the centroid of the finished lead surfaces, when solder dip or tin plate lead finish is applied.
- 4. Measure dimension at all four corners.
- 5. For bottom-brazed lead packages, no organic or polymeric materials shall be molded to the bottom of the package to cover the leads.
- 6. Dimension shall be measured at the point of exit (beyond the meniscus) of the lead from the body. Dimension minimum shall be reduced by 0.0015 inch (0.038mm) maximum when solder dip lead finish is applied.
- 7. Dimensioning and tolerancing per ANSI Y14.5M - 1982.
- 8. Controlling dimension: INCH.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.