




32-bit MCU with Arm® Cortex®-M Core

RENESAS RA FAMILY

Delivering the Ultimate Promise of IoT with Software Flexibility

The Renesas RA family of 32-bit MCUs are built on the Arm® Cortex®-M core architecture. Offering a wide range of performance and features, the Renesas RA family meets the scalability, power consumption and performance needs of nearly any embedded systems end-product.



Strong Security

- Leading-edge, integrated Renesas Security IP
- An extra layer of embedded hardware security providing tamper detection and resistance to side-channel attacks
- Integrated Arm v8-M TrustZone®



Arm Core

- Arm Cortex-M23 core for the most cost/power sensitive applications
- Arm Cortex-M4/M33 cores to deliver the best balance of performance and power
- Arm Cortex-M85 core with Helium™ technology for unprecedented performance



Flexible Software Solution

- Supported by an open and flexible ecosystem concept, the Flexible Software Package (FSP)
- Can be replaced and expanded by any other RTOS or middleware



Best-in-Class Peripheral IP

- Excellent HMI capacitive touch technology
- The industry's highest code flash memory capacity
- Wide range of connectivity solutions

Renesas RA Product Series

The five Renesas RA Family MCU series are based on 32-bit Arm Cortex-M cores. All five have been designed on common DNA, making these products feature- and pin-compatible. This allows easy scalability and code reuse from one device to another.

	Performance Range	Feature	Series Memory Ranges	ASSP Extensions
 RA8	Over 240 MHz 1.68-3.6V	Highest Performance, HMI, Connectivity, Security, Analog	Highest memory integration: up to 2MB Flash, 2MB SRAM	Motor/Inverter AI/ML, HMI
RA6	Up to 240 MHz 2.7-3.6V	Advanced Performance, Connectivity, Security	High memory integration: up to 2MB Flash, 640kB SRAM	Motor/Inverter AI/ML, HMI
RA4	Up to 100 MHz 1.6V-5.5V	Excellent Power, High Performance Mix Paired with Security	Medium memory integration: up to 1MB Flash, 128kB SRAM	Motor/Inverter Sensor, Wireless
RA2	Up to 64 MHz 1.6V-5.5V	Low Power	Medium memory integration: up to 512kB Flash, 48kB SRAM	Rich Analog
RA0	32 MHz 1.6V-5.5V	Optimized functionalities Ultra Low power	Small memory integration: up to 64kB Flash, 12kB SRAM	Sensor

RENESAS RA FAMILY

Target Markets and Benefits

Industrial Automation

- Long product life
- Temperature up to 105°C
- Industrial quality grade
- Strongest robustness
- 24-bit $\Sigma\Delta$ ADC for sensors

Security

- Isolated crypto subsystem
- Symmetric/asymmetric hardware acceleration
- True Random Number Generator (TRNG)
- NIST-certified algorithms
- Key isolation and management

Connectivity

- Large on-chip RAM suitable for stacks
- CAN/USB/Ethernet
- Large amount on serial interfaces
- QSPI interfaces
- Integrated crypto module

Building Automation

- High Flash/RAM ratio
- Wide range of connectivity
- Rich analog features
- Small packages

Metering

- Scalable lineup
- Industrial quality grade
- Long product life
- Integrated crypto module


White Goods

- Temperature up to 105°C
- Scalable lineup
- Motor control solutions
- Capacitive touch interface
- LCD control





Tools and Support

IDE	Renesas e ² studio	Keil MDK	IAR EWArm
Compiler	<ul style="list-style-type: none"> • GCC • LLVM • Arm Compiler* • IAR Arm Compiler* 	<ul style="list-style-type: none"> • Arm Compiler* 	<ul style="list-style-type: none"> • IAR Arm Compiler*
Debug Probe	<ul style="list-style-type: none"> • Renesas E2/E2 Lite • SEGGER J-Link 	<ul style="list-style-type: none"> • SEGGER J-Link • Keil ULINK / CMSIS-DAP** 	<ul style="list-style-type: none"> • IAR I-jet • SEGGER J-Link • Renesas E2/E2 Lite • CMSIS-DAP**
Production Programmer	<ul style="list-style-type: none"> • Renesas PG-FP6 • SEGGER J-Flash • Partner solutions 		

* Compiler must be purchased and licensed directly from third party
 ** Limited support



Evaluation Kits

General-purpose Kits		Application-specific Kits	3rd Party/Partner Kits
MCU evaluation including on-board debugger (EK-RAxxx, FPB-RAxxx)	Individual kits for several products of each Renesas RA series (EK-RAxxx)	Motor, Voice, AI, Touch, Cloud, etc.	Access to partner's ecosystem and tools
			

Learn more: renesas.com/ra/kits

For more information about the Renesas RA MCU family, visit: renesas.com/RA



renesas.com

Corporate Headquarters
 TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks
 Arm® and Cortex® are registered trademarks of Arm Limited. Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information
 For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

© 2024 Renesas Electronics Corporation. All rights reserved.