




Arm® Cortex®-R52 Based MPU RENESAS RZ/N2L GROUP

Easily Implement Industrial Ethernet and TSN on Industrial Systems

The RZ/N2L industrial Ethernet microprocessor (MPU) easily adds network functionality onto industrial equipment and machine. RZ/N2L is optimized as a dedicated networking companion chip that can easily implement industrial Ethernet communication and TSN in industrial equipment. The RZ/N2L is a single chip solution for both industrial network and application processing.



Key Features

- Arm® Cortex®-R52 @ Max 400MHz
- A tightly coupled memory (256KB) directly connected to CPU
- 3-port Gigabit Ethernet switch supporting next-generation network standard TSN and EtherCAT® salve controller
- Host interface allows application CPU to directly connect to RZ/N2L, and access at high speed
- Application CPU can directly access to the system RAM of RZ/N2L
- ELC (Event Link Controller) can be operated without the support of CPU processing
- Supports functional safety like a safety MCU

Benefits


- Enable next-generation network standard TSN, and major industrial Ethernet protocols such as EtherCAT®, PROFINET, EtherNet/IP™
- Add industrial Ethernet features to industrial equipment without major system change
- Operate industrial Ethernet and user application on one chip
- Realize synchronized operation with low latency to the time synchronization in TSN network
- Accelerate functional safety (FuSa) development and certification through upcoming certified FuSa solution for RZ/N2L

Target Applications

- Communication unit
- Remote IO
- Sensor Hub
- Gateway
- Motor Drive

Block Diagram

- Arm® Cortex®-R52 400MHz
- FPU
- TCM 256KB (with ECC)
- Embedded 1.5MB (with ECC)
- 3-port Gigabit Ethernet switch with TSN
- EtherCAT slave controller
- Serial host I/F, Parallel host I/F
- xSPI
- CAN-FD
- PWM Timer
- ΔΣ I/F
- ADC
- Trigonometric function unit



RENESAS RZ/N2L GROUP

Industrial Network Protocol Supported

- EtherCAT®
- PROFINET RT/IRT
- EtherNet/IP™
- OPC UA over TSN
- TSN (IEC/IEEE 60802 Industrial Profile)
- CC-Link IE Field Basic/TSN class A
- Modbus/TCP
- POWERLINK
- DeviceNet
- PROFIBUS
- CANopen
- Modbus/RTU, ASCII
- BACnet

Evaluation Environment and Software

- Renesas e²studio + J-Link by Segger
- IAR Embedded Workbench for Arm + I-Jet ICE/ I-Jet Trace by IAR
- Flexible Software Package (FSP)
 - Hardware drivers
 - FreeRTOS
- Industrial network protocol (sample code)
- Security software package



Renesas Starter Kit+ for RZ/N2L
(P/N:RTK9RZN2LOS00000BE)

Product Information

Part Number	R9A07G084M08GBG	R9A07G084M04GBG	R9A07G084M08GBA	R9A07G084M04GBA
CPU	Cortex®-R52 (Max 400MHz)			
Tightly Coupled Memory	ATCM 128KB (w/ECC) / BTCM 128KB (w/ECC)			
RAM	1.5MB (w/ECC)			
External bus	8, 16bit		Not supported	
Host I/F	Serial Host	OSPI/QSPI		QSPI
	Parallel Host	8, 16bit		Not supported
Industrial Ethernet Protocol	EtherCAT®, PROFINET RT/IRT, EtherNet/IP™, TSN (IEC/IEEE 60802 Industrial Profile), CC-Link IE Field Basic, OPC UA over TSN			
Ether Port	3 ports		2 ports	
Motor Control Peripherals	PWM Timer (MTU3, GPT), ADC*, $\Sigma\Delta$ Interface, Trigonometric function unit			
Security	Supported	Not Supported	Supported	Not Supported
Power	1.1V, 1.8V, 3.3V			
Operating Temperature	Tj = -40 to +125°C			
Package	FBGA		FBGA	
Pin Count	225pin		121pin	
Package Information	13mm x 13mm, 0.8mm pitch		10mm x 10mm, 0.8mm pitch	

*225pin only

Visit www.renesas.com/rzn2l to learn more about RZ/N2L.

Visit www.renesas.com/rskrzn2l for more information about the evaluation kit of RZ/N2L.

renesas.com

Corporate Headquarters
TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks
Arm® and Cortex® are registered trademarks of Arm Limited. Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information
For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

© 2022 Renesas Electronics Corporation. All rights reserved.