

Main Specifications of the RX23T Group of MCUs

Group name	RX23T Group		
	48-pin LQFP 0.5 mm	52-pin LQFP 0.65 mm	64-pin LQFP 0.5 mm
Flash ROM (KB)	64 to 128		
RAM (KB)	10		
Power supply voltage	2.7 V to 5.5 V		
Operating frequency	40 MHz		
I/O ports	I/O:35 Input:1	I/O:38 Input:1	I/O:48 Input:1
CPU	32-bit CPU RXv2 (Floating-point instructions: 11, DSP instructions: 23)		
FPU	Single precision (32-bit) floating point Data types and floating-point exceptions in conformance with the IEEE754 standard		
Peripheral functions	3-phase non-overlapping waveform output for inverter control: 1 channel		
	Phase counting modes for encoder sensor		
	Controls the high-impedance state for PWM output		
	12-bit AD converter (10ch): Three sample-and-hold circuits for current sensing		
	Comparator: 3 channels (D/A converter (DA) for generating comparator reference voltage)		
	Serial communications interfaces: 2 channels		
	I2C bus interface: 1 channel		
	Serial peripheral interface (SPI): 1 channel		
Safety functions	Clock frequency accuracy measurement circuit		
	RAM test assistance functions using the DOC		
	Independent watchdog timer		
	Self-diagnostic and disconnection-detection assistance functions for the A/D converter		
	CRC calculator (CRC)		
	Register write protection function		
Operating temperature range	Ta = -40 to +85°C, -40 to 105°C		
Part no. (ROM 64 KB, Ta = -40 to +85°C)	R5F523T3ADFL	R5F523T3ADFD	R5F523T3ADFM

(Note) Part number varies according to the ROM size and operating temperature.

(Remarks) SuperFlash® is a registered trademark of Silicon Storage Technology, Inc., of the U.S.A. in the United States, Japan, and other countries. Names of products or services mentioned in this release are the trademarks or registered trademarks of their respective owners. Other product and service names that appear in this press release are trademarks or registered trademarks of their respective owners.