
Option List HD6432142,HD6432132,HD6432130

Please check off the appropriate applications by , or within and enter the necessary information.

(1) ROM size

| | | | |
|--------------------------|-----------|---|-----------|
| <input type="checkbox"/> | HD6432142 | : | 64-kbytes |
| <input type="checkbox"/> | HD6432132 | : | 64-kbytes |
| <input type="checkbox"/> | HD6432130 | : | 32-kbytes |

(2) System Oscillator(OSC1,OSC2)

| | | | | |
|--------------------------|--------------------|-----|--|-----|
| <input type="checkbox"/> | Crystal oscillator | f = | | MHz |
| <input type="checkbox"/> | External clock | f = | | MHz |

| | |
|-------------------------------|--|
| Date of order | |
| Customer | |
| Department | |
| Name | |
| ROM code Name | |
| LSI number (Renesas entry) | |

(3) Power Supply Voltage/Maximum Operating Frequency

| | |
|--------------------------|---|
| <input type="checkbox"/> | V _{cc} = 4.5V to 5.5V (20 MHz max.) |
| <input type="checkbox"/> | V _{cc} = 4.0V to 5.5V (16 MHz max, Only Single-Chip Mode is available in JE specification.) |
| <input type="checkbox"/> | V _{cc} = 2.7V to 5.5V (10 MHz max.) |
| <input type="checkbox"/> | V _{cc} = 4.0V to 5.5V (10 MHz max, Low EMI Noise version, Only Single-Chip Mode is available.) |

Notes 1.Please select the power supply voltage/operating frequency version according to the power supply voltage used.

Example: For use at V_{cc} = 4.5V to 5.5V/f = 10MHz
select V_{cc} = 4.5V to 5.5V(20MHz max.).

2.The power supply voltage and maximum operating frequency of the selected version should also be entered on the Single-Chip Microcomputer Ordering Specifications sheet.