





REVISIONS			DATE	APPROVED
REV	DESCRIPTION			
00	INITIAL RELEASE		07/15/99	Tu Vu
01	COMBINE POD & LAND PATTERN		06/12/13	KS




TOLERANCES UNLESS SPECIFIED		DATE		TITLE	
DECIMAL	ANGULAR	07/15/99		BS 352 PACKAGE OUTLINE	
XXX±	±	DRAWN	JY	35.0 X 35.0 mm BODY	
XXXX±		CHECKED		SBCA	
XXXX±		APPROVALS		DRAWING No.	
				PSC-4080	
				REV 01	
				DO NOT SCALE DRAWING	
				SHEET 1 OF 3	


IDT 6024 SILVER CREEK VALLEY ROAD
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 492-8674
 www.IDT.com

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	07/15/99	TJ WJ
01	COMBINE POD & LAND PATTERN	06/12/13	KS

NOTES:


- 1 ALL DIMENSIONING AND TOLERANCING CONFORM TO ANSI Y14.5M-1982
- 2 "e" REPRESENTS THE BASIC SOLDER BALL GRID PITCH
- 3 "M" REPRESENTS THE MAXIMUM SOLDER BALL MATRIX SIZE
- 4 "N" REPRESENTS THE BALLCOUNT NUMBER
- 5 DIMENSION "b" IS MEASURED AT THE MAXIMUM SOLDER BALL DIAMETER, PARALLEL TO PRIMARY DATUM [C-C]
- 6 SEATING PLANE AND PRIMARY DATUM [C-C] ARE DEFINED BY THE SPHERICAL CROWNS OF THE SOLDER BALLS
- 7 "A1" ID CORNER MUST BE IDENTIFIED BY CHAMFER, INK MARK, METALLIZED MARKING, INDENTATION OR OTHER FEATURE ON PACKAGE BODY
- 8 EXACT SHAPE OF EACH CORNER IS OPTIONAL
- 9 ALL DIMENSIONS ARE IN MILLIMETERS



SYMBOL	JEDEC VARIATION			NOTE
	MIN	NOM	MAX	
A	-	-	1.70	
A1	.50	.60	.70	
A2	.80	.90	1.00	
A3	.20	-	-	
D	35.00 BSC			
E	35.00 BSC			
M	26 (DEPOPULATED)			3
N	352			4
e	1.27 BSC			
b	.60	.75	.90	5
CENTER BALL MATRIX	N/A			

TOLERANCES UNLESS SPECIFIED DECIMAL ± XXXX ± ANGULAR ±		IDT 6024 SILVER CREEK VALLEY ROAD San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 492-8674 www.IDT.com	
APPROVALS	DATE	TITLE	REV
DRAWN gy	07/15/99	BS 352 PACKAGE OUTLINE 35.0 X 35.0 mm BODY TBGA	01
CHECKED		SIZE C DRAWING No. PSC-4080	REV 01
DO NOT SCALE DRAWING		SHEET 2 OF 3	


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	07/15/99	TJ WJ
01	COMBINE POD & LAND PATTERN	06/12/13	KS



RECOMMENDED LAND PATTERN DIMENSION

NOTE:

- 1) ALL dimensions are in mm, Angles in degrees.
- 2) Top down view, as view on PCB.
- 3) NSMD Land Pattern Assumed
- 4) Land Pattern Recommendation as per IPC-7351B generic requirement for surface mount design and Land Pattern.

TOLERANCES UNLESS SPECIFIED		DATE	
DECIMAL	ANGULAR	07/15/99	
XXX±	±		
XXXX±			
APPROVALS	DATE	TITLE	REV
DRAWN TJ	07/15/99	BS 352 PACKAGE OUTLINE	01
CHECKED		35.0 X 35.0 mm BODY	
		TBGA	
 IDT 6024 SILVER CREEK VALLEY ROAD San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 492-8674 www.idt.com		SIZE	REV
		C	01
DO NOT SCALE DRAWING		PSC-4080	
		SHEET	3 OF 3