



Reference	Dimension in mm		
Symbol	Min	Nom	Max
D	-	16.00	-
E	-	16.00	-
H <sub>D</sub>	-	14.00	-
H <sub>E</sub>	-	14.00	-
A	-	-	1.60
A1	0.05	0.10	0.15
A2	1.35	1.40	1.45
bp	0.22	0.32	0.38
c	0.09	-	0.20
θ	0.00	3.50	7.00
e	0.65 BSC		
y	-	-	0.08
LP	0.45	0.60	0.75
L1	-	1.00	-

**NOTES:**

1. JEDEC compatible.
2. All dimensions are in mm and angles are in degrees.
3. Use  $\pm 0.05$  mm for the non-toleranced dimensions.
4. Foot length is measured at gauge plane 0.25 mm above seating plane.
5. Details of pin 1 identifier is optional but must be located within the zone indicated.