

## Medical applications with Renesas GreenPAK and AnalogPAK

---

This white paper describes how the GreenPAK and AnalogPAK can be used for medical applications. Their capabilities, resources and versatility are described in terms of applicability for medical technologies.

### Introduction

In the dynamic industry of medical technology, innovation, adaptability, and efficiency have become key factors. In this context, Renesas GreenPAK and AnalogPAK, two programmable mixed-signal devices, can be considered as a so useful resource for innovative developments in medical applications. This whitepaper delves into the characteristics of both GreenPAK and AnalogPAK, focusing on their individual capabilities and the embedded resources that can be fully leveraged for medical device design.

Both programable mixed-signal IC's integrate highly configurable analog and digital components in their different variants, where it can be mentioned analog comparators (ACMPs), operational amplifiers (OPAMPs), PWM modules, Rheostats, Look-Up tables (LUTs), clocks, counter/delays, DFFs, Asynchronous State Machines (ASM) etc.

In most cases, GreenPAKs and AnalogPAKs can be considered as cost-effective non-volatile memory (NVM) configurable hardware devices that allow users to configure both analog and digital functions, enabling processing of mixed signal inputs by performing analog signal conditioning, digital signal processing, and mixed-signal interfacing tasks. In this way, many system functions can be integrated in a single custom circuit, minimizing component count, board space, and power consumption.

In this context, as medical devices grow in complexity, the imperative for programmable solutions and precise analog signal processing with reduced power consumption and in a highly efficient design becomes increasingly crucial. Thus, both GreenPAK and AnalogPAK play a key role in overcoming challenges related to customization and analog functionality.

## 1. AnalogPAK and GreenPAK: A dive into their capabilities for medical applications

Both devices are, at their essence, highly programmable devices that allow to implement applications for different industries and technologies. With a versatile architecture that allows users to configure its functionality according to specific needs, they stand as very interesting options for medical applications because of its adaptability.

The advantages of GreenPAK and AnalogPAK extend beyond mere programmability, seamlessly integrating analog and digital elements. As they are designed for mixed-signal applications, their programmable matrices can be thought as a bridge between analog and digital applications, providing a cost-effective solution for applications that demand quite sophisticated processing resources for both signal types. This can be implemented due to the availability of both analog and digital peripherals integrated in the IC's that allow to combine analog and digital processing. In Table 1, the resources of some of the devices are shown.

	SLG46533V	SLG46534V	SLG46620V	SLG46826V	SLG47004V	SLG47115V
<b>Family</b>	GreenPAK	GreenPAK	GreenPAK	GreenPAK	AnalogPAK	HVPAK
<b># of GPIOs</b>	18	12	18	17	8	8
<b>ACMPs / Current Sense / Differential AMP</b>	4/0/0	3/0/0	6/0/0	4/0/0	3/0/0	2/1/1
<b>OPAMPs</b>	-	-	-	-	3	-
<b>Digital Rheostat</b>	-	-	-	-	2	-
<b>ADC</b>	-	-	1 (8-bit)	4	-	-
<b>LUTs</b>	25	17	26	19	20	17
<b>Counters/Delays</b>	7	7	10	8	7	5
<b>DFF/Latch</b>	15	8	12	17	18	15
<b>PWM Modules</b>	-	-	3	-	-	2
<b>Internal OSC [Hz]</b>	25k   2M   25M	25k   2M   25M	1.7k   25k   2M   25M	25k   2M   25M	2k   25M	2k   25M
<b>ASMs</b>	-	8-state	-	-	-	-
<b>Communications</b>	I <sup>2</sup> C	I <sup>2</sup> C	SPI	I <sup>2</sup> C	I <sup>2</sup> C	I <sup>2</sup> C
<b>HV-Out</b>	-	-	-	-	-	2

**Table 1. GreenPAK and AnalogPAK IC's**

Their flexibility and configurability make them suitable for a wide range of applications. Specifically, analog acquisition and conditioning combined with digital processing and control are invaluable capabilities in medical devices that require a combination of different types of signals.

With the same industry in mind, energy efficiency is non-negotiable. GreenPAK's low power consumption becomes a key factor for devices where battery life is critical. This is the case of energy-sensitive medical devices, where it must be ensured reliability while minimizing the need for frequent battery replacements.

If more analog features are required, AnalogPAK IC's emerge as the most suitable option for precision analog signal processing. Their capabilities in handling analog signals with accuracy and reliability make them a very interesting solution for applications where complex signals must be processed.

As a resume, the key resources and characteristics for medical applications that make GreenPAK and AnalogPAK IC's a suitable solution are:

- **Sensors and Actuators Integration:** Medical applications are based on human body signals acquired with sensors (temperature, oxygen, ECG signals) and sometimes require actuators (motors, switches, buzzers). The entire GreenPAK and AnalogPAK variants include a variety of input and output interfaces.
- **Signal Processing:** GreenPAK devices offer a variety of digital signal processing resources, such as LUTs, ASMs and DFF, which can also be combined with analog resources such as OPAMPs and PWMs so they can be used for mixed signal treatment applications.

- **Low Latency:** As medical applications can require real-time control or monitoring, low-latency signal paths are mandatory. In this context, GreenPAKs and AnalogPAKs have very low signal propagation delays.
- **Security and Reliability:** Medical applications must be secure and reliable as they are meant to care for humans. As the analyzed devices do not have CPU cores and programmable firmware, they cannot be hacked.
- **Low Power Consumption and Small Form Factor:** Some medical devices can be battery-powered or need to operate on low power to extend their operating period. Also, there are portable medical devices. The GreenPAK family are very efficient in terms of power consumption, with typical idle current consumption in the order of  $\mu\text{A}$  and they are offered in small TQFN and MSTQFN packages. These factors make them suitable for such types of applications.
- **Compatibility:** As input and outputs of the IC's are digital or analog signals, including standardized protocols such as I<sup>2</sup>C or SPI, they are fully compatible with other components that are usually used in these applications.

## 2. Case Studies

### 2.1 Vital Sign Monitoring System

The development and implementation of a vital sign monitoring system is based on measuring heart rate, temperature, blood pressure and breathing rate. To do so, different sensors must be used, and analog signal conditioning must be implemented. Based on the capabilities described earlier, using both GreenPAK and AnalogPAK is a very interesting alternative for processing these signal types. This case also illustrates how they can be combined, taking the advantage of their flexibility, programmability, and analog precision.

More details about an aspect of this application can be found in the Renesas Application Note [AN-CM-307 Analog Front End for Heart Rate Monitor](#) and [AN-CM-326 Analog Front-End for Electrocardiogram Monitor](#). It is shown how the heart rate can be measured, including different techniques to obtain the signal and an IC configuration to implement the analog front-end.




Figure 1: Analog Front End for Heart Rate Monitor – Block Diagram




Figure 2: Analog Front-End for Electrocardiogram Monitor – Structure

For temperature and breathing rate, the analog input capabilities such as the ADCs can be applied to interface with sensors to measure temperature, and digital inputs and DFFs with timing blocks can be used for breathing rate measurement.

In the case of blood pressure sensing, programmable digital logic can be used to implement control algorithms. This can include managing inflation and deflation of the cuff, and the sequence for reading sensor values and determine blood pressure levels. The analog signals from the sensors can be conditioned and acquired with the OPAMPs and processed with Analog Comparators.

## 2.2 Glucose Sensor and Monitor

In this case, a glucose sensor and monitor device is analyzed. This application is usually designed as a portable device, powered by a rechargeable battery, playing an important role in controlling diabetic patient's health. As a consequence, high efficiency in energy consumption is required. This is the case of AnalogPAK, which can be used for both signal conditioning and measurement as well as signal processing and user interface, with a highly efficient IC in terms of power consumption, both in processing state and in idle state.

More details about this application can be found in the Renesas Application Note [AN-CM-222 Customized Glucometer using GreenPAK](#). It is shown how a disposable test strip can be measured and analyzed with a GreenPAK IC, giving to the user the information about his glucose level.




Figure 3: Customized Glucometer using GreenPAK – Hardware Schematic

### 2.3 Programmable Drug Delivery Device

A Programmable Drug Delivery Device (PDDD) must be able to deliver different medication regimens, with enhanced user safety and precise control over drug delivery parameters. To do so, the GreenPAK and AnalogPAK ICs can be utilized for various functions, including digital logic to implement control algorithms for drug delivery such as sequencing the opening and closing of valves or controlling the operation of a pump based on the prescribed dosage. This task must be implemented with precise timing circuits where can be used the programmable timers to ensure accurate and controlled drug release intervals.

Also, the OPAMPs and analog input capabilities can be applied to interface with sensors measuring parameters like drug levels, temperature, and pressure. Analog comparators and amplifiers can be configured to process sensor signals.

Finally, the PWM blocks, and their outputs, can be used to control actuators such as pumps or valves. PWM can be employed to adjust the speed of a pump or the opening/closing duration of a valve, allowing precise control over drug delivery rates.

## 3. Conclusion

In conclusion, in this whitepaper an analysis of the capabilities, applications, and collaborative potential of Renesas' GreenPAK and AnalogPAK in the continuous evolving field of medical technology is made. The programmability and analog resources of both GreenPAK's and AnalogPAK's make them, both individually and in collaboration, as suitable technologies in medical device design.

## 4. Revision History

Revision	Date	Description
1.00	May 13, 2023	Initial release.

## IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

### Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

### Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

### Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit [www.renesas.com/contact-us/](http://www.renesas.com/contact-us/).