

Application Note

DA1453x Flash Selector Guide

AN-B-088

Abstract

This document presents an overview of supported Flash devices for the DA1453x and DA14585 Bluetooth IC's.

- DA1453x is referring to DA14531-00, DA14531-01, DA14530 and DA14535.
 - The DA14531-00 is the main DA14531 device. The -00 is just a new naming to introduce the variant DA14531-01.
 - The DA14531-01 is a ROM variant of the main DA14531-00.
 - The DA14535 is a DA14531 upgrade.
-

DA1453x Flash Selector Guide

1 List of Supported Renesas Flash Devices

Table 1: Ordering Information

Memory Size	Flash Device	DA1453x	DA14585
512 kBit	AT25DF512C	✓	✓
	AT25XE512C	✓	✓
1 Mbit	AT25DN011	-	✓
	AT25DF011	✓	✓
	AT25XE011	✓	✓
2 Mbit	AT25EU0021A	✓	✓
	AT25DF021A	✓	✓
	AT25XE021A	✓	✓
4 Mbit	AT25XE041B	✓	✓
	AT25FF041A	✓ (1)	✓
	AT25XE041D	✓ (1)	✓
	AT45DB041E	-	✓
8 Mbit	AT25FF081A	✓(1)	✓
	AT25XE081D	✓ (1)	✓
32 Mbit	AT25SL321	✓	✓

Note 1 This requires a [secondary loader](#) in OTP for enabling Ultra Deep Power Down mode.

2 List of Supported 3rd Party Flash Devices

Table 2: Ordering Information

Memory Size	Flash Device	Manufacturer	DA1453x	DA14585
512 kBit	MX25R512F	Macronix	✓	✓
1 Mbit	P25X10U	Puya	✓	✓
	P25Q10H	Puya	✓	✓
	GD25WD10CTIG	GigaDevice	✓	✓
	W25X10CL	Winbond	✓	✓
2 Mbit	MX25R2035F	Macronix	✓	✓
	GD25VQ20C	GigaDevice	✓	✓
	GD25WD20CTIG	GigaDevice	✓	✓
	W25X20CL	Winbond	✓	✓
4 Mbit	GD25WD40CTIG	GigaDevice	✓	✓
	W25X40CL	Winbond	✓	✓

For additional information related to external memories, please refer to [AN-B-072 DA1453x Booting from OTP and Serial Interfaces](#) and [AN-B-055 DA14585 interfacing with external memory](#).

3 References

- [UM-B-117](#): DA14531 Getting Started with the Pro-Development Kit
- [UM-B-165](#): DA14535 Getting Started with the Pro-Development Kit
- [UM-B-119](#): DA1453x/DA1458x SDK 6 Software Platform Reference: To know more about the software architecture

DA1453x Flash Selector Guide**Revision History**

Revision	Date	Description
1.8	13-02-2024	Section 3 and support for DA14535 device added
1.7	31-May-2022	Update Table 1 (Add AT25SL321) and Table 2 (Add W25X40CL)
1.6	24-Jan-2022	Rebranded to Renesas.
1.5	17-11-2021	Update Table 1
1.4	28-09-2021	Update Table 1 (Add AT25EU0021A)
1.3	30-06-2021	Update Hyperlinks in section 1
1.2	15-02-2021	Update Hyperlinks in section 2
1.1	12-11-2020	Update Table 1
1.0	22-10-2020	Initial Release

DA1453x Flash Selector Guide

Status Definitions

Status	Definition
DRAFT	The content of this document is under review and subject to formal approval, which may result in modifications or additions.
APPROVED or unmarked	The content of this document has been approved for publication.

RoHS Compliance

Dialog Semiconductor's suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

DA1453x Flash Selector Guide

Important Notice and Disclaimer

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

© 2024 Renesas Electronics Corporation. All rights reserved.

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:

<https://www.renesas.com/contact/>

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

(Rev.1.0 Mar 2020)