

Analog IP

Analog-PLL For Frequency Multiplying

Key Features

- Including Loop-filter
- VCO operating range : 850MHz - 1700 MHz
- Output frequency range : 850MHz – 1700 MHz
- Input frequency range : 9.6MHz - 216MHz
- Multiplying (Output freq. / PFD freq.) : 49 - 127
- Divider
 - 7bit feedback divider and 3bit input divider
- Power-down Mode
- Multiple outputs with post-divider
- Power-on sequence is constraint-free
- STBY sequence is constraint-free

Technology

Process : TSMC 28nm HPM/HPC

Operating Condition

Parameter		Min	Max	Unit
Operating Voltage (AVDD)		1.62	1.98	V
Operating Voltage (VDD)		0.935	1.08	V
Junction Temperature		-40	125	°C
Input Clock	Duty	30	70	%
	Rise/Fall time	-	0.2	ns

**This IP is contract design IP. Please contact for detail.*

CTPD-24-136
R06PF0103EJ0100