

Product Change Notice (PCN)

Subject: Add Alternate Assembly Location for VFQFPN-8 Package

Publication Date: 3/2/2022

Effective Date: 6/2/2022

Revision Description:

Initial Release

Description of Change:

This notification is to advise our customers that Renesas is adding CRSS, Malaysia as an alternate assembly location in addition to the current assembly location at ASEC, Taiwan. Presently, CRSS Malaysia is the qualified assembly location for Renesas. The material sets of the current and the alternate assembly locations are as shown in the below table.

No change in moisture sensitive level as a result of this change.

| Material Sets | Existing Assembly ASEC Taiwan | Alternate Assembly CRSS Malaysia |
|----------------|----------------------------------|-------------------------------------|
| Die Attach | ATB-125 film | HR-5104 film |
| Bonding Wire | Copper wire | Copper wire |
| Mold Compound | G700LA | G770HCD |
| Plating Finish | PPF | PPF |

Affected Product List: F2910NBGP, F2910NBGP8, F2910NBGP/W, F2911NBGP, F2911NBGP8.

Reason for Change:

The change is for increased manufacturing capability and business continuity.

Impact on Fit, Form, Function, Quality & Reliability:

The change is expect will have no impact on the form, fit, function, quality, reliability and environmental compliance of the products.

Product Identification:

Assembly lot# with prefix "RC" denote ASEC Taiwan, prefix "MS" denote CRSS Malaysia.

Qualification Status: Completed and Passed. Refer Appendix A.

Sample Availability Date: 4 weeks from sample booking date

Device Material Declaration: Available upon request

Note:

1. Acknowledgement must be received by Renesas within 30 days or Renesas will consider the change as approved.
2. If timely acknowledgement is provided by Customer, then Customer shall have 90 days from the date of receipt of this PCN to make any objections to this PCN. If Customer fails to make objections to this PCN within 90 days of the receipt of the PCN then Renesas will consider the PCN changes as approved.
3. If customer cannot accept the PCN then customer must provide Renesas with a last time buy demand and purchase order.

For additional information regarding this notice, please contact idt-pcn@lm.renesas.com

Appendix A - Qualification Results

Affected Packages: VFQFPN-8

Qual Vehicle: VFQFPN-8

Assembly Material: As shown in page 1

Qual Plan & Results: Tests are in accordance with JEDEC47 recommended tests.

| Test Descriptions | Test Method | Test Results (Rej/SS) | | |
|--|----------------------------|-----------------------|-------|-------|
| | | Lot 1 | Lot 2 | Lot 3 |
| * Temperature Cycling (-55°C to 125°C, 700 cycles) | JESD22-A104 | 0/25 | 0/25 | 0/25 |
| * Temperature Humidity Bias (HAST) (130°C/85% RH, Vccmax, 96 Hrs) | JESD22-A110 | 0/25 | 0/25 | 0/25 |
| High Temperature Storage Bake (150°C, 1000 Hrs) | JESD22-A103 | 0/25 | 0/25 | 0/25 |
| Bond Pull Strength | Mils-Std-883, M2011 | 0/5 | 0/5 | 0/5 |
| Bond Shear Test | JESD22-B116 | 0/5 | 0/5 | 0/5 |
| Moisture Sensitivity Level, MSL | J-STD-20 / MSL 1, 260°C | 0/25 | 0/25 | - |

**Tests were subjected to Preconditioning per JESD22-A113 prior to stress test*