

# シリアルEEPROM 発注型名

## R1E X 24 064 A SA S0 I #S0

RENESAS EEPROM

Operating Voltage

<b>X</b>	1.8 ~ 5.5V
<b>V</b>	2.5 ~ 5.5V

Interface

<b>24</b>	I2C
<b>25</b>	SPI

Memory Density

<b>002</b>	2Kb	<b>128</b>	128Kb
<b>004</b>	4Kb	<b>256</b>	256Kb
<b>008</b>	8Kb	<b>512</b>	512Kb
<b>016</b>	16Kb		
<b>032</b>	32Kb		
<b>064</b>	64Kb		

Chip Generation

<b>A</b>	A mask
<b>B</b>	B mask

Environmental / Packing specs

	Package Material		Tape & Reel (pcs / reel)	
			SOP (8)	TSSOP (8)
<b>#S0</b>	Pb-free	Au-wire	2,500	3,000
<b>#U0</b>	Pb-free, Halogen-free	Au-wire	2,500	3,000
<b>#K0</b>	Pb-free, Halogen-free	Cu-wire	4,000	

Operating Temperature

<b>I</b>	Industrial: -40 ~ 85°C
----------	------------------------

Function

<b>S0</b>	I2C
<b>00</b>	SPI

Package

<b>SA</b>	8pin SOP
<b>TA</b>	8pin TSSOP