

Product Change Notice (PCN)

Subject: Datasheet specification change for listed Renesas HIP4020* Products

Publication Date: 2/11/2019

Effective Date: 5/12/2019

Revision Description:

Initial Release

Description of Change:

This notice is to inform you that Renesas Electronics America Inc has updated datasheet. The update includes a change to the following electrical parameter: -

#	Change details	Maximum Limit		Unit
		From	To	
1	P-channel $r_{DS(ON)}$, Low Supply Voltage	2.1	2.5	Ω

Affected Product List

HIP4020IBZ
HIP4020IBZT
HIP4020IBZTS2705

Reason for Change:

The change to the datasheet aligns the documentation with the product characteristics and is necessary to maintain product manufacturability in support of customer delivery requirements. Details regarding the change are contained on the following page. The product datasheet is available on the Renesas website at : -

<https://www.renesas.com/sg/en/www/doc/datasheet/hip4020.pdf>

Impact on fit, form, function, quality & reliability:

The change will have no other impact on the form, fit, function, quality, reliability and environmental compliance of the devices.

Product Identification:

Product affected by this change is identifiable via Renesas’s internal traceability system.

Qualification status: Not Applicable

Sample availability: 2/18/2019

Device material declaration: Available upon request

Questions or requests pertaining to this change notice, including additional data or samples, must be sent to Renesas within 30 days of the publication date.

For additional information regarding this notice, please contact your regional change coordinator (below)			
Americas: PCN-US@RENESAS.COM	Europe: PCN-EU@RENESAS.COM	Japan: PCN-JP@RENESAS.COM	Asia Pac: PCN-APAC@RENESAS.COM

Appendix A – Affected datasheet (see attached)

HIP4020* datasheet

From (page 3 of 10)

Electrical Specifications $T_A = 25^\circ\text{C}$, $V_{DD} = +5\text{V}$, $V_{SSA} = V_{SSB} = V_{SS} = 0\text{V}$, Unless Otherwise Specified

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNITS
Input Leakage Current	I_{LEAK}	$V_{DD} = +15\text{V}$	-	-	25	nA
Low Level Input Voltage	V_{IL}		V_{SS}	-	0.8	V
High Level Input Voltage	V_{IH}		2		V_{DD}	V
ILF Output Low, Sink Current	I_{OH}	$V_{OUT} = 0.4\text{V}$, $V_{DD} = +12\text{V}$	15	-	-	mA
ILF Output High, Source Current	I_{OL}	$V_{OUT} = 11.6\text{V}$, $V_{DD} = +12\text{V}$	-	-	-15	mA
Input Capacitance	C_{IN}		-	2	-	pF
P-Channel $r_{DS(ON)}$, Low Supply Voltage	$r_{DS(ON)}$	$V_{DD} = +3\text{V}$, $I_{SOURCE} = 250\text{mA}$	-	1.6	2.1	Ω

To (page 3 of 10)

Electrical Specifications $T_A = 25^\circ\text{C}$, $V_{DD} = +5\text{V}$, $V_{SSA} = V_{SSB} = V_{SS} = 0\text{V}$, unless otherwise specified

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Input Leakage Current	I_{LEAK}	$V_{DD} = +15\text{V}$	-	-	25	nA
Low Level Input Voltage	V_{IL}		V_{SS}	-	0.8	V
High Level Input Voltage	V_{IH}		2		V_{DD}	V
ILF Output Low, Sink Current	I_{OH}	$V_{OUT} = 0.4\text{V}$, $V_{DD} = +12\text{V}$	15	-	-	mA
ILF Output High, Source Current	I_{OL}	$V_{OUT} = 11.6\text{V}$, $V_{DD} = +12\text{V}$	-	-	-15	mA
Input Capacitance	C_{IN}		-	2	-	pF
P-Channel $r_{DS(ON)}$, Low Supply Voltage	$r_{DS(ON)}$	$V_{DD} = +3\text{V}$, $I_{SOURCE} = 250\text{mA}$	-	1.6	2.5	Ω