


### 32-PIN PLASTIC SDIP (10.16mm (400))



**NOTES**

1. Each lead centerline is located within 0.17 mm of its true position (T.P.) at maximum material condition.
2. Item "e1" to center of leads when formed parallel.

(UNIT:mm)

ITEM	DIMENSIONS
D	28.40 MAX.
D1	28.00±0.20
E	9.30 MAX.
E1	8.89±0.20
A	4.85±0.15
A1	0.51 MIN.
A2	3.80
e	1.778 (T.P.)
e1	10.16 (T.P.)
b	0.46 <sup>+0.10</sup> <sub>-0.06</sub>
b1	1.00±0.10
b2	0.73±0.10
c	0.25 <sup>+0.10</sup> <sub>-0.05</sub>
L	3.20±0.30
x	0.17
θ	0° to 15°
Z	0.635

P32CT-70-DAA-1