


JEDEC TRAY

Tray Code	RENESAS Code	Previous Code
L196-52	PLBG0175GA-A	175FHE
	PLBG0199GA-A	199FHE
	PLBG0224GA-A	224FHE
	PLBG0261JA-A	261FHE
	PLBG0288JA-A	288FHE
	PLBG0320KB-A	320FHE
	PLBG0417KA-A	417FHE
	PLBG0452KA-A	452FHE-A
	PTBG0175GA-A	175F7F

Unit:mm



The pin1 is located in the hatching portion

Note : Numbers in parentheses are the numbers of ICs contained in five trays per inner box, and those without parentheses are the numbers of ICs contained in eight trays per inner box.

Position dimension of cells (mm)	Z_w	15.45
	Z_L	15
	e_w	15
	e_L	15
Thickness (mm)	H_1	7.62
Number of cells	N_w	8
	N_L	20
Maximum storage No. IC/Tray		160
Maximum storage No. IC/Inner box (Note)		1280(800)
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack