

ISL71590SEH

Total Dose Testing

AN1895

Rev 2.00

December 20, 2016

Introduction

This report documents the results of low and high dose rate total dose testing and subsequent anneals of the [ISL71590SEH](#) radiation hardened temperature sensor. The tests were conducted to provide an assessment of the total dose hardness of the part, and to provide an estimate of dose rate sensitivity. Parts were irradiated under bias and with all pins grounded at low and high dose rate. The ISL71590SEH is acceptance tested on a wafer-by-wafer basis to 300krad(Si) at high dose rate (50–300rad(Si)/s) and to 50krad(Si) at low dose rate (0.01rad(Si)/s).

Downpoints for the low dose rate tests were 0, 10, 30, 50, 114, and 150krad(Si). Downpoints for the high dose rate tests were 0, 30, 50, 100, 300, and 450krad(Si). All irradiations and anneals are complete.

Key Features

- Minimal accuracy shift over total dose rate irradiation.-2.0K to +0.5K
- Linear output current 1.0μA/K
- Wide operating power supply range 4V to 31V
- Low power consumption1.5mW at 5V supply
- Operating temperature range -55°C to +125°C
- SEL/SEB threshold LET. 86.4MeV•cm²/mg
- Total dose tolerance, high dose rate. 300krad(Si)
- Total dose tolerance, low dose rate 50krad(Si)
- QML qualified per MIL-PRF-38535
- Produced in conformance with Standard Microcircuit Drawing (SMD) [5962-13215](#)

Part Description

The ISL71590SEH is a radiation-hardened two-terminal temperature transducer. It has a high impedance current output that allows it to be insensitive to voltage drops across long lines. With a supply voltage of between 4V and 36V applied to the input pin, the device acts as a constant current generator with a scale factor of 1μA/K. The ISL71590SEH is specified across the -55°C to +125°C temperature range and can operate across the -55°C to +150°C temperature range without the need of additional circuitry.

With power requirements as low as 1.5mW (5V at +25°C), the part is an ideal choice for payload and booster temperature sensing as any well-insulated twisted pair cable can be used for proper operation. The ISL71590SEH can be used in a wide range of applications including temperature compensation networks, laser diode temperature compensation, sensor bias and linearization functions, and Proportional To Absolute Temperature (PTAT) biasing. The high output impedance (>10MΩ) leaves plenty of room for variations in the power supply voltage. The part is electrically durable as it can withstand an absolute maximum forward voltage of 40V outside of the heavy ion environment (with a 37V absolute maximum in-beam rating) and a reverse voltage of -40V. The ISL71590SEH is available in a 2 Ld hermetically sealed flatpack.

Related Literature

- For a full list of related documents, visit our website
 - [ISL71590SEH](#) product page
- MIL-STD-883 test method 1019

Test Description

Irradiation Facilities

High dose rate testing was performed at 69.7rad(Si)/s using a Gammacell 220 ⁶⁰Co irradiator located in the Palm Bay, Florida Intersil facility. Low dose rate testing was performed at 0.01rad(Si)/s using the Intersil Palm Bay Hopewell Designs N40 panoramic ⁶⁰Co irradiator. Annealing was performed under the [Figure 1](#) bias configuration at +100 °C for 168 hours using a small temperature chamber.

Test Fixturing

[Figure 1](#) shows the configuration used for biased irradiation at both high and low dose rate.




FIGURE 1. IRRADIATION BIAS CONFIGURATION FOR THE ISL71590SEH

Characterization Equipment and Procedures

All electrical testing was performed outside the irradiator using the production Automated Test Equipment (ATE) with datalogging at each downpoint. Downpoint electrical testing was performed at room temperature. Due to the precision nature of the part all electrical characterization is performed using production ATE and an advanced constant-temperature liquid bath facility.

Experimental Matrix

Total dose irradiation proceeded in accordance with the guidelines of MIL-STD-883 Test Method 1019.7. The experimental matrix consisted of five samples irradiated at low dose rate under bias, five samples irradiated at low dose rate with all pins grounded, five samples irradiated at high dose rate under bias, and five samples irradiated at high dose rate with all pins grounded.

Samples of the ISL71590SEH were drawn from preproduction wafer lot X0A8P and were packaged in the hermetic 2 Ld solder-sealed production flatpack (K2.A) package. Samples were processed through the standard burnin cycle before irradiation, as required by MIL-STD-883.

Downpoints

Downpoints for the low dose rate tests were 0, 10, 30, 50, 114, and 150krad(Si). Downpoints for the high dose rate tests were 0, 30, 50, 100, 300, and 450krad(Si). All irradiations were followed by a high temperature anneal at +100 °C under bias.

Test Results

Attributes Data

TABLE 1. ISL71590SEH TOTAL DOSE TEST ATTRIBUTES DATA

PART	DOSE RATE Rad(Si)/s	BIAS	SAMPLE SIZE	DOWNPOINT	PASS (Note 1)	FAIL
ISL71590SEH	0.01	Figure 1	5	Pre-irradiation	5	-
				10krad(Si)	5	0
				30krad(Si)	5	0
				50krad(Si)	5	0
				114krad(Si)	3	2
				150krad(Si)	1	4
				Anneal	5	0
ISL71590SEH	0.01	Grounded	5	Pre-irradiation	5	-
				10krad(Si)	5	0
				30krad(Si)	5	0
				50krad(Si)	5	0
				114krad(Si)	3	2
				150krad(Si)	0	5
				Anneal	5	0
ISL71590SEH	69.7	Figure 1	5	Pre-irradiation	5	-
				30krad(Si)	5	0
				50krad(Si)	5	0
				100krad(Si)	5	0
				300krad(Si)	5	0
				450krad(Si)	5	0
				Anneal	5	0
ISL71590SEH	69.7	Grounded	5	Pre-irradiation	5	-
				30krad(Si)	5	0
				50krad(Si)	5	0
				100krad(Si)	5	0
				300krad(Si)	5	0
				450krad(Si)	5	0
				Anneal	5	0

NOTE:

- 'Pass' indicates a sample that passes all post-irradiation SMD limits.

Variables Data

The plots in [Figures 2](#) through [7](#) show data at all downpoints. We plotted the average, minimum, and maximum of the total dose response for each parameter at low and high dose rate. For clarity in interpreting the temperature error data, [Figure 2](#) shows

the combined low and high dose rate response, [Figure 3](#) shows the low dose rate response only, and [Figure 4](#) shows the high dose rate response only.

Variables Data Plots




FIGURE 2. ISL71590SEH temperature error in Kelvin as a function of total dose irradiation at low and at high dose rate for the biased (per [Figure 1](#)) and unbiased (all pins grounded) cases, plotting the average, minimum, and maximum. The low dose rate was 0.01rad(Si)/s and the high dose rate was 69.7rad(Si)/s. The irradiations were followed by a +100 °C 168-hour biased anneal; the LDR anneal was performed after 150krad(Si) at low dose rate, while the HDR anneal was performed after 450krad(Si) at high dose rate. The sample size for all cells was five. The post-irradiation SMD specification limits are -2.0K to +0.5K.

Variables Data Plots (Continued)




FIGURE 3. ISL71590SEH temperature error in Kelvin as a function of total dose irradiation at low dose rate for the biased (per Figure 1) and unbiased (all pins grounded) cases, plotting the average, minimum, and maximum. The dose rate was 0.01rad(Si)/s. The irradiations were followed by a +100 °C 168-hour biased anneal; the LDR anneal was performed after 150krad(Si) at low dose rate. The sample size for all cells was five. The post-irradiation SMD specification limits are -2.0K to +0.5K.




FIGURE 4. ISL71590SEH temperature error in Kelvin as a function of total dose irradiation at high dose rate for the biased (per Figure 1) and unbiased (all pins grounded) cases, plotting the average, minimum, and maximum. The dose rate was 69.7rad(Si)/s. The irradiations were followed by a +100 °C 168-hour biased anneal; the HDR anneal was performed after 450krad(Si) at high dose rate. The sample size for all cells was five. The post-irradiation SMD specification limits are -2.0K to +0.5K.

Variables Data Plots (Continued)




FIGURE 5. ISL71590SEH power supply rejection at 4V supply, in $\mu\text{A}/\text{V}$, as a function of total dose irradiation at low and at high dose rate for the biased (per Figure 1) and unbiased (all pins grounded) cases, plotting the average, minimum, and maximum. The low dose rate was $0.01\text{rad}(\text{Si})/\text{s}$ and the high dose rate was $69.7\text{rad}(\text{Si})/\text{s}$. The irradiations were followed by a $+100^\circ\text{C}$ 168-hour biased anneal; the LDR anneal was performed after $150\text{krad}(\text{Si})$ at low dose rate, while the HDR anneal was performed after $450\text{krad}(\text{Si})$ at high dose rate. The sample size for all cells was five. The post-irradiation SMD specification limits are $-0.5\mu\text{A}/\text{V}$ to $+0.5\mu\text{A}/\text{V}$.




FIGURE 6. ISL71590SEH power supply rejection at 15V supply, in $\mu\text{A}/\text{V}$, as a function of total dose irradiation at low and at high dose rate for the biased (per Figure 1) and unbiased (all pins grounded) cases, plotting the average, minimum, and maximum. The low dose rate was $0.01\text{rad}(\text{Si})/\text{s}$ and the high dose rate was $69.7\text{rad}(\text{Si})/\text{s}$. The irradiations were followed by a $+100^\circ\text{C}$ 168-hour biased anneal; the LDR anneal was performed after $150\text{krad}(\text{Si})$ at low dose rate, while the HDR anneal was performed after $450\text{krad}(\text{Si})$ at high dose rate. Sample size for all cells was five. The post-irradiation SMD specification limits are $-0.2\mu\text{A}/\text{V}$ to $+0.2\mu\text{A}/\text{V}$.

Variables Data Plots (Continued)




FIGURE 7. ISL71590SEH power supply rejection at 31V supply, in $\mu\text{A/V}$, as a function of total dose irradiation at low and at high dose rate for the biased (per Figure 1) and unbiased (all pins grounded) cases, plotting the average, minimum, and maximum. The low dose rate was 0.01rad(Si)/s and the high dose rate was 69.7rad(Si)/s . The irradiations were followed by a $+100^\circ\text{C}$ 168-hour biased anneal; the LDR anneal was performed after 150krad(Si) at low dose rate, while the HDR anneal was performed after 450krad(Si) at high dose rate. Sample size for all cells was five. The post-irradiation SMD specification limits are $-0.1\mu\text{A/V}$ to $+0.1\mu\text{A/V}$.

Discussion and Conclusion

We report the results of a characterization low and high dose rate total dose test of the ISL71590SEH integrated temperature sensor. All irradiations were followed by a high temperature anneal at $+100^\circ\text{C}$ under bias. All electrical measurements were performed at room temperature and were performed before irradiation, after each irradiation step, and after each annealing period. This is a simple part with one key performance parameter, the temperature error, but that simplicity does not necessarily translate into easy electrical testing. Careful liquid-bath testing using Fluorocarbon fluid is required for repeatable and accurate data (and for adequate production testing as well, incidentally) and we used four control units at each test operation to insure repeatable data.

Figures 2 through 7 show the total dose and anneal response of the part's parameters. In Figure 2 we plot both the low and high dose rate response on the same set of axes, while Figures 3 and 4 show the low dose rate and high dose rate responses separately for clarity.

The temperature error showed a very gradual change over high dose rate irradiation (Figures 2 and 4) from the pre-irradiation value of near zero to -0.5K after 450krad(Si) , with minimal anneal response. The low dose rate irradiation produced more pronounced shifts (Figures 2 and 3), with the samples within the -2.0K to $+0.5\text{K}$ SMD limits after 50krad(Si) , but with some out of specification on the negative side after the 114krad(Si) and

150krad(Si) downpoints. See attributes data in Table 1. We observed a strong anneal response back to approximately -1.5K , see Figures 2 and 3, resulting in all samples being within the -2.0K SMD limit after anneal. Interestingly, we observed no bias sensitivity at all for either dose rate. The power supply rejection is the only other measured parameter and was found to be stable at 4V, 15V, and 31V supply voltage, although the data for the 114krad(Si) low dose rate downpoint is suspect, especially for the 31V case; see Figure 7. The parameter remained well within the respective SMD limits at all downpoints.

We conclude that the temperature error remained within the -2.0K to $+0.5\text{K}$ SMD post-irradiation specification limits after 50krad(Si) at low dose rate or 300krad(Si) at high dose rate, but the part must be considered low dose rate sensitive based on the 'delta parameter' diagnostic algorithm outlined in MIL-STD-883 test method 1019 or based simply on inspection of Figure 2. As noted before, the ISL71590SEH is acceptance tested on a wafer-by-wafer basis at both low and high dose rate. No differences in total dose response between biased and grounded irradiation were noted at either dose rate, and the part is hence not considered bias sensitive. Interestingly, high temperature biased annealing following low dose rate irradiation produced a strong anneal signature, while performing the same step on high dose rate samples produced no response at all.

Appendices

TABLE 2. REPORTED PARAMETERS AND THEIR POST-IRRADIATION LIMITS

FIGURE	PARAMETER	LIMIT, LOW	LIMIT, HIGH	UNITS	NOTES
2	Temperature error, high and low dose rate	-2.0	+0.5	K	
3	Temperature error, low dose rate	-2.0	+0.5	K	
4	Temperature error, high dose rate	-2.0	+0.5	K	
5	Power supply rejection ratio	-0.5	+0.5	μA/V	4V supply
6	Power supply rejection ratio	-0.2	+0.2	μA/V	15V supply
7	Power supply rejection ratio	-0.1	+0.1	μA/V	31V supply

Revision History The revision history provided is for informational purposes only and is believed to be accurate, but not warranted. Please visit our website to make sure you have the latest revision.

DATE	REVISION	CHANGE
December 15, 2016	AN1895.2	Updated temperature error limits.
September 2, 2015	AN1895.1	Final report - all irradiations and anneals are complete.
November 1, 2013	AN1895.0	Initial report.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338