

Widescreen Signaling (WSS)

Introduction [1]

To facilitate the handling of various aspect ratios of program material received by TVs, a widescreen signalling (WSS) system has been developed. This standard allows a WSS-enhanced 16:9 TV to display programs in their correct aspect ratio.

The Copy Generation Management System (CGMS-A) for analog PAL video signals will use some of the reserved bits. For analog NTSC video signals, EIA-744 adds CGMS capability to EIA-608. The PALplus system, which allows the transmission of 16:9 programs over normal PAL systems, requires the presence of the WSS signal.

625-line PAL and SECAM systems are based on ITU-R BT.1119 [2]; 525-line NTSC systems are based on EIAJ CPX-1204. [3] For analog YUV video signals, WSS information should be present on the Y signal. For analog RGB video signals, WSS information should be present on all three signals.

625-Line PAL and SECAM Systems

DATA TIMING

The first part of line 23 is used to transmit the WSS information, as shown in Figure 1.

The clock frequency is 5MHz ($\pm 100\text{Hz}$). The signal waveform should be a sine-squared pulse, with a half-amplitude duration of $200 \pm 10\text{ns}$. The signal amplitude is $500\text{mV} \pm 5\%$.

The NRZ (non-return to zero) data bits are processed by a bi-phase code modulator, such that one data period equals 6 elements at 5MHz.

DATA CONTENT

The WSS consists of a run-in code, a start code, and 14 bits of data, as shown in Table 1.




FIGURE 1. 625-LINE WSS LINE 23 TIMING

TABLE 1. PAL WSS INFORMATION

| | | |
|--------------------------------|--|---|
| Run-In | 29 Elements at 5MHz | 1 1111 0001 1100 0111 0001 1100 0111 (1F1C 71C7 _H) |
| Start Code | 24 Elements at 5MHz | 0001 1110 0011 1100 0001 1111 (1E 3C1F _H) |
| Group 1 (Aspect Ratio) | 24 Elements at 5MHz "0" = 000 111 "1" = 111 000 | b3, b2, b1, b0 |
| Group 2 (Enhanced Services) | 24 Elements at 5MHz "0" = 000 111 "1" = 111 000 | b7, b6, b5, b4 (b5, b6, b7 = "0" since they are reserved) |
| Group 3 (Subtitles) | 18 Elements at 5MHz "0" = 000 111 "1" = 111 000 | b10, b9, b8 |
| Group 4 (Reserved) | 18 Elements at 5MHz "0" = 000 111 "1" = 111 000 | b13, b12, b11 (b11, b12, b13 = "0" since they are reserved) |

RUN-IN

The run-in consists of 29 elements at 5MHz of a specific sequence, shown in Table 1.

START CODE

The start code consists of 24 elements at 5MHz of a specific sequence, shown in Table 1.

GROUP 1 DATA

The group 1 data consists of 4 data bits that specify the aspect ratio. Each data bit generates 6 elements at 5MHz. Data bit b0 is the LSB.

Table 2 lists the data bit assignments and usage. The number of active lines listed in Table 2 are for the exact aspect ratio (a = 1.33, 1.56, or 1.78).

The aspect ratio label indicates a range of possible aspect ratios (a):

$$4:3a \leq 1.46$$

$$14:91.46 < a \leq 1.66$$

$$16:91.66 < a \leq 1.90$$

$$>16:9a > 1.90$$

To allow automatic selection of the display mode, a 16:9 receiver should support the following minimum requirements:

Case 1: The 4:3 aspect ratio picture should be centered on the display, with black bars on the left and right sides.

Case 2: The 14:9 aspect ratio picture should be centered on the display, with black bars on the left and right sides. Alternately, the picture may be displayed

using the full display width by using a small (typically 8%) horizontal geometrical error.

Case 3: The 16:9 aspect ratio picture should be displayed using the full width of the display.

Case 4: The >16:9 aspect ratio picture should be displayed as in Case 3 or use the full height of the display by zooming in.

GROUP 2 DATA

The group 2 data consists of four data bits that specify enhanced services. Each data bit generates six elements at 5MHz. Data bit b4 is the LSB.

b4:

0 camera mode

1 film mode

GROUP 3 DATA

The group 3 data consists of three data bits that specify subtitles. Each data bit generates six elements at 5MHz. Data bit b8 is the LSB.

b8:

0 no subtitles within teletext

1 subtitles within teletext

b10, b9:

00 no open subtitles

01 subtitles inside active image

10 subtitles outside active image

11 reserved

TABLE 2. PAL WSS GROUP 1 (ASPECT RATIO) DATA BIT ASSIGNMENTS AND USAGE

| b3, b2, b1, b0 | ASPECT RATIO LABEL | FORMAT | POSITION | ACTIVE LINES | MINIMUM REQUIREMENTS |
|----------------|--------------------|--------------------------|----------|--------------|----------------------|
| 1000 | 4:3 | Full Format | - | 576 | Case 1 |
| 0001 | 14:9 | Letterbox | Center | 504 | Case 2 |
| 0010 | 14:9 | Letterbox | Top | 504 | Case 2 |
| 1011 | 16:9 | Letterbox | Center | 430 | Case 3 |
| 0100 | 16:9 | Letterbox | Top | 430 | Case 3 |
| 1101 | > 16:9 | Letterbox | Center | - | Case 4 |
| 1110 | 14:9 | Full Format | Center | 576 | - |
| 0111 | 16:9 | Full Format (Anamorphic) | - | 576 | - |

525-Line NTSC Systems

DATA TIMING

Lines 20 and 283 are used to transmit the WSS information, as shown in Figure 2.

The bit frequency is $F_{SC}/8$ or about 447.443kHz; F_{SC} is the color subcarrier frequency of 3.579545MHz. The signal waveform of a data bit should be a sine-squared pulse, with a half-amplitude duration of $2.235\mu\text{s} \pm 20\text{ns}$. The signal amplitude is 70 ± 10 IRE for a "1"; 0 ± 5 IRE for a "0".

DATA CONTENT

The WSS consists of 2 bits of start code, 14 bits of data, and 6 bits of CRC (cyclic redundancy check) as shown in Table 3. The CRC used is $X^6 + X + 1$, all preset to "1".

START CODE

The start code consists of a "one" data bit followed by a "zero" data bit, shown in Table 3.

WORD 0 DATA

The word 0 data consists of 6 data bits:

b0:

0 = 4:3 aspect ratio

1 = 16:9 aspect ratio

b1:

0 = normal

1 = letterbox

b2-b5 = 0000

WORD 1 DATA

All bits are reserved, and have a value of "0".

WORD 2 DATA

All bits are reserved, and have a value of "0".

TABLE 3. NTSC WSS INFORMATION

| | |
|------------|--|
| Start Code | "1" |
| Start Code | "0" |
| Word 0 | b5, b4, b3, b2, b1, b0 |
| Word 1 | b9, b8, b7, b6 (= "0000" since they are reserved) |
| Word 2 | b13, b12, b11, b10 (= "0000" since they are reserved) |
| CRC | b19, b18, b17, b16, b15, b14 |




FIGURE 2. 525-LINE WSS LINE 20 AND LINE 283 TIMING

Summary

This Application Note presented some of the capabilities of the widescreen signalling (WSS) signal. With the number of widescreen TVs rapidly increasing, WSS allows the consumer to personally configure their TVs for greatest viewing enjoyment.

Using NTSC and PAL decoders that support WSS, such as the HMP8116, can bring new capabilities to multimedia PCs and 16:9 TVs. These capabilities include being able to handle 16:9 programs and supporting CGMS-A.

Using NTSC and PAL encoders that support WSS, such as the HMP8171 and HMP8173, allow the design of DVD players and settop boxes that support these emerging standards without becoming rapidly obsolete.

References

- [1] Jack, Keith. *Video Demystified*. San Diego, CA: HighText Interactive, Inc., 1996.
- [2] ITU-R BT.1119
- [3] EIAJ CPX-1204

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
 11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338